

CHERRY DW 5000



Models may vary from the image shown

A wireless desktop for high flyers.

The CHERRY DW 5000 is rock-solid CHERRY technology in a functional design. Made to the highest quality standards ensuring lasting reliability. For use at home and in the workplace.

Key benefits

- High-quality, wireless keyboard with 10 hotkeys
- Optical sensor technology (1500 dpi)
- 3-button mouse, for both left-handed and right-handed operation
- Battery status display in keyboard and mouse
- Simple installation; no technical knowledge required
- Interference-free, wireless 2.4 GHz technology (with a range of approx. 8 m)
- Operation of several desktops (multi-station capability)
- USB receiver

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

anthracite

Key colour:

black

Weight (product):

approx. 800 g (keyboard with battery), approx. 113 g (mouse with battery), approx. 3 g (receiver)

Total weight (with packaging):

approx. 1500 g

Transmission range:

approx. 8 m

Frequency range:

2.400 GHz - 2.4835 GHz

Storage Temperature:

-15°C to 60°C

Operating Temperature:

0°C to 40°C





Current Consumption:

max. 5 mA (keyboard), max. 15 mA (mouse), max. 35 mA (receiver)

Interface:

- USB

Product approvals:

- c-tick 
- CE 
- FCC 
- cTUVus 

System requirements:

- USB connection

Delivery Volume:

- 2 batteries (type AA)
- 1 signal receiver
- Operating instructions in hard copy
- 2 batteries (type AAA)
- 1 optical wireless mouse
- 1 wireless keyboard

Dimensions (product):

467.7 x 171.5 x 21.6 mm (keyboard), 112.53 x 64.97 x 34.11 mm (mouse), 39.35 x 14 x 7.5 mm (receiver)

Packaging dimensions:

approx. 590 x 210 x 51 mm

Reliability:

- MTBF (90) > 80,000 hours

Mouse:

- Scanning: Optical
- Resolution: 1500 dpi
- Number of Keys: 3
- Mouse wheel design: Scroll wheel with key function
- Design: Symmetrical
- Connection: wireless
- Housing colour: black
- Key colour: anthracite

Keyboard:

- Key technology: LPK
- Service life, standard key: > 10 million key operations
- Inscription layout: Standard
- Number of Keys: Product dependant, see table "Models"
- Number of additional keys: 10

Packaging Unit:

- Number of products in the master package: 6
- Number of master packages per pallet: 18

Warranty:

2 years

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Number of Keys
1	CHERRY DW 5000	JD-0500BE-	4025112080159	Belgium	105+10
2	CHERRY DW 5000	JD-0500CH-	4025112080173	Switzerland	105+10
3	CHERRY DW 5000	JD-0500DE	4025112076619	Germany	105+10
4	CHERRY DW 5000	JD-0500ES-	4025112080210	Spain	105+10
5	CHERRY DW 5000	JD-0500EU	4025112076626	US English with EURO symbol	104+10
6	CHERRY DW 5000	JD-0500FR-	4025112080180	France	105+10
7	CHERRY DW 5000	JD-0500GB-	4025112080197	UK	105+10
8	CHERRY DW 5000	JD-0500IT-	4025112080203	Italy	105+10
9	CHERRY DW 5000	JD-0500PN-	4025112080623	Pan-Nordic	105+10