

Smooth Flow™ Tack Flux No-Clean in 10cc Syringe w/plunger & tip

Product Highlights

Smooth Flow™ Technology

A lower density flux vehicle for better shear spread and improved flow during heating

Ideal for all rework, solder, de-solder and reflow applications

Non-corrosive, non-conductive, no-clean

Tack flux will not run all over PCB when applied

Excellent wetting

Easily cleaned with isopropyl alcohol (IPA)

Attachment of BGA spheres

Soldering flip chip components

Long stencil life, Wide process window

Halogen Free (EN14582 test method)

Clear residue

Can be used with Lead and Lead-Free applications

RoHS 3 and REACH compliant



Representative Photo Only
Please note flux color may vary from light yellow to orange/brown

Specifications

Flux Type:	Synthetic No-Clean (for Lead and Lead-Free applications)
Flux Classification:	ROL0
Color:	Light yellow to orange/brown
Packaging:	10cc/10g Syringe
Shelf Life:	Refrigerated >24 months, Unrefrigerated >24 months

Stencil Life

>8 hours @ 20-50% RH 22-28°C (72-82°F)

>4 hours @ 50-70% RH 22-28°C (72-82°F)

Stencil Cleaning

Automated stencil cleaning systems for both stencil and misprinted boards. Manual cleaning using isopropyl alcohol (IPA).

Storage and Handling

Store refrigerated or at room temperature 3-25°C (37-77°F). Do not freeze. Allow 4 hours for flux to reach an operating temperature of 20-25°C (68-77°F) before use.

Transportation

This product has no shipping restrictions. Shipping below 0°C (32°F) or above 25°C (77°F) for normal transit times by ground or air will not impact this product's stated shelf life.

Conforms to the following Industry Standards:

J-STD-004B, Amendment 1 (Solder Fluxes):	Yes
RoHS 3 Directive (EU) 2015/863:	Yes