



MS Series


The MS series of cable end float switches are designed for controlling levels in large tanks, cisterns or reservoirs and can be directly installed on submersible pumps. The casing is manufactured in blow moulded Polyethylene (PEHD), with 5m PVC cable with protective earth conductor as standard. The switching element is a microswitch, with UL, VDE and CENELEC approvals, activated by a moving stainless steel ball and having an electrical life of 200,000 operations. Non hygroscopic closed cell expanded polyurethane is injected around the switch housing within the outer casing, hermetically sealing the unit. It is capable of working down to 100 metres depth in water.

Version with polyurethane cable is for use in fuel oils.

Technical Specifications					
Cynergy3 Part		MS10A	MS10B	MS20A	MS10AU
Contact Form		N/O	N/C	N/O	N/O
Switching Current Max. Resistive		10A	10A	20A	10A
Switching Current Max. AC		4A	4A	8A	4A
Inductive	DC	1 A	1A	2A	1A
Power Rating	AC VA	750	750	1500	750
Max	DC W	180	180	360	180
Switching Voltage	AC V	250			
Max	DC V	110			
Cable Material		PVC		Polyurethane	
Cable length		5m with protective earth wire included			
Body Material		High Density Polyethylene			
Temp Range	°C	0 / +55			
	°F	+ 32 / +131			
Max. working pressure bar		10			



- Direct power switching
- Cable mounting
- 100 metre depth



Cynergy3 Components Ltd
7 Cobham Road
Ferndown Industrial Estate
Wimborne
Dorset BH21 7PE
Tel: +44 (0) 1202 897969
sales@cynergy3.com
www.cynergy3.com


MS Series




Part Numbering System

		MS	10	A	U	10		
Series							Cable length in metres:	
Max. current							Blank = 5M standard	
Contact Form							Cable covering:	
A = n/o							Blank = PVC	
B = n/c							U = Polyurethane	
C = c/o							W = WRC approved	

Installation



wiring diagram for filling pump



wiring diagram for emptying pump

