

PANEL CUTOUT
MAX. PANEL THICKNESS
14.0mm [.551]


SWITCH FUNCTION	
POS. 1	POS. 2
ON	(ON)
1-3, 4-6	1-2, 4-5
(ON) = MOMENTARY	

Ø18.00
[.709 in]

Ø12.00
[.472 in]

▲ RING ILLUMINATION
COLOR: BLUE


▲ ACTUATOR FINISH
POLISHED STAINLESS STEEL



DPDT
CONTACT CONFIGURATION

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 1A 24VDC
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MΩ MIN.
8. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
10. OPERATING TEMP.: -20°C to 55°C
11. ▲ DENOTES CRITICAL PARAMETER.
12. LAMP VOLTAGE: 20mA, 24V
- ▲ 13. ILLUMINATION COLOR: BLUE
14. HARDWARE SUPPLIED: O-RING AND HEXNUT
- ▲ 15. INGRESS RATING: IP65
16. 2011/65/EU (ROHS) COMPLIANT



E-SWITCH®

C	22888	UPDATED RATING TO 1A 24VDC	6/27/17	MJR
B	20595	CHG LAMP VOLTAGE 24V WAS 2.8V	05/08/12	drg
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV3WF2H0SS-345

SCALE
3:2DATE
3/7/2012DR
BMADWG
52-PV3WF2H0SS345REV
C