

## Cooper Bussmann

[Homepage](#)  
[About Cooper Bussmann](#)  
[Contact Us](#)  
[Privacy](#)  
[Legal](#)  
[Cooper Bussmann® Brand](#)  
[Site Map](#)



## SC-40

Class G, Time-Delay Fuse, 40A, 480V

### Product Information

Product Type:	Fuse
Product Family:	Electrical Power
Brand:	Cooper Bussmann
Class:	G

### Recommended Products

Rec. Fuse Block:	<a href="#">G30060 Series</a>
Rec. Inline Fuse Holder:	<a href="#">HEJ Series</a>

### Physical Properties

Dimensions:	2.25in.(L) × 0.41in.(W) × 0in.(H)
-------------	-----------------------------------

### Datasheets

[Datasheet](#)

### Certifications

[UL Listed](#)

[CSA Certified](#)

### Electrical Properties

Maximum AC Voltage:	480
Maximum DC Voltage:	300
Amperage Rating:	40
AC Interrupting Ratings:	<ul style="list-style-type: none"> <li>100000 at 480V</li> </ul>
DC Interrupting Ratings:	<ul style="list-style-type: none"> <li>100000 at 300V</li> </ul>
Fuse Class:	Class G
Time Delay:	Yes

# Time-Delay Fuses

## Class G - 600 Volt, 1/2 - 20 Amps

### 480 Volt, 25 - 60 Amps



Catalog Symbol: SC  
 Current-Limiting  
 Ampere Rating: 1/2 to 60A (fast-acting),  
 7 to 60A (time-delay)  
 Voltage Ratings:  
 SC 1/2 to 20 600Vac, 170Vdc  
 SC 25 to 60 480Vac, 300Vdc  
 Interrupting Rating: 100,000A RMS Sym. AC, 10,000A dc  
 Agency Information:  
 UL Listed, Std. 248-5, Class G, Guide JDDZ, File E4273  
 CSA Certified, C22.2 No. 248.5, Class 1422-01, File 53787

**Catalog Numbers**


SC-1/2	SC-6	SC-25
SC-1	SC-7	SC-30
SC-1 1/2	SC-8	SC-35
SC-2	SC-9	SC-40
SC-2 1/2	SC-10	SC-45
SC-3	SC-12	SC-50
SC-4	SC-15	SC-60
SC-5	SC-20	—

**Carton Quantity and Weight**

Catalog Number	Carton Qty.	Weight†	
		Lbs.	Kg.
1/2-15	4	0.060	0.0272
20	4	0.064	0.029
25-30	2	0.040	0.018
35-60	2	0.075	0.0340

†Weight per carton.


**Dimensional Data**



Fuse (Amps)	A
SC-1/2 to 15	1.31"
SC-20	1.41"
SC-25 to 30	1.62"
SC-35 to 60	2.25"

**General Information:**

- Compact branch-circuit units with high interrupting rating and current-limitation.
- With 600V rating, they can be used in 120/208, 120/240 and 277/480V circuits.
- Length variations relative to case size make the "rejection" type fuses.
- In general, SC fuses are about 1/3 the size of the 600V NEC fuse type.
- SC fuses with ampere ratings above 6A have a degree of overload time-delay which permits them to pass temporary overloads. At 200% load, they have a minimum opening time of 12 seconds.



Recommended fuseblocks/fuseholders for Class G fuses  
 See Data Sheets listed below

- Open fuseblocks - 1106
- In-line fuseholders - 1123, 1124

CE