

AC axial fan

sickled blades (S series)

with full round nozzle

ebm-papst Mulfingen GmbH & Co. KG

Bachmühle 2 · D-74673 Mulfingen

Phone +49 7938 81-0

Fax +49 7938 81-110

info1@de.ebmpapst.com

www.ebmpapst.com

Limited partnership · Headquarters Mulfingen
County court Stuttgart · HRA 590344General partner Elektrobau Mulfingen GmbH · Headquarters Mulfingen
County court Stuttgart · HRB 590142

Nominal data

| Type | W4D400-CP12-30 | | | | |
|-------------------------------|-------------------|----------|----------|------|------|
| Motor | M4D074-EI | | | | |
| Phase | | 3~ | 3~ | 3~ | 3~ |
| Nominal voltage | VAC | 230 | 230 | 400 | 400 |
| Connection | | Δ | Δ | Y | Y |
| Frequency | Hz | 50 | 60 | 50 | 60 |
| Type of data definition | | fa | fa | fa | fa |
| Valid for approval / standard | | CE | CE | CE | CE |
| Speed | min ⁻¹ | 1450 | 1690 | 1450 | 1690 |
| Power input | W | 135 | 185 | 135 | 185 |
| Current draw | A | 0.76 | 0.68 | 0.44 | 0.39 |
| Max. back pressure | Pa | 150 | 120 | 150 | 120 |
| Min. ambient temperature | °C | -25 | -25 | -25 | -25 |
| Max. ambient temperature | °C | 40 | 40 | 40 | 40 |
| Starting current | A | 3.0 | 3.0 | 1.7 | 1.7 |

ml = max. load · me = max. efficiency · fa = running at free air · cs = customer specs · cu = customer unit
Subject to alterations

Data according to ErP directive

| | | | | | |
|-----------------------|--------|--------------------------------|-------------------|--------------|--------------|
| Installation category | A | Overall efficiency η_{es} | Actual | Request 2013 | Request 2015 |
| Efficiency category | Static | Efficiency grade N | 32.7 | 25.1 | 29.1 |
| Variable speed drive | No | Power input P_e | 43.6 | 36 | 40 |
| Specific ratio* | 1.00 | Power input P_e | kW | 0.19 | |
| | | Air flow q_v | m ³ /h | 2595 | |
| | | Pressure increase p_{fs} | Pa | 91 | |
| | | Speed n | min ⁻¹ | 1415 | |

Data established at point of optimum efficiency

* Specific ratio = $1 + p_s / 100\,000\text{ Pa}$ 

AC axial fan

sickled blades (S series)

with full round nozzle

Technical features

| | |
|---|---|
| Mass | 8 kg |
| Size | 400 mm |
| Material of electronics housing | Rotor: Coated in black |
| Material of impeller | Sheet steel, coated in black |
| Material of wall ring | Sheet steel, pre-galvanised and coated in black plastic |
| Material of guard grille | Steel, phosphated and coated in black plastic |
| Number of blades | 5 |
| Direction of air flow | "V" |
| Direction of rotation | Counter-clockwise, seen on rotor |
| Type of protection | IP 44; Depending on installation and position as per EN 60034-5 |
| Insulation class | "B" |
| Humidity class | F1-2 |
| Max. permissible ambient motor temp. (transp./ storage) | + 80 °C |
| Min. permissible ambient motor temp. (transp./storage) | - 40 °C |
| Mounting position | Shaft horizontal or rotor on bottom; rotor on top on request |
| Condensate discharge holes | Rotor-side |
| Operation mode | S1 |
| Motor bearing | Ball bearing |
| Touch current acc. IEC 60990 (measuring network Fig. 4, TN system) | < 0.75 mA |
| Cable exit | Variable |
| Protection class | I (if protective earth is connected by customer) |
| Approval | CCC |




AC axial fan

sickled blades (S series)


with full round nozzle

Product drawing



- | | |
|---|---|
| 1 | Direction of air flow "V" |
| 2 | Connection line PVC 7G 0.5 mm ² , 7x brass lead tips crimped |


Connection screen



Note: Direction of rotation changes when two phases are reversed

| | | | | | |
|----------|------------------|----|-----------------|----|--------------|
| Δ | Delta connection | Y | Star connection | L1 | black |
| L2 | blue | L3 | brown | U1 | black |
| V1 | blue | W1 | brown | U2 | green |
| V2 | white | W2 | yellow | PE | green/yellow |

Charts: Air flow 50 Hz



Measurement: LU-27622

Air performance measured as per ISO 5801 Installation category A. For detailed information on the measuring set-up, please contact ebm-papst. Suction-side noise levels: LwA measured as per ISO 13347 / LpA measured with 1m distance to fan axis. The values given are valid under the measuring conditions mentioned above and may vary according to the actual installation situation. With any deviation from the standard set-up, the specific values have to be checked and reviewed with the unit installed.

Measured values

| | Conn. | U | f | n | P _e | I | LpA _{in} | LwA _{in} | qv | p _{fs} |
|---|-------|-----|----|-------------------|----------------|------|-------------------|-------------------|-------------------|-----------------|
| | | V | Hz | min ⁻¹ | W | A | dB(A) | dB(A) | m ³ /h | Pa |
| 1 | Y | 400 | 50 | 1450 | 135 | 0.44 | 65 | 74 | 4000 | 0 |
| 2 | Y | 400 | 50 | 1435 | 161 | 0.47 | 65 | 73 | 3535 | 35 |
| 3 | Y | 400 | 50 | 1420 | 182 | 0.49 | 65 | 72 | 2995 | 70 |
| 4 | Y | 400 | 50 | 1410 | 203 | 0.50 | 67 | 74 | 2355 | 100 |


Conn. = Connection · U = Supply voltage · f = Frequency · n = Speed · P_e = Power input · I = Current draw · LpA_{in} = Sound pressure level inlet side · LwA_{in} = Sound power level inlet side
qv = Air flow · p_{fs} = Pressure increase



AC axial fan

sickled blades (S series)
with full round nozzle

Charts: Air flow 60 Hz



Measurement: LU-27623

Air performance measured as per ISO 5801 Installation category A. For detailed information on the measuring set-up, please contact ebm-papst. Suction-side noise levels: L_{wA} measured as per ISO 13347 / L_{pA} measured with 1m distance to fan axis. The values given are valid under the measuring conditions mentioned above and may vary according to the actual installation situation. With any deviation from the standard set-up, the specific values have to be checked and reviewed with the unit installed.

Measured values

| | Conn. | U | f | n | P _e | I | L _{pA_{in}} | L _{wA_{in}} | qv | p _{fs} |
|---|-------|-----|----|-------------------|----------------|------|------------------------------|------------------------------|-------------------|-----------------|
| | | V | Hz | min ⁻¹ | W | A | dB(A) | dB(A) | m ³ /h | Pa |
| 1 | Y | 400 | 60 | 1690 | 185 | 0.39 | 69 | 76 | 4615 | 0 |
| 2 | Y | 400 | 60 | 1660 | 223 | 0.45 | 70 | 76 | 4145 | 40 |
| 3 | Y | 400 | 60 | 1635 | 256 | 0.49 | 69 | 76 | 3580 | 80 |
| 4 | Y | 400 | 60 | 1605 | 290 | 0.54 | 70 | 76 | 2895 | 120 |

Conn. = Connection · U = Supply voltage · f = Frequency · n = Speed · P_e = Power input · I = Current draw · L_{pA_{in}} = Sound pressure level inlet side · L_{wA_{in}} = Sound power level inlet side
 qv = Air flow · p_{fs} = Pressure increase

