



RECOMMENDED PANEL CUTOUT
 EMPFOHLENER FRONTPLATTEN AUSSCHNITT



RECOMMENDED PCB LAYOUT - COMPONENT SIDE VIEW
 EMPFOHLENER FUER LEITERPLATTE - BESTÜCKUNGSSEITE
 ALL TOLERANCES ±0.05 [0.002] UNLESS NOTED



NOTE 1: SIDE SHIELD TABS IN FRONT 4.57mm (F1)
 NOTE 2: ONE REAR SHIELD TAB CENTERED

MATERIALS AND FINISH
 HOUSING: GLASS FILLED POLYESTER UL 94 V-0 BLACK
 SHIELDING: Cu ALLOY, PLATED WITH Ni
 CONTACTS: PHOSPHOR BRONZE
 CONTACT FINISH: Au, 0.8µm [30µin], OVER Ni
 TERMINAL FINISH: SnPb

Information: MAXCONN No.: MJHS-G-88-4A-30	Tolerances  All Dimensions in mm	Scale	2:1	-
		Designation	MOD JACK - MJR 8P8C, 1X4	
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.	Subject to modification without prior notice. Drawing will not be updated.	 www.ERNI.com	133198	
			Index	Date

Consider protection memos from DIN 24