








Stecklänge / mating length




Bestückungsplan / contact layout

32 31 30 29 28 27 26 25 24 23 22 21 20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1



Leiterplatten-Lochbild / PCB drillhole pattern



Elastische Einpresszone / compliant pressfit zone

Isolierwerkstoff / housing material : PBT GF 30

Bauart 4 / type 4

Anforderungsstufe 1 = 500 Steckzyklen / performance class 1 = 500 mating cycles

Fehlende Maße und Angaben nach IEC 60 603-2 / DIN EN 60 603-2

Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2

Schichtaufbau im metallisierten Loch siehe Zeichnung 164062 / Nr. 6
diameter of drilled hole see drawing 164062 / No. 6

1) $\phi 1.0^{+0.09}_{-0.06}$ Durchmesser des metallisierten Loches

$\phi 1.0^{+0.09}_{-0.06}$ Diameter of finished plated-through hole

Bedruckung siehe Zeichnung 294905

Marking see drawing 294905

Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 16016 is to be observed.

Information:				Tolerances				Scale 2:1			
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.		All Dimensions in mm		Designation			
								Messerleiste TE 160 EE <i>Male Connector TE 160 Pressfit</i>			
-		16.11.2009				www.ERNI.com		384673		A3	
Index		Date									
								Class		STVTE	

Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 16016 to be observed.