

SPECIFICATIONS

REV.	BY	DATE	PART NO.
K	BT	11-25-98	LCP8-10

ELECTRICAL

RESISTANCE RANGE (OHMS)-----	1K,2K,5K,10K,20K,50K
RESISTANCE TOLERANCE -----	±15%
LINEARITY,INDEPENDENT -----	±2.0%
RESOLUTION -----	ESSENTIALLY INFINITE
ELECTRICAL STROKE -----	.433±.020
OUTPUT SMOOTHNESS -----	0.1% AGAINST INPUT VOLTAGE
POWER RATING -----	0.2WATT
INSULATION RESISTANCE -----	1000 MEGOHMS @ 500 VDC
DIELECTRIC STRENGTH -----	500 VAC MIN.
FRICTION -----	30 GRAMS

MECHANICAL

MECHANICAL STROKE -----	.472
STOP STRENGTH -----	APPROX. 2 POUNDS
LIFE EXPECTANCY -----	20,000,000 STROKES
WEIGHT APPROX. -----	0.2 OZS.
MARKINGS -----	ETI SYSTEMS P/N LCP8-10 RESISTANCE
SPRING RETURN FORCE WHEN APPLICABLE -----	RETRACTED, APPROX. 230GRAMS EXTENDED, APPROX. 57GRAMS



ENVIRONMENTAL

SHOCK -----	50G, 11ms
VIBRATION -----	10Hz TO 2000Hz 15G
OPERATING TEMPERATURE RANGE -----	-30° C TO +105° C
TEMPERATURE COEFFICIENT -----	±400 PPM /°C

OPTIONS

RESISTANCE TOLERANCE -----	±10%
LINEARITY,PRECISION -----	±1%
SPECIAL MACHINED SHAFT	

SCHEMATIC



MODEL NO'S.

SHAFT STYLES

LCP8P-10	(P)		PLAIN
LCP8T-10	(T)		THREADED 2-56 UNC-2A
LCP8C-10	(C)		CHAMFERED
LCP8S-10	(S)		SPRING RETURN (INTERNAL)

SCALE	NONE
DATE	12--76
BY	
APPRV'D	BT
CODE IDENT:	19477

THIS DOCUMENT CONTAINS PROPRIETARY DATA OF POLARIS INDUSTRIAL ENTERPRISES, INC. NO DISCLOSURE, REPRODUCTION, OR USE OF ANY PART THERE OF MAY BE MADE EXCEPT BY WRITTEN PERMISSION.

TITLE

LINEAR MOTION
POTENTIOMETER



CARLSBAD
CALIFORNIA

PART NO.

LCP8-10

TOLERANCES

XX = +/- .010" FRACT. = +/- 1/64"
XXX = +/- .005" ANGLES = +/- 1/2°

ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.