


SC/UPC - E2000/APC Duplex Jumper, I-V(ZN)H 02E 9/125μ OS2, LSZH Yellow Jacket, x meter



Specifications:


1. Insertion Loss: < 0.3dB @1310nm
Return Loss: > 55dB@1310nm;E2000/APC:> 65dB@1310nm
2. End surface test is according to OP-03-05001
3. Test standard: GR-326-CORE
4. Test report has to match the serial No.
5. RoHS compliant
6. Fiber cable according to IEC 60793-2
7. SC connector according to IEC 61754-4
E2000 connector according to IEC 61754-15

**RoHS
compliant**

9	E2000/APC SM 3.0 connector,Green	2
8	E2000/APC 3.0 boot, green	2
7	Ø3.0mm SM duplex OS2 9/125μ LSZH Yellow cable	
6	Heat shrink tube, black	2
5	SC 3.0 boot, red	1
4	SC 3.0 boot, black	1
3	SC clip, blue	1
2	SC SM 3.0 connector, Blue	2
1	Dust cover	2
Item	Description	Qty

 ELEKTRONIK			
SC/UPC - E2000/APC Duplex Jumper, I-V(ZN)H 02E 9/125 OS2, LSZH Yellow Jacket, x meter			
Part No: O0939.x			
Drawing No:		Page :1 of 3	

Packing:
The corresponding label data for each cable assembly shall be affixed to the package



9# PE Bag(220mm x 280mm)

Prüfprotokoll
inspection sheet
Typ: O0939.x
Stückzahl 1
quantity 1

Einfügedämpfung nach DIN 18600 Verfahren 7
insertion loss acc. to DIN 18600 mode 7
Wellenlänge 1310 nm Steckerdämpfung<0.3dB
wavelength 1310nm insertion loss <0.3dB
9/125
Date: 2012-01-18
Achtung LWL Komponenten
attention fiber optic cable

-Vorsichtigig handhaben
handle with care
-Mindestbiegeradius von 40mm nicht unterschreiten
do not decrease bending radius of 40mm
-Stecken u. Lösen der Verbindung nur durch
Handhabung am Steckergehäuse
Ensure to use only connector body for connection/disconnection
Nicht am Kabel ziehen!!!
never pull at fiber optic cables!!!
-Reklamationen in diesem Bereich können wir nicht anerkennen
complaints in this regard cannot be accepted
-Ferrulen stets durch Staubschutzkappe schützen
und vor jedem Einsatz säubern
ferrules must be protected via dust covers and must be
cleaned before use

Test Report

SC/UPC - E2000/APC Duplex Jumper, I-V(ZN)H 02E
9/125 OS2, LSZH Yellow Jacket, x meter

Part Number: O0939.x Quantity:1 pc

SC/UPC		E2000/APC	
IL: 0.13dB	RL: 57dB	IL: 0.09dB	RL: 65dB
IL: 0.06dB	RL: 59dB	IL: 0.10dB	RL: 67dB

Bar Code: [Barcode]

Batch: 20120118

Bar Code Label(100mmx60mm)

RoHS
compliant



EFB

SC/UPC - E2000/APC Duplex Jumper, I-V(ZN)H 02E 9/125 OS2, LSZH Yellow Jacket, x meter

Part No: O0939.x

Drawing No:

Page :2 of 3

Indoor Cable Series (Duplex)

1. Characteristics

- . Aramid yarn strenth member ensures tension resistance and long term stability in transmission
- . Figure 8 structure jacket facilitate embranchment
- . Small outer diameter, lightweight
- . Flame-retardant jacket, halogenfree
- . Low attenuation

2.Applications

- .Installation in conduits and shafts
- .Indoor distribution
- .Jumper and adapter cable
- .Connecting workstations inside buildings(FTTD)

3.Temperature Range


-20°C up to +70°C

4.Fiber Optic Cable Performance

- .Number of fibers: 2
- .Outer diameter: 2.8×5.7 mm
- .Nominal weight: 13.2 kg / km
- .Max. tension: 300 N (short - term)
160 N (long - term)
- .Min. Bending Radius: 20 H (Dynamic)
10 H (Static)
- .Max . Crush Resistance (N/100 mm²):1000
- .Complies with TIA/EIA-568 B.3 & Bellcore GR-409-CORE & OFNR-UL/CSA FT-4
- .Maximum Attenuation: ≤ 0.4dB @Full spectrum
- .Dispertion Coefficient: ≤ 3.0ps/(nm.km) @1310nm
≤ 18ps/(nm.km) @1550nm

5.Cable Specification

- .Fiber type: Singlemode 9/125μ m OS2
- .Yellow jacket , LSZH



**RoHS
compliant**



EFB

SC/UPC - E2000/APC Duplex Jumper, I-V(ZN)H 02E 9/125 OS2, LSZH
Yellow Jacket, x meter

Part No: O0939.x

Drawing No:

Page :3 of 3