



PART NO.	HOLDING DIA. "D"	"E" REF.
SPNW-3	3/16 (4.8)	.60 (15.2)
SPNW-4	1/4 (6.4)	.63 (16.0)
SPNW-5	5/16 (7.9)	.66 (16.8)
SPNW-6	3/8 (9.5)	.69 (17.5)
SPNW-7	7/16 (11.1)	.72 (18.3)
SPNW-8	1/2 (12.7)	.75 (19.1)
SPNW-9	9/16 (14.3)	.85 (21.6)
SPNW-10	5/8 (15.9)	.88 (22.4)
SPNW-11	11/16 (17.5)	.91 (23.1)
SPNW-12	3/4 (19.1)	.94 (23.9)
SPNW-14	7/8 (22.2)	1.00 (25.4)
SPNW-16	1.0 (25.4)	1.06 (28.5)
SPNW-18	1-1/8 (28.6)	1.15 (29.2)
SPNW-20	1-1/4 (31.8)	1.21 (30.7)

NOTES:

1. MATERIAL: CLAMPS: STEEL, (ZINC ELECTROPLATED).
2. CUSHION: NEOPRENE, (MIL R-3065 AND AMS-3209).
3. COLOR: SILVER WITH BLACK NEOPRENE CUSHION.

REV	DESCRIPTION	ENGR	DATE	TITLE:	FILE #	DWN:	APP:	PART #	PRINT TYPE
F	REMOVED VIEW NEOPRENE CUSHION; CHANGED TITLE BLOCK AND FILE NO.	SM	03.26.01	STEEL PLATED NEOPRENE CLAMP, WIDE	SPNW	P.B.		SEE TABLE	CA
E	CONVERTED TO ACAD	PB	12.21.95	TOLERANCES UNLESS NOTED					
D	"E" DIM. CHANGED	RS	02.24.92	.XX=±.010	MAT'L: SEE NOTES	DT: 12-21-95	DT:		
C	"E" MADE "E" REF. FRACTION MADE DECIMAL ("E" ONLY)	FL	04.04.91	.XXX=±.005	RE: RICHCO, INC.		RICHCO INC.		
B	REDRAWN, SIZES -22, -24, & -32 DELETED	JO	01.31.90	FRAC=1/64			PO BOX 804238, CHICAGO, 60680		
				ANG=1°			(773) 539-4060		