



Anwendung/Application :

3.3V - 5.0V
Universal PCI

Operating System (OS):

Geprüft/Approved:

Verpackung/Packing:



LowProfile 1P Parallel SPP/EPP/ECP PCI 32-Bit Karte

Beschreibung :	Die EX-41211 LowProfile PCI Parallel Karte stellt einen Parallel SPP/EPP/ECP High Performance Ausgang zur Verfügung. Er ist entwickelt worden um einen weiteren Parallele Ausgang für PC's, kleine Workstations oder Server über den PCI Bus zu erweitern. Die EX-41211 kann in schmale Gehäuse bis zu einer maximaler Bauhöhe von 8cm eingesetzt werden.
Merkmale :	- Universal PCI 32-Bit Parallel Karte mit einem Anschluss - Schnittstelle: SPP (Standard Parallel Port), EPP (Enhanced Parallel Port), ECP (Enhanced Capacity Port) - I/O Adressen: wird vom Betriebs System vergeben - Interrupt: wird vom System BIOS vergeben mit Interrupt Sharing - Keine Jumper Einstellung erforderlich (nicht möglich) - Unterstützt Motherboard mit 5V und 3.3V
Chip-Set :	Oxford OX12PCI840
Datentransfer-Rate :	2Mbyte/Sek.
Anschlüsse :	1 x 25 Pin D-SUB Parallel Buchse
Hardwaresysteme :	PCI 32-Bit und PCI-X 64-Bit Bus
Betriebstemperatur :	0 bis 55°C (32 bis 131°F)
Luftfeuchtigkeit :	5 bis 95%
Abmessung / Gewicht :	120 x 63 mm / 100g
Lieferumfang :	- EX-41211 - Treiber CD - Handbuch

LowProfile 1P Parallel SPP/EPP/ECP PCI 32-Bit card

Description :	The EX-41211 LowProfile PCI parallel adapter provides one SPP/EPP/ECP high performance ports. It is designed for PC's, thin clients or server to provide instant LPT port expansion via the PCI- or PCI-X Bus. The card is fully Universal PCI Plug-and-Play compatible and no IRQ and I/O address conflict problems. The EX-41211 can be use for a small computer chassis of maximum 8cm high.
Feature :	- Universal PCI 32-Bit Parallel card with one port - Interface: SPP (Standard Parallel Port), EPP (Enhanced Parallel Port), ECP (Enhanced Capacity Port) - I/O addresses: Setting from the operating system - Interrupt: Setting from the System BIOS with Interrupt Sharing - No Jumper setting - Support Motherboard with 5V and 3.3V
Chip-Set :	Oxford OX12PCI840
Data transfer rate :	2Mbyte/Sec.
Connectors :	1 x 25 pin D-SUB parallel female connector
Hardware system :	PCI 32-Bit and PCI-X 64-Bit Bus
Operating Temperature :	0 to 55°C (32 to 131°F)
Humidity :	5 to 95%
Size / Weight :	120 x 63 mm / 100g
Packaging contents :	- EX-41211 - Driver CD - Manual