


File E61760(N) 59140 and 59141 MINI FLANGE MOUNT SERIES



Features

- Magnetically operated position sensor
- Matching actuator available
- Compact size requires only 3.2cm² board space
- Screw down or adhesive mounting
- Customer defined sensitivity
- Choice of cable length
- Leads can exit from LH or RH side

Benefits

- No standby power requirement
- Operates through non-ferrous materials such as wood, plastic or aluminium
- Hermetically sealed, magnetically operated contacts continue to operate long after optical and other technologies fail due to contamination

Applications

- Position and limit sensing
- Security system switch
- Linear actuators
- Door switch

DIMENSIONS (in) mm		SCHEMATICS	
<p>Actuator</p>	<p>Sensor (2 wire versions)</p>	<p>Switch Types 1 & 2</p> <p>Switch Type 3</p> <p>Switch Type 4</p>	
		<p>Note: 59140 shown 59141 leads exit opposite side</p>	

CUSTOMER OPTIONS - Switching Specifications

TABLE 1	Switch Type	Select Option	1	2	3	4
		Contact Type	Normally Open	Normally Open High V.	Change Over	Normally Closed
Contact Rating	Power	Watts - max	10	10	5	5
Voltage	Switching	Vdc - max.	200	300	175	175
	Breakdown	Vdc - min.	250	450	200	200
Current	Switching	A - max.	0.5	0.5	0.25	0.25
	Carry	A - max.	1.2	1.5	1.5	1.5
Resistance	Contact, Initial	Ohms - max.	0.2	0.2	0.2	0.2
	Insulation	Ohms - min.	10 ¹⁰	10 ¹⁰	10 ⁹	10 ⁹
Temperature	Operating	°C	-40 to +105	-20 to +105	-40 to +105	-40 to +105
	Storage	°C	-65 to + 105	-65 to +105	-65 to +105	-65 to +105
Time	Operate	ms - max.	1.0	1.0	3.0	3.0
	Release	ms - max.	1.0	1.0	3.0	3.0
Capacitance	Contact	pF - typ.	0.3	0.2	0.3	0.3
Shock	11ms ½ sine	G - max.	100	100	50	50
Vibration	50-2000 Hz.	G - max.	30	30	30	30

CUSTOMER OPTIONS - Sensitivity, Cable Length and Termination Specifications

TABLE 2	Sensitivity	TABLE 3	Cable Length	TABLE 4	Termination (2 wire versions shown)																										
<p>Activate distances (d) are approximate using Hamlin 57140-000 actuator as illustrated.</p> <p>Switch AT before modification</p>		<p>(Cable 24AWG 7/32 PVC 105°C UL1430 / UL1569)</p>	<table border="1"> <thead> <tr> <th>Select Option</th> <th>Length(in)mm</th> </tr> </thead> <tbody> <tr> <td>02</td> <td>(11,81) 300</td> </tr> <tr> <td>05</td> <td>(39,37)1,000</td> </tr> </tbody> </table>	Select Option	Length(in)mm	02	(11,81) 300	05	(39,37)1,000	<table border="1"> <thead> <tr> <th>Select Option</th> <th>Description</th> <th>Diagram</th> </tr> </thead> <tbody> <tr> <td>A or F</td> <td>Tinned or untinned</td> <td></td> </tr> </tbody> </table>	Select Option	Description	Diagram	A or F	Tinned or untinned																
				Select Option	Length(in)mm																										
02	(11,81) 300																														
05	(39,37)1,000																														
Select Option	Description	Diagram																													
A or F	Tinned or untinned																														
<table border="1"> <thead> <tr> <th>Select Option</th> <th>S</th> <th>T</th> <th>U</th> <th>V</th> </tr> </thead> <tbody> <tr> <td>Switch Type</td> <td>Pull-In AT Range</td> <td>Activate Distance (d) (in)mm</td> <td>Pull-In AT Range</td> <td>Activate Distance (d) (in)mm</td> </tr> <tr> <td>1</td> <td>12-18</td> <td>(.453)</td> <td>17-23</td> <td>(.374)</td> </tr> <tr> <td>2</td> <td>11.5</td> <td>9.5</td> <td>22-28</td> <td>8.0</td> </tr> <tr> <td>3</td> <td>15-20</td> <td>(.413)</td> <td>20-25</td> <td>(.354)</td> </tr> <tr> <td>4</td> <td>10.5</td> <td>9.0</td> <td>25-30</td> <td>7.5</td> </tr> </tbody> </table>	Select Option	S	T	U	V	Switch Type	Pull-In AT Range	Activate Distance (d) (in)mm	Pull-In AT Range	Activate Distance (d) (in)mm	1	12-18	(.453)	17-23	(.374)	2	11.5	9.5	22-28	8.0	3	15-20	(.413)	20-25	(.354)	4	10.5	9.0	25-30	7.5	<p>ORDERING INFORMATION</p> <p>Series 59140/59141 — 59140/59141 — X X XX X</p> <p>Switch Type — Table 1 (1, 2, 3 or 4)</p> <p>Sensitivity — Table 2 (S, T, U or V)</p> <p>Cable Length — Table 3 (02 or 05)</p> <p>Termination — Table 4 (A or F)</p>
Select Option	S	T	U	V																											
Switch Type	Pull-In AT Range	Activate Distance (d) (in)mm	Pull-In AT Range	Activate Distance (d) (in)mm																											
1	12-18	(.453)	17-23	(.374)																											
2	11.5	9.5	22-28	8.0																											
3	15-20	(.413)	20-25	(.354)																											
4	10.5	9.0	25-30	7.5																											