


MICRO SWITCH
FREEPORT ILLINOIS U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929


SWITCH-TOGGLE

112 TW1 SERIES CHART 2



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CAT. LIST.	RECOMMENDED LOCKING COMBINATIONS FOR CONFIGURATION SEE LETTERED DETAILS	CIRCUIT WITH TOGGLE IN			ELECTRICAL DATA
		EXTREME POSITION KEYWAY SIDE	CENTER	EXTREME POSITION OPPOSITE KEYWAY	
112 TW1-1	A, B, C, D, E, F, G, H, J, K, L, M, N, P	ON	OFF	ON	28VDC & 115 VAC 5 AMP RES 2 AMP IND 1 AMP LAMP
112 TW1-3	D, F, G	ON	NONE	ON	
112 TW1-5	E, F, K, L, M, N	MOM ON	OFF	ON	
112 TW1-7	E, L, N	MOM ON	OFF	MOM ON	
112 TW1-8	F	MOM ON	NONE	ON	
112 TW1-2	D, F, G	OFF	NONE	ON	



NOTE-

- 1 - FURNISHED UNASSEMBLED
- 2 - TERMINATION WILL ACCEPT CRIMP CONTACT CONFORMING TO M39029/1-101
- 3 - SUFFIX MUST BE ADDED FOR DESIRED TYPE TOGGLE LOCKING
- 4 - MATTE FINISH
- 5 - SWITCH DESIGNED TO CONFORM TO MS 27721 EXCEPT TERMINATION, LENGTH, AND WEIGHT

SCALE 2 TO 1
DO NOT SCALE PRINT
UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±
WEIGHT 1.0 OZ MAX