



1750L



NOTE: All LEADS 9.0" OUT MIN.

**DIMENSIONS:**

|   |                       |
|---|-----------------------|
| A | 4.050" ±0.063         |
| B | 3.050" ±0.125         |
| C | 3.500" ±0.063         |
| D | 2.490" ±0.063         |
| E | 1.940" ±0.063         |
| F | 3.460" ±0.063         |
| G | 0.187"X 0.300" ±0.015 |

**ELECTRICAL DATA:**

|                |                                       |
|----------------|---------------------------------------|
| Turns ratio:   | 31.16 : 1                             |
| Inductance     | @240V, 60Hz =>106.10H (Open circuit)  |
| DCR            | @ 20C, BLU - BRN =98.6 Ω ±20%         |
|                | @ 20C, BLK - GRN =0.170 Ω ±20%        |
| FREQ. RESP     | @ 50W, 70Hz - 15kHz REF. TO 1kHz ±1dB |
| Pri. Impedance | 4200 Ω CT, 458 V                      |
| Sec. Impedance | 4 Ω (124.14 V)                        |
| Power          | 50 WATTS                              |



**HAMMOND  
ELECTRONICS**

52 RANKIN PLACE,  
WATERLOO, ONTARIO, N2L 3Z5.  
PHONE (519) 886-6181  
FAX # (519) 886-9540

TITLE

OUTPUT TRANSFORMER

|    |          |              |                       |
|----|----------|--------------|-----------------------|
|    |          |              | DR BY<br>IOAN POP     |
| 0  | 05/11/09 | PRELIMINARY. | I.P. DATE<br>05/11/09 |
| NO | DATE     | REVISION     | DIM IN(X)MM( )        |

1750L