



DIMENSIONS:

A	2.500" ±0.063
B	2.685" ±0.125
C	3.060" ±0.063
D	2.000" ±0.063
E	1.688" ±0.063
G	0.203" x 0.375" ±0.015



NOTE: ALL LEADS 6" OUT MIN. STRIPPED 0.5"



ELECTRICAL DATA:

TESTS	CONDITIONS	ACCEPTANCE CRITERIA
Iex	@ 125V, 60Hz, WHT - BLK	188.4mA Max.
Sec. N.L.V	@ 125V, 60Hz, WHT - BLK	
	RED - RED =	611.7V ±2%
	RED - RED/YEL = RED/YEL - RED =	305.9V ±2%
	YEL - YEL =	7.012V ±2%
	GRN - GRN =	7.012V ±2%
DCR	@ 20°C, WHT - BLK =	7.384 Ω ±20%
	@ 20°C, RED - RED =	339.5 Ω ±20%
	@ 20°C, YEL - YEL =	0.430 Ω ±20%
	@ 20°C, GRN - GRN =	0.074 Ω ±20%
HIPOT	PRIMARY - SECONDARY	2000V, 60Hz, 1 SEC

REV.#	REVISION	DATE	HAMMOND MANUFACTURING™			
0	RELEASED.	C.I. 11/07/12	ELECTRONIC DIVISION 52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5			
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: POWER TRANSFORMER	DWG. NO. 270CX
			DATE: 11/07/12	APP'D. BY:		
				DIMENSIONS: IN(X) MM()		

PH # (519) 886-6181
FAX # (519) 886-9540