

HIGH TEMPERATURE MAGNETIC SENSORS

HTMC1001D HTMC1021D

APPLICATIONS*


- Down-Hole Compassing/Heading Sensing
- Replace Expensive Fluxgate Sensors
- Proximity Sensing
- Position/Angle Sensing
- Replace Hall Effect Sensors
- Signal Transformation (Isolation)
- Current Measurement

*See HMC1001/2 1021/2 Family data sheet for more information


FEATURES

- Ceramic Dip Package
- Reliable For -55 to +225°C Operation
- ± 2 Gauss Field Range (HTMC1001D)
 ± 6 Gauss Field Range (HTMC1021D)
- 1mV/V/Oersted Sensitivity (Room Temp)
- Patented On-Chip Straps Require Low Voltage Set/Reset Pulse



HTMC 1001D PINOUT / PACKAGE



HTMC 1021D PINOUT / PACKAGE



MR SENSOR CIRCUIT



Not actual size

HTMC1001/2D

SPECIFICATIONS

Characteristic	Conditions	HTMC1001D Typical	HTMC1021D Typical	Unit
Bridge Supply	Vbridge referenced to GND	5	5	Volts
Bridge Resistance*	Bridge current = 5mA	850	1100	Ω
Operating Temperature	Ambient	-55 to 225° C	-55 to 225° C	° C
Storage Temperature	Ambient, unbiased	250° C	250° C	° C
Field Range*	Full scale (FS) — total applied field	± 2	± 6	gauss
Linearity Error*	Best fit straight line (at 25° C)	± 1 gauss ± 2 gauss ± 6 gauss	0.1 1 1.6	%FS
Hysteresis Error*	3 sweeps across ± 3 gauss @ 25° C	0.05	0.08	%FS
Repeatability Error*	3 sweeps across ± 3 gauss @ 25° C	0.05	0.08	%FS
Bridge Offset*	Offset = (OUT+) - (OUT-), Field=0 gauss after Set pulse, Vbridge=5V	± 20	± 2.5	mV
Sensitivity*	At Vbridge=5V	3.2	1.0	mV/V/gauss
Resolution*	Bandwidth=10Hz, Vbridge=5V	27	85	μ gauss
Bandwidth*	Magnetic signal (lower limit = DC)	5	5	MHz
OFFSET Strap*	Measured from OFFSET+ to OFFSET-	2.5	50	Ω
OFFSET Strap Ω Tempco	TA = -55 to +225° C	3900	3900	ppm/° C
OFFSET Field*	Field applied in sensitive direction	51	4.6	mA/gauss
Set/Reset Strap*	Measured from S/R+ to S/R-	1.5	7.7	Ω
Set/Reset Current*	Current at 0.1% duty cycle, or less	3.2	0.5	Amp
Disturbing Field*	Sensitivity starts to degrade. Use S/R pulse to restore sensitivity.	3	20	gauss
Sensitivity Tempco	TA = -55 to +225° C Vbridge=5V Ibridge=5mA	-3000 -600	-3000 -600	ppm/° C
Bridge Offset Tempco	TA = -55 to +225° C Ibridge=5mA	± 300 ± 10	± 500 ± 10	ppm/° C
Resistance Tempco	Vbridge = 5V, -55 to +225° C	2500	2500	ppm/° C

*Temperature is 25°C unless otherwise specified.

Honeywell reserves the right to make changes to any products or technology herein to improve reliability, function or design. Honeywell does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights nor the rights of others.

Honeywell