







Belegungsplan
Loading-Plan

Schirm Shield	
1	Gelb Yellow
2	Orange Orange
3	Weiß White
6	Blau Blue



Kodierstiftkammern 2x
Coding-key-chambers 2x



Übertragungseigenschaften nach
ISO/IEC 11801:2002: Class D
Schutzart: IP67/65
Temperaturbereich: -40°C ... +70°C
Transmission properties in accordance
with ISO/IEC 11801:2002: Class D
Protection level: IP67/65
Temperature range: -40°C ... +70°C

4xAWG 22/7 schleppfähig/trailing	09 45 715 0061	100 m
4xAWG 22/7 schleppfähig/trailing	09 45 715 0056	50 m
4xAWG 22/7 schleppfähig/trailing	09 45 715 0053	20 m
4xAWG 22/7 schleppfähig/trailing	09 45 715 0051	10 m
4xAWG 22/7 schleppfähig/trailing	09 45 715 0027	5 m
4xAWG 22/7 schleppfähig/trailing	09 45 715 0025	3 m
4xAWG 22/7 schleppfähig/trailing	09 45 715 0023	1,5 m
4xAWG 22/7 flexibel/stranded	09 45 715 1183	100 m
4xAWG 22/7 flexibel/stranded	09 45 715 1178	50 m
4xAWG 22/7 flexibel/stranded	09 45 715 1175	20 m
4xAWG 22/7 flexibel/stranded	09 45 715 1173	10 m
4xAWG 22/7 flexibel/stranded	09 45 715 1168	5 m
4xAWG 22/7 flexibel/stranded	09 45 715 1166	3 m
4xAWG 22/7 flexibel/stranded	09 45 715 1164	1,5 m
4xAWG 22/1 massiv/solid	09 45 715 1161	100 m
4xAWG 22/1 massiv/solid	09 45 715 1156	50 m
4xAWG 22/1 massiv/solid	09 45 715 1153	20 m
4xAWG 22/1 massiv/solid	09 45 715 1151	10 m
4xAWG 22/1 massiv/solid	09 45 715 1127	5 m
4xAWG 22/1 massiv/solid	09 45 715 1125	3 m
4xAWG 22/1 massiv/solid	09 45 715 1123	1,5 m
massiv / flexibel solid / stranded	Bestell-Nr. Part-No.	Maß a Dim. a

			All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances		
				Dat.	Name	Maßstab/Scale /	RJ1 Kabel AWG 22, IP67/65 RJ1 Cable AWG 22, IP67/65 2x RJ45, Metal, Data 3A				
			Detail.	28.05.03	Wae						
32429	26.11.04	Wie	Insp.	28.05.03	VSo						
32201	24.08.04	Wie	Stand.								
32089	28.06.04	Wie	HARTING Electronics GmbH & Co. KG				TB 09 45 715 1123			Blatt/ page /	
31013			D-32339 ESPELKAMP								
Mod.	Dat.	Name					Sub.				