Honeywell

# MICRO SWITCH™ Hazardous Area Switches

**LSX Series**

Datasheet

# MICRO SWITCH™ LSX Series Hazardous Area Limit Switches

MICRO SWITCH™ LSX hazardous area switches are designed for use in adverse environments. They are approved for use in hazardous locations and NEMA classified atmospheres because their rugged housings have integral flame paths. These flame paths force internal expanding gases to cool below external atmosphere ignition temperatures before they leave the housing. The LSX also features tracking interchangeability with MICRO SWITCH™ BX Series Hazardous Area switches. An optional mounting plate provides the same tracking and mounting as the standard HDLS Series (heavy-duty limit switch).

The majority of HDLS operating heads and circuitry options are available for the LSX Series. The rotary actuated LSX series products are designed for use with levers that have non-sparking actuators due to the potentially hazardous environment. The other styles of LSX Series switches which are the plunger actuated and wobble actuated products incorporate an integral non-sparking actuator.

## *What makes our switches better?*

- Industry-leading breadth of product
- Weather sealed to NEMA 1, 3, 4, 6, 13
  Explosion proof to NEMA 7 (Class 1, Division 1 & 2, Groups B, C, D), NEMA 9 (Class 2, Division 1 & 2, Groups E, F, G)
- Extensive variety of actuation heads and multiple non-sparking actuators
- All metal drive train that offers consistent operating characteristics through a broad temperature range. Also lasts longer (without need for frequent adjustment) than drive trains with plastic parts

SAFE • RELIABLE
EXPLOSION PROOF • WEATHER SEALED

# Features and Benefits

### DESIGN FLEXIBILITY

MICRO SWITCH™ LSX limit switches' field adjustability (CW-CCW operation, rotatable operating head) assists in matching the switch to the application. Available with momentary, maintained, sequential, or center neutral action.

## *All-metal drive train for consistent operation*

### UNIQUE DESIGN FEATURES

The head design is keyed for more **secure head-to-body retention** with the head indexable in any one of four positions 90° apart. Captive mounting screws in the heads help prevent the loss of screws during replacement or repositioning of the head. Self-lifting pressure plate terminals **save wiring time**.

## *Industry-leading breadth of products*

### WITHSTANDS MANY CAUSTIC ENVIRONMENTS

**A die-cast zinc head** and aluminum body make the LSX suitable for indoor and outdoor applications. A **diaphragm seal** between the head and body is designed to provide an extra measure of protection. Switches remain functional when exposed to many severe environments and caustic chemicals.

### OPTIONAL SEALS

Standard seals are suitable for most applications, but **optional fluorocarbon or fluorosilicone seals** are available for many harsh chemical, high or low temperature environments.

### DESIGNED TO CONTROL LOW-VOLTAGE DC APPLICATIONS

Hazardous area switches are available with a choice of **silver or gold-plated contacts** to handle a variety of electrical load requirements from low energy to power-duty control.

# Potential Applications

## GRAIN ELEVATORS

Monitors plugged grain conveyors, slide gate position, diverter valves, and leg positions

## CONTROL VALVES AND ACTUATORS

Senses the “on” or “off” position of the valve

## ON-SHORE DRILLING

Detects end of travel positions for extend and retract operations of drilling equipment

## PIPELINES

Monitors pig position and resulting pipeline health

## PETROCHEMICAL AND CHEMICAL PLANTS

Monitors the position of control valves, doors, and gates

## WATER TREATMENT PLANTS

Detects control valve position

## PAINT BOOTHS

Door interlocks for sliding or hinged gates or doors

## HAZARDOUS WASTE HANDLING

Often used as a valve position monitor

# MICRO SWITCH™ Hazardous Area Limit Switches

**Figure 1. MICRO SWITCH™ LSX SERIES FEATURES AND OPTIONS**



**Figure 2. MICRO SWITCH™ LSX SERIES NOMENCLATURE**

**LSX** **J** **3K** – **7A**

| Switch Type | Head Style | Circuitry and Conduit Connection | Modification Code | Actuator Options |
|---|---|---|---|---|
| **LSX** Series Hazardous Area Switch | **A** Side rotary; momentary | **3E** 1NO/1NC, gold contacts, 1/2-14NPT | **1** CW rotation | **1** Fixed roller, 1.5 in radius |
| | **B** Top rotary; momentary | **3K** 1NO/1NC, 1/2-14NPT | **2** CCW rotation | **1A** Fixed 0.75 in x 0.25 in nylon roller, 1.5 in radius |
| | **C** Top plunger, plain | **3N** SPNC direct acting, 1/2-14NPT | **3** Head assembled with actuator to right side | **1C** Fixed 0.75 in x 0.25 in nylon roller, 1.5 in radius |
| | **D** Top plunger, roller | **4K** 1NO/1NC, 3/4-14NPT | **4** Head assembled with actuator to left side | **2** Adjustable, rollerless |
| | **E** Side plunger plain; momentary | **4L** 2NO/2NC, 3/4-14NPT | **5** Head assembled with actuator toward mounting surface | **2A** Adjustable, 0.75 in x 0.25 in nylon roller |
| | **F** Side plunger roller; momentary | **4M** 2NO/2NC, 3/4-14NPT, sequential operation | **6** Roller perpendicular to mounting surface | **2C** Adjustable, 0.75 in x 0.25 in nylon roller |
| | **H** Side rotary, momentary; low PT, low torque | **4N** 2NO/2NC, 3/4-14NPT, center neutral | **8** Roller on side plunger in vertical position | **2J** Adjustable, 1.0 in x 0.5 in nylon roller |
| | **J** Wobble stick | **4S** 2NO/2NC, gold contacts, 3/4-14NPT | | **2K** Adjustable, 0.5 in x 0.25 in nylon roller |
| | **K** Whisker | **4T** 2NO/2NC, gold contacts, 3/4-14NPT, sequential operation | | **3E** Yoke, 0.75 in x 0.25 in nylon roller |
| | **L** Side rotary; sequential | **4U** 2NO/2NC, gold contacts, 3/4-14NPT, center neutral | | **3M** Yoke, 0.75 in x 0.25 in nylon roller |
| | **M** Side rotary; central neutral | **7L** 2NO/2NC, 1/2-14NPT | | **3S** Yoke, 0.75 in x 0.25 in nylon roller, same side |
| | **N** Side rotary; maintained | **7M** 2NO/2NC, 1/2-14NPT, sequential operation | | **4** Hub only |
| | **P** Side rotary, momentary; low PT and DT | **7N** 2NO/2NC, 1/2-14NPT, center neutral | | **4M** Hub rod, aluminum |
| | **R** Side rotary, momentary; low torque | **7S** 2NO/2NC, gold contacts, 1/2-14NPT | | **5** Offset, rollerless |
| | **U** Side rotary, low pre-travel | **7T** 2NO/2NC, gold contacts,1/2-14NPT, sequential operation | | **5A** Offset, 0.75 in x 0.25 in nylon roller |
| | **V** Top plunger, adjustable | **7U** 2NO/2NC, gold contacts,1/2-14NPT, center neutral | | **5C** Offset, 0.75 in x 0.25 in nylon roller |
| | **W** Side plunger, adjustable | | | **7A** Plastic wobble stick |
| | | | | **8A** Whisker, 5.5 in |
| | | | | **9A** Fixed, 0.75 in x 0.25 in nylon roller, open, 1.33 in radius |
| | | | | **9C** Fixed, 0.75 in x 0.25 in nylon roller, closed, 1.33 in radius |

*Not all combinations available. Please contact Honeywell for assistance.*

To order high temperature versions, insert the additional letters **Y** and **C** in the appropriate places in the standard catalog listing, as shown below:

| | |
|---|---|
| **LSXA3K** | standard, side-rotary plug-in switch |
| **LSXYAC3K** | completely FC-sealed version of LSXA3K |

To order low temperature versions, insert the additional letters **Y** and **B** in the appropriate places in the standard catalog listing, as shown below:

| | |
|---|---|
| **LSXA3K** | standard, side-rotary plug-in switch |
| **LSXYAB3K** | low-temperature version of LSXA3K |

*For more details, please see page 8.*

# MICRO SWITCH™ Hazardous Area Limit Switches

**Table 1. Specifications**

| Characteristic | Parameter |
|---|---|
| Product type | MICRO SWITCH™ hazardous area limit switches |
| Actuators | side pin plunger<br>side rotary<br>top pin plunger - adjustable<br>wobble - cat whisker<br>side pin plunger - adjustable<br>side rotary maintained<br>top roller plunger<br>wobble - plastic rod<br>side roller plunger<br>top pin plunger<br>top rotary |
| Circuitry | 1NC 1NO SPDT snap action, double break<br>2NC 2NO DPDT snap action, double break<br>2NC 2NO DPDT snap action, double break, sequential<br>2NC 2NO DPDT snap action, double break, center neutral |
| Electrical | 10 A thermal<br>single and double pole: AC15 A600, AC15 B600; DC13 R300 (see table on page 8) |
| Housing material | zinc head, aluminum body |
| Termination types | 0.5 in - 14 NPT conduit<br>0.75 in - 14 NPT conduit |
| Housing type | LSX non-plug-in |
| Agency approvals and standards | UL, CSA |
| Sealing | NEMA 1, 3, 4, 6, 13 |
| Hazardous area designations | NEMA 7 (Class 1, Division 1 & 2, Groups B, C, D), NEMA 9 (Class 2, Division 1 & 2, Groups E, F, G) |
| Operating temperature* | standard: -12 °C to 121 °C [10 °F to 250 °F]<br>optional: -40 °C to 121 °C [-40 °F to 250 °F] |
| UNSPSC code | 39122213 |
| UNSPSC commodity | 39122213 Limit Switch |

* Reference operating head styles on page 9 and 10 for exceptions.

# LSX Series

## MICRO SWITCH™ LSX SERIES ELECTRICAL RATINGS: 10 A CONTINUOUS CARRY ac VOLTS; PILOT DUTY: AC15, A600

| Electrical Rating | Circuitry | Vac | Amps at 0.35 Power Factor Make | Amps at 0.35 Power Factor Break |
|---|---|---|---|---|
| AC15, A600 | SPDT DPDT | 120 | 60 | 6 |
| | | 240 | 30 | 3 |
| | | 480 | 15 | 1.5 |
| | | 600 | 12 | 1.2 |

## MICRO SWITCH™ LSX SERIES ELECTRICAL RATINGS: dc VOLTS; PILOT DUTY: DC13, R300

| Electrical Rating | Circuitry | Vdc | Make & Break Amps Inductive | Make & Break Amps Resistive |
|---|---|---|---|---|
| DC13, R300 | SPDT DPDT | 120 | 0.25 | 0.8 |
| | | 240 | 0.15 | 0.4 |

MICRO SWITCH™ LSX limit switches are capable of the following low voltage dc loads

| Circuitry | Vdc | Amps Inductive | Amps Resistive |
|---|---|---|---|
| SPDT, DPDT | 24 | 10 | 10 |

## SWITCH CONTACT STYLES, DOUBLE BREAK

| SPDT (1NC/1NO) | DPDT (2NC/2NO) |
|---|---|
|   |   |

**Center Neutral (SPDT each direction)**
**Pole 1 operates CCW; Pole 2 operates CW**




NOTE: Same polarity each pole

## TEMPERATURE LIMITS

| | Standard LSX | | | | Low Temperature LSX (Fluorosilicone Sealed): Y_B | | | | High Temperature LSX (Fluorocarbon Sealed)*: Y_C | | |
|---|---|---|---|---|---|---|---|---|---|---|---|
| | Low Limit | | High Limit | | Low Limit | | High Limit | | Low Limit | | High Limit |
| | -12 °C [10 °F] | -1 °C [30 °F] | 93 °C [200 °F] | 121 °C [250 °F] | -40 °C [-40°F] | -29 °C [-20 °F] | 93 °C [200 °F] | 121 °C [250 °F] | -12 °C [10 °F] | -1 °C [30 °F] | 121 °C [250 °F] |
| LSXA - Side Rotary Momentary | • | | | • | • | | | • | • | | • |
| LSXB - Top Rotary | | • | | • | | • | | • | | • | • |
| LSXC - Top Plain Plunger | • | | • | | • | | • | | • | | • |
| LSXD - Top Roller Plunger | • | | • | | • | | • | | • | | • |
| LSXE - Side Plain Plunger | • | | • | | • | | • | | • | | • |
| LSXF - Side Roller Plunger | • | | • | | • | | • | | • | | • |
| LSXH - Side Rotary, Low Diff, Low Torque | | • | | • | | • | | • | | • | • |
| LSXJ - Wobble Stick | • | | • | | • | | | • | • | | • |
| LSXK - Cat Whisker | • | | • | | | • | | • | • | | • |
| LSXL - Side Rotary, Sequence | • | | | • | • | | | • | • | | • |
| LSXM - Side Rotary, Center Neutral | | • | | • | • | | | • | | • | • |
| LSXN - Side Rotary, Maintained | | • | | • | | • | | • | | • | • |
| LSXP - Side Rotary, Low Diff | • | | | • | • | | | • | • | | • |
| LSXR - Side Rotary, Low Torque | | • | | • | | • | | • | | • | • |
| LSXU - Side Rotary, 5º Low Pretravel | • | | | • | | | | | | | • |
| LSXV - Top Adjustable Plunger | • | | • | | • | | • | | • | | • |
| LSXW - Side Adjustable Plunger | • | | • | | • | | • | | • | | • |

* For LSX application wherein the upper temperature limit is normally above 93 °C [200 °F], extended switch life can be obtained by using completely fluorocarbon-sealed switches rather than standard LSX.

# MICRO SWITCH™ Hazardous Area Limit Switches

## SPECIAL OPTIONS

### HIGH TEMPERATURE/CHEMICAL RESISTANT SWITCHES

Completely fluorocarbon (FC)-sealed switches have a full FC body gasket covering the switch cavity. Rotary types have an extra FC seal on the operating shaft, while plunger versions have FC boot seals. They are designed for use in applications where the environment includes fire-resistant synthetic fluids. In addition, the FC-sealed switches may be used with such industrial fluids as Cellulube, Fyrquell, Houghto-Safe, Pydraul, and other special cutting and hydraulic fluids. The additional FC seals also promote extended operating life for rotary-actuated LSX switches in applications where the temperatures are normally -12 °C to 121 °C [10 °F to 250 °F].

To order, insert the additional letters **Y** and **C** in the appropriate places in the standard catalog listing, as shown below:

| | |
|---|---|
| **LSXA3K** | standard, side-rotary plug-in switch |
| **LSXYAC3K** | completely FC-sealed version of LSXA3K |

### LOW TEMPERATURE SWITCHES

All forms of LSX limit switches are also available in low-temperature construction. Design features include fluorosilicone diaphragm, shaft seals, and external boot seal (where applicable).

To order, insert the additional letters **Y** and **B** in the appropriate places in the standard catalog listing, as shown below:

| | |
|---|---|
| **LSXA3K** | standard, side-rotary plug-in switch |
| **LSXYAB3K** | low-temperature version of LSXA3K |

## MICRO SWITCH™ LSX SERIES OPERATING HEADS

**SIDE ROTARY:** Heads may be positioned in any one of four positions, 90° increments. All are momentary action except maintained head (LSXN Series).

**LSXA - Standard:** 60° minimum overtravel, 15° maximum pretravel, 5° (single pole) and 7° (double pole) maximum differential travel.

**LSXR - Low operating torque:** 60° minimum overtravel, 15° maximum pretravel, 0.19 Nm [1.7 in-lb] maximum operating torque.

**LSXN - Maintained contact:** Maintained on counterclockwise rotation and reset on clockwise rotation, and vice versa.

**LSXP - Low differential:** 68° minimum overtravel, 9° maximum pretravel, 3° (single pole) and 4° (double pole) maximum differential travel.

**LSXH - Low torque, low differential travel:** 68° minimum overtravel. Features low operating torque and narrow differential travel.

**LSXL - Sequence action:** 48° minimum overtravel. Delayed action between operation of two poles.

**LSXM - Center neutral:** 57° minimum overtravel. One pole operates on the clockwise rotation, and the other pole on the counterclockwise rotation.

**LSXU - Low pretravel:** 5° max. pretravel, 70° min. overtravel.

**TOP ROTARY:** Available levers provide greater versatility. Heads may be positioned in any one of four positions, 90° increments. All are momentary action.

**LSXB:** With 100° minimum overtravel. Various levers that fit side rotary shafts may be used on the top rotary shaft. Switch is suitable for use when increased overtravel is required.

# LSX Series

## MICRO SWITCH™ LSX SERIES OPERATING HEADS

**TOP PLUNGERS:** Available with 4,83 mm [0.19 in] minimum overtravel. Top pin plungers are offered in pin plunger, an adjustable plunger, and a roller plunger.

| | |
|---|---|
| | **LSXC - Top pin plunger:** A copper alloy plunger for in-line actuating motion. Oil-tight seals on plunger and between the operating head and housing are designed to keep out coolant, dust, and chips. Momentary action. |
| | **LSXD - Top roller plunger:** A copper alloy roller plunger is adjustable to 90° angles to accept cam or slide operation from any of two directions. Boot seal on the plunger. Momentary action. |
| | **LSXV - Adjustable top pin plunger:** A copper alloy adjustable plunger is designed to simplify the application and decreases installation time. The operating points of the switch can be adjusted from 65,66 mm to 72,0 mm [2.585 in to 2.535 in]. Seals are the same as the pin plunger. Momentary action. |

**WOBBLE LEVER ACTUATING HEADS:** Heads come with either a Delrin® plastic rod or a copper alloy cat whisker. Any movement of the lever (except pull) will actuate the switch.

| | |
|---|---|
| | |
| **LSXJ - Plastic rod:** Recommended where possible scratching or marring by the actuator is to be avoided. | **LSXK - Cat whisker:** Copper alloy actuator designed for low operating force applications. |

**SIDE PLUNGERS:** Made of non-sparking copper alloy. Available with 4,83 mm [0.19 in] minimum overtravel. Side plungers are offered in plain plunger, an adjustable pin plunger, and a roller plunger.

| | |
|---|---|
| | **LSXE - Side pin plunger:** A copper alloy plunger for actuating motion inline with the plunger travel. Actuating head may be rotated in any of four positions, 90° apart. A boot seal on the plunger and a gasket seal between the head and housing is designed to keep out coolant, dust, and chips. Momentary action. |
| | **LSXF - Side roller plunger:** A copper alloy roller plunger fits close quarters under cams and slides. The head may be rotated in any of four positions, 90° apart. The roller can be turned vertical or horizontal to the switch. Boot seal on plunger. Momentary action. |
| | **LSXW - Adjustable side pin plunger:** Has the same features of the side plain plunger plus the means to adjust the operating points of the switch from 41 mm to 47,4 mm [1.615 in to 1.865 in]. Momentary action. |

# MICRO SWITCH™ Hazardous Area Limit Switches

## SIDE ROTARY • MICRO SWITCH™ LSX SERIES ORDER GUIDE/RECOMMENDED LISTINGS

| | Standard (LSXA) | | Low Differential (LSXP) | | Low Torque (LSXR) | |
|---|---|---|---|---|---|---|
| **Description** | Standard | | Low differential travel | | Low operating torque | |
| | **SPDT** | **DPDT** | **SPDT** | **DPDT** | **SPDT** | **DPDT** |
| **Contact closed ■**<br>**Contact open □** |  |  |  |  |  |  |
| **Pretravel** | 15° max. | | 9° max. | | 15° max. | |
| **Differential travel** | 5° max. | 7° max. | 3° max. | 4° max. | 5° max. | 7° max. |
| **Overtravel** | 60° min. | | 66° min. | | 60° min. | |
| **Operating torque** | 0,45 Nm [4 in-lb] max. | | 0,45 Nm [4 in-lb] max. | | 0,19 Nm [1.7 in-lb] max. | |
| **Action** | Momentary, CW, & CCW (Spring return) | | | | | |
| **Operating temperature range[2]** | -12 °C to 121 °C [10 °F to 250 °F] | | | | -1 °C to 121 °C [30 °F to 250 °F] | |

| | | Contacts | Conduit (NPT) | | | |
|---|---|---|---|---|---|---|
| SPDT |  | Silver | 0.5 in | **LSXA3K** | **LSXP3K** | **LSXR3K** |
| | | Silver | 0.75 in | **LSXA4K** | **LSXP4K** | **LSXR4K** |
| | | Gold[1] | 0.5 in | **LSXA3E** | **LSXP3E** | **LSXR3E** |
| DPDT |  | Silver | 0.5 in | **LSXA7L** | **LSXP7L** | **LSXR7L** |
| | | Silver | 0.75 in | **LSXA4L** | **LSXP4L** | **LSXR4L** |
| | | Gold[1] | 0.75 in | **LSXA4S** | **LSXP4S** | **LSXR4S** |

[1] Gold-plated contacts
[2] Completely fluorocarbon sealed switches are preferred for use in temperatures above 93 °C [200 °F]
For low temperature or high temperature versions, see page 9.

# LSX Series

## SIDE ROTARY • MICRO SWITCH™ LSX SERIES ORDER GUIDE/RECOMMENDED LISTINGS

| | Maintained Contact (LSXN) | | Low Torque (LSXH) | |
|---|---|---|---|---|
| **Description** | Maintained, 2-position Std. | | Momentary, low torque | |
| | **SPDT** | **DPDT** | **SPDT** | **DPDT** |
| **Contact closed ■**<br>**Contact open □** |  |  |  |  |
| **Pretravel** | 65° max. | | 9° max. | |
| **Differential travel** | 40° max. | | 3° max. | 4° max. |
| **Overtravel** | 20° min. | | 66° min. | |
| **Operating torque** | 0,45 Nm [4 in-lb] max. | | 0,19 Nm [1.7 in-lb] max. | |
| **Action** | Maintained | | Momentary, CW, & CCW (Spring return) | |
| **Operating temp. range[2]** | -1 °C to 121 °C [30 °F to 250 °F] (for low temp or high temp versions, see page 9) | | | |

| | | Contacts | Conduit (NPT) | | |
|---|---|---|---|---|---|
| SPDT |  | Silver | 0.5 in | **LSXN3K** | **LSXH3K** |
| | | Silver | 0.75 in | **LSXN4K** | **LSXH4K** |
| | | Gold[1] | 0.5 in | **LSXN3E** | **LSXH3E** |
| DPDT |  | Silver | 0.5 in | **LSXN7L** | **LSXH7L** |
| | | Silver | 0.75 in | **LSXN4L** | **LSXH4L** |
| | | Gold[1] | 0.75 in | **LSXN4S** | **LSXH4S** |

[1] Gold-plated contacts
[2] Completely fluorocarbon sealed switches are preferred for use in temperatures above 93 °C [200 °F]
For low temperature or high temperature versions, see page 9.

# MICRO SWITCH™ Hazardous Area Limit Switches

## SIDE ROTARY • MICRO SWITCH™ LSX SERIES ORDER GUIDE/RECOMMENDED LISTINGS

| | Center Neutral (LSXM) | Sequence Action (LSXL) |
|---|---|---|
| **Description** | Center Neutral (Pole 1 operates CCW; Pole 2 operates CW) | Sequential (Pole 1 operates before Pole 2, either CW, CCW, or both) |
| **Contact closed ■ Contact open □** | **DPDT** | **DPDT** |
| **Pretravel** | 18° max. | 1st: 15°; 2nd: additional 10° |
| **Differential travel** | 10° max. | each pole: 5° |
| **Overtravel** | 57° min. | 48° min. |
| **Operating torque** | 0,45 Nm [4 in-lb] max. | 0,45 Nm [4 in-lb] max. |
| **Action** | CW & CCW (Spring return) | |
| **Operating temp. range[2]** | -1 °C to 121 °C [30 °F to 250 °F] | -12 °C to 121 °C [10 °F to 250 °F] |

| | | Contacts | Conduit (NPT) | | |
|---|---|---|---|---|---|
| DPDT |  | Silver | 0.5 in | **LSXM7N** | **LSXL7M** |
| | | Silver | 0.75 in | **LSXM4N** | **LSXL4M** |
| | | Gold[1] | 0.5 in | **LSXM7U** | **LSXL7T** |
| | | Gold[1] | 0.75 in | **LSXM4U** | **LSXL4T** |

[1] Gold-plated contacts
[2] Completely fluorocarbon sealed switches are preferred for use in temperatures above 93 °C [200 °F]
For low temperature or high temperature versions, see page 9.

## TOP ROTARY • MICRO SWITCH™ LSX SERIES ORDER GUIDE/RECOMMENDED LISTINGS

| | Standard (LSXB) | |
|---|---|---|
| **Description** | Standard | |
| | **SPDT** | **DPDT** |
| **Contact closed ■**<br>**Contact open □** | Snap Action<br>1NO/1NC<br>  | Snap Action<br>2NO/2NC<br>  |
| **Pretravel** | 25° max. | |
| **Differential travel** | 10° max. | 12° max. |
| **Overtravel** | 110° min. | |
| **Operating torque** | 0,25 Nm [2.5 in-lb] | |
| **Action** | Momentary, CW, & CCW (Spring return) | |
| **Operating temp. range[1]** | -1 °C to 121 °C [30 °F to 250 °F] (for low temp or high temp versions, see page 9) | |

| | | Contacts | Conduit (NPT) | | |
|---|---|---|---|---|---|
| SPDT |  | Silver | 0.5 in | **LSXB3K** | – |
| | | Silver | 0.75 in | – | **LSXB4L** |

[1] Completely fluorocarbon sealed switches are preferred for use in temperatures above 93 °C [200 °F]
For low temperature or high temperature versions, see page 9.

# MICRO SWITCH™ Hazardous Area Limit Switches

**Table 2. Common levers for use with MICRO SWITCH™ LSX Rotary Switches***

Levers for use with side-rotary-actuated switches are available in a wide choice of sizes and materials. The most common listings are shown below. Rollers may be on either side of the lever to best match the external actuating mechanism.

| | | | | | | |
|---|---|---|---|---|---|---|
| | | | | | | |
| **Fixed lever, nylon roller**<br>**LSZ51A -** front mount roller<br>**LSZ51C -** back mount roller | | **Short fixed lever, nylon roller**<br>**LSZ59A -** front mount roller<br>**LSZ59C -** back mount roller | | | **Offset lever, nylon roller**<br>**LSZ55A -** back mount roller<br>**LSZ55C -** front mount roller | |
| | | | | | | |
| **One-way lever, nylon roller**<br>**LSZ60A -** front mount roller | | **Yoke lever, nylon rollers**<br>**LSZ53A -** front/back mount rollers | | | | |
| | | | | | | |
| **Adjustable lever, nylon roller**<br>**LSZ52A -** back mount roller<br>**LSZ52C -** front mount roller | **LSZ52J**<br>adjustable lever, nylon roller<br>25,4 mm [1 in] | **LSZ52K**<br>adjustable lever, nylon roller<br>38,1 [1.5 in] | **LSZ54M**<br>aluminum rod<br>140 mm [5.5 in] | **LSZ61**<br>loop<br>152 mm [6 in] | **LSZ67CA****<br>Plastic conveyor roller | **LSZ68**<br>rod with spring<br>305 mm [12 in] |

* Non-sparking rollers and actuators must be used in hazardous areas.
** May require orientation of switch and lever to enable gravity to help restore switch's free position.

# LSX Series

### Table 3. LSX Series Lever Order Guide

| | Catalog Listing | Material | Roller Dia. mm [in] | Roller Width mm [in] | Roller Mounting |
|---|---|---|---|---|---|
| **Fixed 38,1 mm [1.5 in] radius** | | | | | |
| | LSZ51 | Rollerless | n/a | n/a | n/a |
| | LSZ51A | Nylon | 19 [0.75] | 6,35 [0.25] | Front |
| | LSZ51C | Nylon | 19 [0.75] | 6,35 [0.25] | Back |
| | LSZ51F | Nylon | 25,4 [1.0] | 12,7 [0.50] | Front |
| | LSZ51G | Nylon | 38,1 [1.5] | 6,35 [0.25] | Front |
| | LSZ51J | Nylon | 25,4 [1.0] | 12,7 [0.50] | Back |
| | LSZ51M | Nylon | 19 [0.75] | 31,7 [1.25] | Back |
| | LSZ51P | Nylon | 19 [0.75] | 12,7 [0.50] | Front |
| | LS2Z51A (sst) | Nylon | 19 [0.75] | 6,35 [0.25] | Front |
| | LS2Z51C (sst) | Nylon | 19 [0.75] | 6,35 [0.25] | Back |
| | LS2Z51E (sst) | Copper alloy | 19 [0.75] | 6,35 [0.25] | Front |
| | LS2Z51F (sst) | Copper alloy | 19 [0.75] | 6,35 [0.25] | Back |
| **Adjustable 38,1 mm [1.5 in] to 88,9 mm [3.5 in] radius** | | | | | |
| | LSZ52 | Rollerless | n/a | n/a | n/a |
| | LSZ52A | Nylon | 19 [0.75] | 6,35 [0.25] | Back |
| | LSZ52C | Nylon | 19 [0.75] | 6,35 [0.25] | Front |
| | LSZ52E | Nylon | 19 [0.75] | 33,0 [1.30] | Front |
| | LSZ52J | Nylon | 25,4 [1.0] | 12,7 [0.50] | Front |
| | LSZ52K | Nylon | 38,1 [1.5] | 6,35 [0.25] | Front |
| | LSZ52M | Nylon | 50,8 [2.0] | 6,35 [0.25] | Front |
| | LSZ52N | Nylon | 19 [0.75] | 12,7 [0.50] | Front |
| | LS2Z52A (sst) | Nylon | 19 [0.75] | 6,35 [0.25] | Front |
| | LS2Z52C (sst) | Nylon | 19 [0.75] | 6,35 [0.25] | Back |
| | LS2Z52E (sst) | Copper alloy | 19 [0.75] | 6,35 [0.25] | Front |
| | LS2Z52F (sst) | Copper alloy | 19 [0.75] | 6,35 [0.25] | Back |
| **Yoke – 38,1 mm [1.5 in] radius** | | | | | |
| | LSZ53A | Nylon | 19 [0.75] | 6,35 [0.25] | Front/Back |
| | LSZ53E | Nylon | 19 [0.75] | 6,35 [0.25] | Back/Front |
| | LSZ53M | Nylon | 19 [0.75] | 31,7 [1.25] | Back/Front |
| | LSZ53S | Nylon | 19 [0.75] | 6,35 [0.25] | Back/Back |
| **Rod** | | | | | |
| | LSZ54 | Hub only | n/a | n/a | n/a |
| | LSZ54M | Alum, 140 mm [5.5 in] | Ø 3,2 [Ø 0.125] | n/a | n/a |
| | LSZ54N | Stainless, 330 mm [13 in] | Ø 3,2 [Ø 0.125] | n/a | n/a |
| | LSZ54P | Plastic rod, 305 mm [12 in] | Ø6,85 [Ø 0.27] | n/a | n/a |
| | LSZ54W | Plastic rod, 183 mm [7.2 in] | Ø6,85 [Ø 0.27] | n/a | n/a |
| **Offset – 38,1 mm [1.5 in] radius** | | | | | |
| | LSZ55 | Rollerless | n/a | n/a | n/a |
| | LSZ55A | Nylon | 19 [0.75] | 6,35 [0.25] | Back |
| | LSZ55C | Nylon | 19 [0.75] | 6,35 [0.25] | Front |
| | LSZ55E | Nylon | 19 [0.75] | 12,7 [0.50] | Front |
| | LSZ55K | Nylon | 38,1 [1.5] | 6,35 [0.25] | Front |

| | Catalog Listing | Material | Roller Dia. mm [in] | Roller Width mm [in] | Roller Mounting |
|---|---|---|---|---|---|
| **Short fixed - 33,02 mm [1.3 in] radius** | | | | | |
| | LSZ59A | Nylon | 19 [0.75] | 6,35 [0.25] | Front |
| | LSZ59C | Nylon | 19 [0.75] | 6,35 [0.25] | Back |
| **One-way roller lever** | | | | | |
| | LSZ60A | Nylon | 19 [0.75] | 6,35 [0.25] | Front |
| **Flexible loop** | | | | | |
| | LSZ61 | Ø 4,8 [Ø 0.19 ] Nylatron | 152 mm [6 in] flexible loop | | |
| | LSZ618 | Ø 4,8 [Ø 0.19 ] Nylatron | 241 mm [9.5 in] flexible loop | | |
| | LSZ54 | Hub only | n/a | n/a | n/a |
| **Spring rod** | | | | | |
| | LSZ68 | Delrin rod, 305 mm [12 in] | Ø 6,35 [0.25] | n/a | n/a |
| | LSZ617 | Delrin rod, 406 mm [16 in] | Ø 6,35 [0.25] | n/a | n/a |
| | LSZ686 | Delrin rod, 152 mm [6 in] | Ø 6,35 [0.25] | n/a | n/a |
| **Rubber roller levers** | | | | | |
| | LSZ51Y 38,1 [1.5] radius (standard) | Rubber | 50 [2.0] | 12,7 [0.5] | front |
| | LSZ55Y 38,1 [1.5] radius (offset) | Rubber | 50 [2.0] | 12,7 [0.5] | front |
| | LSZ52Y 38,1 to 89 [1.5 to 3.5] radius (adjustable) | Rubber | 50 [2.0] | 12,7 [0.5] | front |
| **Plastic roller levers** | | | | | |
| | LSZ67AA (conveyor)* | Plastic | 38,1 [1.5] | 96,5 [3.8] | n/a |

* May require orientation of switch and lever to enable gravity to help restore switch to free position.

# MICRO SWITCH™ Hazardous Area Limit Switches

## TOP PLUNGER • MICRO SWITCH™ LSX SERIES ORDER GUIDE/RECOMMENDED LISTINGS

All top plungers are momentary action.

| | Plain (LSXC) | | Roller (LSXD) | | Adjustable (LSXV) | |
|---|---|---|---|---|---|---|
| | | | | | | |
| **Description** | Top plain plunger for in-line operating motion | | Top roller plunger – can be set at 90° increments to accept cam or slide actuation | | Adjustable top plain plunger simplifies installation since operating point can be adjusted from 65,66 mm min.; 72,0 mm max. [2.585 in min; 2.835 in max.] | |
| | **SPDT** | **DPDT** | **SPDT** | **DPDT** | **SPDT** | **DPDT** |
| **Contact closed ■<br>Contact open □** |  |  |  |  |  |  |
| **Pretravel** | 1,78 mm [0.07 in] | | | | | |
| **Differential travel** | 0,38 mm [0.015 in] | 0,51 mm [0.02 in] | 0,38 mm [0.015 in] | 0,51 mm [0.02 in] | 0,38 mm [0.015 in] | 0,51 mm [0.02 in] |
| **Overtravel** | 4,83 mm [0.19 in] | | | | | |
| **Operting force** | 17,8 N [4 lb] max. | | | | | |
| **Operating point** | 58,55 mm ±0,76 mm [2.305 in ±0.030 in] | | 68,58 mm ±1,02 mm [2.70 in ±0.040 in] | | 65,66 mm min.; 72,0 mm max. [2.585 in min; 2.835 in max.] | |
| **Operating temp. range[2]** | -12 °C to 93 °C [10 °F to 200 °F] (for low temp or high temp versions, see page 9) | | | | | |

| | | Contacts | Conduit (NPT) | | | |
|---|---|---|---|---|---|---|
| SPDT |  | Silver | 0.5 in | **LSXC3K** | **LSXD3K** | **LSXV3K** |
| | | Silver | 0.75 in | **LSXC4K** | **LSXD4K** | **LSXV4K** |
| | | Gold[1] | 0.5 in | **LSXC3E** | **LSXD3E** | **LSXV3E** |
| DPDT |  | Silver | 0.5 in | **LSXC7L** | **LSXD7L** | **LSXV7L** |
| | | Silver | 0.75 in | **LSXC4L** | **LSXD4L** | **LSXV4L** |
| | | Gold[1] | 0.75 in | **LSXC4S** | **LSXD4S** | **LSXV4S** |

[1] Gold-plated contacts
[2] Completely fluorocarbon sealed switches are preferred for use in temperatures above 93 °C [200 °F]
For low temperature or high temperature versions, see page 9.

# LSX Series

## SIDE PLUNGER • MICRO SWITCH™ LSX SERIES ORDER GUIDE/RECOMMENDED LISTINGS

All side plungers are momentary action. Heads may be positioned to accept actuation from any of four directions, 90° apart.

| | Plain (LSXE) | | Roller (LSXF) | | Adjustable (LSXW) | |
|---|---|---|---|---|---|---|
| | | | | | | |
| **Description** | Side plain plunger for in-line operating motion | | Side roller plunger – can be set at 90° increments to accept cam or slide actuation | | Adjustable side plain plunger simplifies installation since operating point can be adjusted from 41 mm min.; 47,37 mm max. [1.615 in min.; 1.865 in max.] | |
| | **SPDT** | **DPDT** | **SPDT** | **DPDT** | **SPDT** | **DPDT** |
| **Contact closed ■**<br>**Contact open □** | | |  |  | | |
| **Pretravel** | 2,54 mm [0.10 in] | | | | | |
| **Differential travel** | 1,14 mm [0.045 in] | | | | | |
| **Overtravel** | 4,83 mm [0.19 in] | | | | | |
| **Operting force** | 26,7 N [6 lb] max. | | | | | |
| **Operating point** | 33,02 mm ±0,76 mm [1.300 in ±0.030 in] | | 44,07 mm ±1,02 mm [1.735 in ±0.04 in] | | 41 mm min.; 47,37 mm max. [1.615 in min.; 1.865 in max.] | |
| **Operating temp. range[2]** | -12 °C to 93 °C [10 °F to 200 °F] (for low temp or high temp versions, see page 9) | | | | | |

| | | Contacts | Conduit (NPT) | | | |
|---|---|---|---|---|---|---|
| SPDT |  | Silver | 0.5 in | **LSXE3K** | **LSXF3K** | **LSXW3K** |
| | | Silver | 0.75 in | **LSXE4K** | **LSXF4K** | **LSXW4K** |
| | | Gold[1] | 0.5 in | **LSXE3E** | **LSXF3E** | **LSXW3E** |
| DPDT |  | Silver | 0.5 in | **LSXE7L** | **LSXF7L** | **LSXW7L** |
| | | Silver | 0.75 in | **LSXE4L** | **LSXF4L** | **LSXW4L** |
| | | Gold[1] | 0.75 in | **LSXE4S** | **LSXF4S** | **LSXW4S** |

[1] Gold-plated contacts
[2] Completely fluorocarbon sealed switches are preferred for use in temperatures above 93 °C [200 °F]
For low temperature or high temperature versions, see page 9.

# MICRO SWITCH™ Hazardous Area Limit Switches

## WOBBLE • MICRO SWITCH™ LSX SERIES ORDER GUIDE/RECOMMENDED LISTINGS

LSJ1A-7A - Plastic rod | LSK1A-8A - Cat whisker

**Contact closed ■**
**Contact open □**

| | LSXJ Series 7A Actuator | | LSXK Series 8A Actuator | |
|---|---|---|---|---|
| **Description** | Delrin® plastic rod lever (wobble stick) | | Cat whisker actuator for low operating force applications | |
| | **SPDT** | **DPDT** | **SPDT** | **DPDT** |
| |  | | **-8A**  | |
| **Actuator length** | 152,4 mm [6 in] | | 139,7 mm [5.5 in] copper alloy | |
| **Pretravel** | 25,4 mm [1.0 in] | | 51,0 mm [2.0 in] | |
| **Operating force** | 2,78 Nm [10 oz] | | 1,39 Nm [5 oz] | |
| **Operating temp. range[2]** | -12 °C to 93 °C [10 °F to 200 °F] (for low temp or high temp versions, see page 9) | | | |

| | | Contacts | Conduit (NPT) | | |
|---|---|---|---|---|---|
| SPDT |  SPDT Double Break | Silver | 0.5 in | **LSXJ3K-7A** | **LSXK3K-8A** |
| | | Silver | 0.75 in | **LSXJ4K-7A** | **LSXK4K-8A** |
| | | Gold[1] | 0.5 in | **LSXJ3E-7A** | **LSXK3E-8A** |
| DPDT |  DPDT Double Break | Silver | 0.5 in | **LSXJ7L-7A** | **LSXK7L-8A** |
| | | Silver | 0.75 in | **LSXJ4L-7A** | **LSXK4L-8A** |
| | | Gold[1] | 0.75 in | **LSXJ4S-7A** | **LSXK4S-8A** |

[1] Gold-plated contacts
[2] Completely fluorocarbon sealed switches are preferred for use in temperatures above 93 °C [200 °F]
For low temperature or high temperature versions, see page 9.

## REPLACEMENT CONTACT BLOCKS

| Circuitry | Replacement Contact Block |
|---|---|
| Single pole | LSXZ3K |
| Double pole | LSXZ3L |
| Sequence or central neutral | LSXZ3M |

## REPLACEMENT HEADS FOR STANDARD LSX SWITCHES

| Switch Type | Catalog Listing/Operating Head Only |
|---|---|
| LSXA | LSXZ1A |
| LSXB | LSXZ1B |
| LSXC | LSXZ1C |
| LSXD | LSXZ1D |
| LSXE | LSXZ1E |
| LSXF | LSXZ1F |
| LSXH | LSXZ1H |
| LSXJ | LSXZ1JGA |
| LSXK | LSXZ1KHA |
| LSXL | LSXZ1L |
| LSXM | LSXZ1M |
| LSXN | LSXZ1N |
| LSXP | LSXZ1P |
| LSXR | LSXZ1R |
| LSXU | LSXZ1U |
| LSXV | LSXZ1V |
| LSXW | LSXZ1W |

## ADAPTER PLATE

Catalog listing LSXZ4022 adapter plate enables the NEMA-rated, explosion-proof LSX Series to be mounted on existing HDLS mounting holes. The LSX has a recessed back into which the adapter plate fits and mounts, using two screws (furnished)




## ASSEMBLY MODIFICATIONS

Momentary action rotary switches can be furnished in other than the normal assembled conditions. To specify modifications, add the numbers shown below to the catalog listings. Modification number suffixes are:

**1** Clockwise actuation only
**2** Counterclockwise actuation only
**3** Shaft to right of switch front
**4** Shaft to left of switch front
**5** Shaft to back of switch

**For example,**
Catalog listing LSXA3K**23** is a LSXA3K switch adjusted for counter-clockwise actuation only. The operating shaft is to the right side of the switch when viewing it from the front (label side). No lever.

## PLUNGER ASSEMBLY MODIFICATIONS

Add the following modification numbers to the catalog listing in the plunger switch:

**3** Side plunger to right of switch front
**4** Side plunger to left of switch front
**5** Side plunger to back of switch
**6** Roller on top plungers perpendicular to mounting surface
**8** Roller on side plungers in vertical position

**For example,**
Catalog listing LSXF3K**3** is a LSXF3K switch with the side roller plunger to the right side.

**Figure 3. MICRO SWITCH™ LSX SERIES PRODUCT REFERENCE DIMENSIONS • mm [in]**
**SIDE ROTARY - HEAD CODES: A, H, L, M, N, P, Q, R, AND U**




**Figure 4. MICRO SWITCH™ LSX SERIES WOBBLE STICK, HEAD CODE J • mm [in]**




**Figure 5. MICRO SWITCH™ LSX SERIES CAT WHISKER WOBBLE, HEAD CODE K • mm [in]**



**Figure 6. MICRO SWITCH™ LSX SERIES TOP ROTARY, HEAD CODE B • mm [in]**




**Figure 7. MICRO SWITCH™ LSX SERIES TOP PIN PLUNGER, HEAD CODE C • mm [in]**




**Figure 8. MICRO SWITCH™ LSX SERIES TOP ROLLER PLUNGER, HEAD CODE D • mm [in]**




**Figure 9. MICRO SWITCH™ LSX SERIES SIDE PLUNGER, HEAD CODE E • mm [in]**




**Figure 10. MICRO SWITCH™ LSX SERIES ADJUSTABLE TOP PIN PLUNGER, HEAD CODE V • mm [in]**




**Figure 11. MICRO SWITCH™ LSX SERIES SIDE ROLLER PLUNGER, HEAD CODE F • mm [in]**




**Figure 12. MICRO SWITCH™ LSX SERIES ADJUSTABLE SIDE PIN PLUNGER, HEAD CODE W • mm [in]**



# MICRO SWITCH™ Hazardous Area Limit Switches

**This datasheet supports the following MICRO SWITCH™ LSX Series Hazardous Area Limit Switches**

LSXA3E
LSXA3E-1A
LSXA3E-2K
LSXA3E1
LSXA3E24-1A
LSXA3K
LSXA3K-1A
LSXA3K-1C
LSXA3K-2C
LSXA3K-2J
LSXA3K-2K
LSXA3K-4M
LSXA3K-5C
LSXA3K1
LSXA3K1-1C
LSXA3K1-2C
LSXA3K4-4M
LSXA3K5
LSXA3K5-1A
LSXA3K5-4M
LSXA3K5-5C
LSXA3N
LSXA4K
LSXA4K-1A
LSXA4K-2C
LSXA4K-2J
LSXA4L
LSXA4L-1A
LSXA4L-1C
LSXA4L-2C
LSXA4L-2K
LSXA4L-4M
LSXA4L-5C
LSXA4L13-2J
LSXA4L2-1C
LSXA4L3-2C
LSXA4L4-1A
LSXA4L4-2C
LSXA4L5
LSXA4L5-1A
LSXA4S
LSXA4S-2K
LSXA4S13-2C
LSXA4S5
LSXA7L
LSXA7L-1A
LSXA7S
LSXA7S-2
LSXA7S1-1C
LSXA7S2-1C
LSXB3K
LSXB3K-4M
LSXB4L
LSXB4L-1C
LSXB4L-4M
LSXC3E
LSXC3K
LSXC4K
LSXC4L
LSXC4S
LSXC7L
LSXD3E
LSXD3K
LSXD3K6
LSXD4K
LSXD4L
LSXD4L6
LSXD7L
LSXE3K
LSXE3K3
LSXE3K4
LSXE4K
LSXE4L
LSXF3E
LSXF3K
LSXF3K5
LSXF3K8
LSXF4L
LSXF4L5
LSXF7L
LSXF7L5
LSXH3K
LSXH3K-2C
LSXH3K-4M
LSXH3K3-2C
LSXH4K
LSXH4L
LSXH4L-4
LSXH4L3
LSXH7L4-1A
LSXJ3E-7A
LSXJ3K-7A
LSXJ4L-7A
LSXJ4S-7A
LSXJ7L-7A
LSXK3K-8A
LSXK4L-8A
LSXL4M
LSXL4M4
LSXL7M-2C
LSXM4N
LSXM4N-1A
LSXM4N-1C
LSXM4N-2C
LSXM4N-2J
LSXM4N-3S
LSXM4N-4M
LSXM4N-5C
LSXM4N3-1A
LSXM4N4
LSXM4N4-1A
LSXM4N5
LSXM4N5-1A
LSXM4U
LSXM7N
LSXM7N-1A
LSXM7U
LSXN3K
LSXN3K-1A
LSXN3K-4M
LSXN4K
LSXN4L
LSXN4L-1A
LSXN4L-2C
LSXN4L-3S
LSXN4L4
LSXN4S-3S
LSXN7L
LSXN7L-2A
LSXP3E
LSXP3K
LSXP3K-1A
LSXP3K-1C
LSXP3K-5C
LSXP3K1
LSXP3K3
LSXP3K3-1A
LSXP3K5-1A
LSXP4K
LSXP4K-2C
LSXP4L
LSXP4L-2C
LSXP4L3-2C
LSXP7L
LSXP7L14-2C
LSXP7L3
LSXQA3K332
LSXQC4C
LSXR3K
LSXR3K-1A
LSXR3K-1C
LSXR3K-5A
LSXR4K-2C
LSXR4L
LSXR4L-1C
LSXR4L-2J
LSXR4L-5A
LSXR4L-5C
LSXR4L1
LSXR4L24
LSXU3K
LSXV3K
LSXV4L
LSXV4S
LSXV7L
LSXW3K
LSXW3K3
LSXW4L
LSXW7L
LSXYAB3E
LSXYAB3K
LSXYAB3K-1A
LSXYAB3K2
LSXYAB3K2-5C
LSXYAB3K5-2C
LSXYAB4K
LSXYAB4K-1A
LSXYAB4L
LSXYAB4L-1A
LSXYAB4L4
LSXYAB4L5-1A
LSXYAB7L
LSXYAC3K
LSXYAC3K-2C
LSXYAC4L
LSXYBB3K
LSXYBB4L
LSXYCB3K
LSXYCB4L
LSXYCC3K
LSXYCC4L
LSXYDB3K
LSXYDB4L
LSXYDC7L
LSXYEB3K
LSXYEC3K
LSXYFB3K
LSXYHB3K-2C
LSXYJB3K-7A
LSXYLB4M
LSXYMB4N
LSXYMB4N-1A
LSXYMB4N-2C
LSXYMB4N5-1A
LSXYMC4N
LSXYNB3K
LSXYNB3N-1A
LSXYNB4L
LSXYPB3K
LSXYPB4L
LSXYPB4S
LSXYPC4L5
LSXYRB3K
LSXYVC3K
LSXYWC3K
LSXYWC4L5
LSXZ1C
LSXZ1CB
LSXZ1CC
LSXZ1D
LSXZ1DB
LSXZ1DC
LSXZ1E
LSXZ1EB
LSXZ1EC
LSXZ1F
LSXZ1FB
LSXZ1FC
LSXZ1KHA
LSXZ1V
LSXZ1VB
LSXZ1VC
LSXZ1W
LSXZ1WB
LSXZ1WC
LSXZ23E
LSXZ23EB
LSXZ23K
LSXZ23KB
LSXZ23N
LSXZ23NB
LSXZ24K
LSXZ24KB
LSXZ24L
LSXZ24LB
LSXZ24M
LSXZ24MB
LSXZ24N
LSXZ24NB
LSXZ24S
LSXZ24SB
LSXZ24SC
LSXZ24T
LSXZ24TB
LSXZ24TC
LSXZ24U
LSXZ24UB
LSXZ24UC
LSXZ27L
LSXZ27LB
LSXZ27N
LSXZ27NB
LSXZ27S
LSXZ27SB
LSXZ27SC
LSXZ27T
LSXZ27TB
LSXZ27TC
LSXZ27U
LSXZ27UB
LSXZ27UC
LSXZ3E
LSXZ3K
LSXZ3L
LSXZ3M
LSXZ3S
LSXZ4012
LSXZ4022

## ADDITIONAL INFORMATION

The following associated literature is available on the Honeywell web site at sensing.honeywell.com:

- Product installation instructions
- Product range guide
- Hazardous area product brochure
- Product application-specific information
  - Application note: Electronic sensors and electromechanical switches in valves and flow meters
  - Application note: MICRO SWITCH™ switches in conveyor applications
  - Application note: Sensors and switches for industrial manual process valves
  - Application note: Sensors and switches used in valve actuators and valve positioners
  - Limit and enclosed switches reference standards
  - Sensors and switches in oil rig applications

**⚠WARNING**

**PERSONAL INJURY**

**DO NOT USE** these products as safety or emergency stop devices or in any other application where failure of the product could result in personal injury.

**Failure to comply with these instructions could result in death or serious injury.**

**⚠WARNING**

**MISUSE OF DOCUMENTATION**

- The information presented in this product sheet is for reference only. Do not use this document as a product installation guide.
- Complete installation, operation, and maintenance information is provided in the instructions supplied with each product.

**Failure to comply with these instructions could result in death or serious injury.**

## WARRANTY/REMEDY

Honeywell warrants goods of its manufacture as being free of defective materials and faulty workmanship. Honeywell's standard product warranty applies unless agreed to otherwise by Honeywell in writing; please refer to your order acknowledgement or consult your local sales office for specific warranty details. If warranted goods are returned to Honeywell during the period of coverage, Honeywell will repair or replace, at its option, without charge those items it finds defective. **The foregoing is buyer's sole remedy and is in lieu of all other warranties, expressed or implied, including those of merchantability and fitness for a particular purpose. In no event shall Honeywell be liable for consequential, special, or indirect damages.**

While we provide application assistance personally, through our literature and the Honeywell website, it is up to the customer to determine the suitability of the product in the application.

Specifications may change without notice. The information we supply is believed to be accurate and reliable as of this printing. However, we assume no responsibility for its use.

**Find out more**

Honeywell serves its customers through a worldwide network of sales offices, representatives and distributors. For application assistance, current specifications, pricing or name of the nearest Authorized Distributor, contact your local sales office.

To learn more about Honeywell's sensing and control products, call **+1-815-235-6847 or 1-800-537-6945**, visit **sensing.honeywell.com,** or e-mail inquiries to **info.sc@honeywell.com**

Sensing and Control
Honeywell
1985 Douglas Drive North
Golden Valley, MN 55422
**honeywell.com**

002385-2-EN IL50 GLO
August 2014
Copyright © 2014 Honeywell International Inc. All rights reserved.