

CATALOG LISTING
14TL1-10 SERIES CHART 1
PAGE 1 OF 1

ISSUE
4

REVISIONS
A 085 DWG
0049025
S M A L R 81
B RE INST
PR 11666
S L B 8
8 NOV 82
C CO-
94428
CSL
28 NOV 99


FORMTEK
DRAWN
S L B 8 NOV 82
CHECK
DWG 10 NOV 82
CHECK

MICRO SWITCH
FREEPORT, ILLINOIS, U S A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929


SWITCH - BASIC

CATALOG LISTING
14TL1-10 SERIES
CHART 1


THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.






















STYLE 1 LEVER



CODE L191 15A-125, 250, 277 VAC
1/2 HP-125 VAC, 1 HP-250, 277 VAC
5A-125 VAC "L"



CATALOG LISTING	AVAILABLE LOCKING COMBINATIONS FOR CONFIGURATION SEE LETTERED DETAILS	STYLE NUMBER	CURRENT CAPACITY (AMPS)									
			RESISTIVE LOAD					LAMP LOAD	INDUCTIVE LOAD			
			DC VOLTS		AC VOLTS							
			30	115	250	115	230	30 VDC	115 VAC	30 VDC	115 VAC	
	14TL1-10	NONE	1	20	.75	.5	15	6	5	4	12	15
	14TL1-10 	A,B,D,E,F,G,H,J,K,L M,N,P	2	(REFER TO L191 FOR UL RATING)								
"A"  LOCKED IN THREE POSITIONS	"B"  LOCKED IN CENTER AND EXTREME POSITION (KEYWAY SIDE)	"D"  LOCKED OUT OF CENTER POSITION	"E"  LOCKED IN CENTER POSITION	"F"  LOCKED IN EXTREME POSITION (OPPOSITE KEYWAY)	 LOCKWASHER 							
"G"  LOCKED IN EXTREME POSITION (KEYWAY SIDE)	"H"  LOCKED OUT OF CENTER AND EXTREME POSITION (KEYWAY SIDE)	"J"  LOCKED OUT OF CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)	"K"  LOCKED IN CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)	"L"  LOCKED OUT OF EXTREME POSITION (KEYWAY SIDE)								
"M"  LOCKED OUT OF AND INTO EXTREME POSITION (OPPOSITE KEYWAY)	"N"  LOCKED OUT OF EXTREME POSITION (OPPOSITE KEYWAY)	"P"  LOCKED OUT OF AND INTO EXTREME POSITION (KEYWAY SIDE)	 LOCKING RING 									
CIRCUIT MADE WITH TOGGLE LEVER IN												
KEYWAY SIDE		CENTER						OPPOSITE KEYWAY		 HEX NUT (2) 		
												
MAINTAINED POSITION		MAINTAINED POSITION		MAINTAINED POSITION								

- NOTES
- 1 - SWITCHES ARE CAPABLE OF WITHSTANDING A TEMPERATURE OF 160°F CONTINUOUSLY AT FULL RATED LOAD
 - 2 - CIRCUIT DESIGNATION AND MICRO SWITCH CATALOG LISTING STAMPED ON SIDE OF SWITCH
 - 3 - KEYWAY SHOWN ON LEFT SIDE
 - 4 - FURNISHED UNASSEMBLED
 - 5 - FOR TERMINAL COVER SEE MICRO SWITCH CATALOG LISTING 5PA9
 - 6 - SUFFIX LETTER MUST BE ADDED FOR DESIRED TYPE TOGGLE LOCKING. SEE CHART FOR AVAILABLE LOCKING COMBINATIONS