

FED MFG CODE 91029

CHART 1

RESISTIVE LOAD					LAMP LOAD		INDUCTIVE LOAD	
DC VOLTS			AC VOLTS					
28	125	250	125	250	28 VDC	125 VAC	28 VDC	125 VAC

ITL56-61	MOM ON	OFF	NONE
----------	--------	-----	------

(REFER TO L192 FOR UL RATING)

HEX NUT (2)


15A-125, <u>250</u> OR 277VAC 1/2HP-125VAC; 1HP-<u>250</u>, 277VAC 5A-125VAC "L" CODE L192	10A-125, <u>250</u> OR 277VAC 1/4HP-125VAC; 1/2HP-<u>250</u>, 277VAC 3A-125VAC "L" CODE L192
---	---

MICRO SWITCH
FREEPORT ILLINOIS U S A
A DIVISION OF HONEYWELL
FED MFG CODE 91929

SWITCH-TOGGLE

CATALOG LISTING
1TL156 SERIES
CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH A DIVISION OF HONEYWELL THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CATALOG LISTING	CIRCUIT MADE WITH TOGGLE LEVER IN		
	KEYWAY SIDE (1-2)	CENTER (1-2)	OPPOSITE KEYWAY (2-3)
ITL156-1	ON	OFF	ON
ITL156-2	OFF	NONE	ON
ITL156-3	ON	NONE	ON
ITL156-21	NONE	OFF	ON
ITL156-31	NONE	ON	ON
ITL156-4	MOM OFF	NONE	ON
ITL156-5	MOM ON	OFF	ON
ITL156-6	MOM ON	NONE	OFF
ITL156-7	MOM ON	OFF	MOM ON
ITL156-8	MOM ON	NONE	ON
ITL156-51	NONE	ON	MOM ON
ITL156-61	MOM ON	OFF	NONE

MILITARY RATING (AMPS)									
RESISTIVE LOAD					LAMP LOAD		INDUCTIVE LOAD		
DC VOLTS		AC VOLTS			28 VDC	125 VAC	28 VDC	125 VAC	
28	125	250	125	250					
20	.75	.5	15	6	5	3	15	10	
(REFER TO L191 FOR UL RATING)									
15	.75	.5	15	6	4	2	10	7	
(REFER TO L192 FOR UL RATING)									

NOTES

- 1 - SWITCHES ARE CAPABLE OF WITHSTANDING A TEMPERATURE OF 160°F CONTINUOUSLY AT FULL RATED LOAD
- 2 - CIRCUIT DESIGNATION AND MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
- 3 FURNISHED UNASSEMBLED

4 APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS

