






Lage beachten! / look at position!



					general tolerance		scale: 3:1	
					ISO 2768 AA-CS-12		Assembly instruction: Stripping dimension: Fidelity	
						date	name	HF-Leitung flexibel RF-flexible cable assembly
					generate	06.06.07	Pölz	
					checked			
					Norm			
								K-2397
								Rev.
nr.	rev.	alteration	date	name				




M/s 3:1



M/s 1:1



Kabelzuschnitt / stripping dimension
Kabel / cabel: Hirose U.FL-LP-066



Aussen crimpsen / out crimp: $\square$ 2,67
Innen crimpsen / in crimp: löten / solder

IMS CONNECTOR SYSTEMS					general tolerance ISO 2768 mH angle: $\pm 5^\circ$		scale: 10:1	
					generate		Assembly instruction: M8	
					checked		Stripping dimension:	
					Norm		SMP-Kabelwinkelbuchse	
							SMP-Cable mount angle jack	
							4109.SMP.2420.04	
							Rev. a	
Entwurf nr.	a rev.	El. optimiert alteration	28.03.06 date	Pölz name				