



**Z i L O G**

**High-Performance 8-Bit Microcontrollers**

## **Z8 Encore!® 4K Series**

### **Product Brief**

PB014206-0106

**Z8 Encore!**

### **Product Block Diagram**

|                                    |                      |                               |
|------------------------------------|----------------------|-------------------------------|
| 1–4 KB Flash                       | 256 B–1 KB RAM       | Up to 8 10-Bit ADC Channels   |
| Watch-Dog Timer with RC Oscillator | <b>5 MHz eZ8 CPU</b> | Two 16-Bit Timers/PWM         |
| Analog Comparator                  |                      | POR/VBO & Reset Control       |
| UART with IrDA                     | On-Chip Debugger     | Internal Precision Oscillator |
| Up to 24 General-Purpose I/O Pins  |                      |                               |

### **Overview**

The Z8 Encore!® 4K Series Flash microcontrollers are based on the ZiLOG® eZ8 CPU. The Z8 Encore!® 4K Series MCU family of devices sets a new standard of performance and on-chip peripherals.

The Z8 Encore!® 4K Series feature support up to 4 KB of Flash program memory and 1KB register RAM.

The Z8 Encore!® 4K Series devices feature up to eight single-ended/differential channels of 10-bit A/D conversion.

These devices include two enhanced 16-bit reloadable timers featuring Capture, Compare, and PWM capabilities.

Up to 18 vectored interrupts with programmable priorities provide increased application flexibility.

The Z8 Encore!® 4K Series features an on-chip Internal Precision Oscillator (5 MHz/32 KHz) as a trimmable clock source that requires no external components.

The new single-pin debugger and programming interface simplifies code development and allows for easy in-circuit programming.

The full-duplex UART provides serial communications and IrDA encoding and decoding capability. The UART baud rate generator (BRG) can be configured and used as a basic 16-bit timer.

### **Z8 Encore!® 4K Series Features**

Key features of Z8 Encore!® 4K Series MCU include:

- 5 MHz eZ8 CPU core
- Up to 4 KB Flash memory with in-circuit programming capability
- Up to 1 KB register RAM
- Up to 8 channels 10-bit analog-to-digital converter (ADC)
- On-chip analog comparator
- Full-duplex 9-bit UART with bus transceiver Driver Enable Control
- The UART baud rate generator (BRG) can be configured and used as a basic 16-bit timer
- Infrared Data Association (IrDA)-compliant infrared encoder/decoders, integrated with UART
- Two 16-bit timers with capture, compare, and PWM capabilities
- Watch-Dog Timer (WDT) with internal RC oscillator



- 16 to 24 I/O pins depending upon package
- Direct LED Drive with programmable drive strengths
- Up to 18 interrupts with configurable priority
- On-chip debugger
- Voltage Brown-Out Protection (VBO)
- Power-On Reset (POR)
- Internal Precision Oscillator (5 MHz/32 KHz)
- 2.7 to 3.6 V operating voltage with 5 V-tolerant inputs
- 8-pin, 20-pin, and 28-pin packages
- 0°C to +70°C standard temperature and –40°C to +105°C extended temperature operating ranges

## eZ8 CPU Features

The eZ8 CPU, ZiLOGs latest 8-bit central processing unit, meets the continuing demand for faster and more code-efficient microcontrollers. The eZ8 CPU features include:

- New instructions for improved performance including BIT, BSWAP, BTJ, CPC, LDC, LDCI, LEA, MULT, and SRL
- New instructions support 12-bit linear addressing of the Register File
- Compatible with existing Z8<sup>®</sup> code
- Up to 10 MIPS operation
- C-Compiler friendly
- 2 to 9 clock cycles per instruction

## Z8 Encore!<sup>®</sup> 4K Series Development Kit

The Z8 Encore!<sup>®</sup> 4K Series Development System includes the following:

### Hardware

- Z8 Encore!<sup>®</sup> 4K Series Development Board
- Smart Cable for PC to Z8 Encore!<sup>®</sup> 4K Series Development Board (DB9 to 6-pin male)
- 5 V DC power supply

### Software on CD-ROM

- ZDS II–Z8 Encore!<sup>®</sup> IDE with ANSI C-Compiler
- Sample code
- Document browser
- Acrobat Reader<sup>®</sup>

### Documentation

- Quick Start Guide
- Registration card
- Z8 Encore!<sup>®</sup> 4K Series technical documentation (on CD-ROM)
  - Development Kit User Manual
  - ZDSII IDE User Manual
  - eZ8 CPU User Manual
  - Product Specification
  - Product Brief
  - Application Notes

## Architecture

Figure 1 illustrates the Z8 Encore!® 4K Series block diagram.




Figure 1. Z8 Encore!® 4K Series Block Diagram



## Ordering Information

You can order the Z8 Encore!® 4K Series from ZiLOG®, referencing the following part numbers. For more information regarding ordering, please consult your local ZiLOG® sales office. The ZiLOG® website [www.zilog.com](http://www.zilog.com) lists all regional offices and provides additional Z8 Encore!® product information.

| Part Number                                                           | Flash | RAM  | I/O Lines | Interrupts | 16-Bit Timers w/PWM | 10-Bit A/D Channels | UART with IrDA | Comparator | Description         |
|-----------------------------------------------------------------------|-------|------|-----------|------------|---------------------|---------------------|----------------|------------|---------------------|
| <b>Z8 Encore!® with 4KB Flash, 10-Bit Analog-to-Digital Converter</b> |       |      |           |            |                     |                     |                |            |                     |
| <b>Standard Temperature: 0° to +70°C</b>                              |       |      |           |            |                     |                     |                |            |                     |
| Z8F0423PB005SC                                                        | 4 KB  | 1 KB | 6         | 12         | 2                   | 4                   | 1              | 1          | PDIP 8-pin package  |
| Z8F0423QB005SC                                                        | 4 KB  | 1 KB | 6         | 12         | 2                   | 4                   | 1              | 1          | QFN 8-pin package   |
| Z8F0423SB005SC                                                        | 4 KB  | 1 KB | 6         | 12         | 2                   | 4                   | 1              | 1          | SOIC 8-pin package  |
| Z8F0423SH005SC                                                        | 4 KB  | 1 KB | 16        | 18         | 2                   | 7                   | 1              | 1          | SOIC 20-pin package |
| Z8F0423HH005SC                                                        | 4 KB  | 1 KB | 16        | 18         | 2                   | 7                   | 1              | 1          | SSOP 20-pin package |
| Z8F0423PH005SC                                                        | 4 KB  | 1 KB | 16        | 18         | 2                   | 7                   | 1              | 1          | PDIP 20-pin package |
| Z8F0423SJ005SC                                                        | 4 KB  | 1 KB | 22        | 18         | 2                   | 8                   | 1              | 1          | SOIC 28-pin package |
| Z8F0423HJ005SC                                                        | 4 KB  | 1 KB | 22        | 18         | 2                   | 8                   | 1              | 1          | SSOP 28-pin package |
| Z8F0423PJ005SC                                                        | 4 KB  | 1 KB | 22        | 18         | 2                   | 8                   | 1              | 1          | PDIP 28-pin package |
| <b>Extended Temperature: -40° to +105°C</b>                           |       |      |           |            |                     |                     |                |            |                     |
| Z8F0423PB005EC                                                        | 4 KB  | 1 KB | 6         | 12         | 2                   | 4                   | 1              | 1          | PDIP 8-pin package  |
| Z8F0423QB005EC                                                        | 4 KB  | 1 KB | 6         | 12         | 2                   | 4                   | 1              | 1          | QFN 8-pin package   |
| Z8F0423SB005EC                                                        | 4 KB  | 1 KB | 6         | 12         | 2                   | 4                   | 1              | 1          | SOIC 8-pin package  |
| Z8F0423SH005EC                                                        | 4 KB  | 1 KB | 16        | 18         | 2                   | 7                   | 1              | 1          | SOIC 20-pin package |
| Z8F0423HH005EC                                                        | 4 KB  | 1 KB | 16        | 18         | 2                   | 7                   | 1              | 1          | SSOP 20-pin package |
| Z8F0423PH005EC                                                        | 4 KB  | 1 KB | 16        | 18         | 2                   | 7                   | 1              | 1          | PDIP 20-pin package |
| Z8F0423SJ005EC                                                        | 4 KB  | 1 KB | 22        | 18         | 2                   | 8                   | 1              | 1          | SOIC 28-pin package |
| Z8F0423HJ005EC                                                        | 4 KB  | 1 KB | 22        | 18         | 2                   | 8                   | 1              | 1          | SSOP 28-pin package |
| Z8F0423PJ005EC                                                        | 4 KB  | 1 KB | 22        | 18         | 2                   | 8                   | 1              | 1          | PDIP 28-pin package |
| Replace C with G for Lead-Free Packaging                              |       |      |           |            |                     |                     |                |            |                     |



| Part Number                                | Flash | RAM  | I/O Lines | Interrupts | 16-Bit Timers w/PWM | 10-Bit A/D Channels | UART with IrDA | Comparator | Description         |
|--------------------------------------------|-------|------|-----------|------------|---------------------|---------------------|----------------|------------|---------------------|
| <b>Z8 Encore!® with 4KB Flash</b>          |       |      |           |            |                     |                     |                |            |                     |
| <b>Standard Temperature: 0° to 70°C</b>    |       |      |           |            |                     |                     |                |            |                     |
| Z8F0413PB005SC                             | 4 KB  | 1 KB | 6         | 12         | 2                   | 0                   | 1              | 1          | PDIP 8-pin package  |
| Z8F0413QB005SC                             | 4 KB  | 1 KB | 6         | 12         | 2                   | 0                   | 1              | 1          | QFN 8-pin package   |
| Z8F0413SB005SC                             | 4 KB  | 1 KB | 6         | 12         | 2                   | 0                   | 1              | 1          | SOIC 8-pin package  |
| Z8F0413SH005SC                             | 4 KB  | 1 KB | 16        | 18         | 2                   | 0                   | 1              | 1          | SOIC 20-pin package |
| Z8F0413HH005SC                             | 4 KB  | 1 KB | 16        | 18         | 2                   | 0                   | 1              | 1          | SSOP 20-pin package |
| Z8F0413PH005SC                             | 4 KB  | 1 KB | 16        | 18         | 2                   | 0                   | 1              | 1          | PDIP 20-pin package |
| Z8F0413SJ005SC                             | 4 KB  | 1 KB | 24        | 18         | 2                   | 0                   | 1              | 1          | SOIC 28-pin package |
| Z8F0413HJ005SC                             | 4 KB  | 1 KB | 24        | 18         | 2                   | 0                   | 1              | 1          | SSOP 28-pin package |
| Z8F0413PJ005SC                             | 4 KB  | 1 KB | 24        | 18         | 2                   | 0                   | 1              | 1          | PDIP 28-pin package |
| <b>Extended Temperature: -40° to 105°C</b> |       |      |           |            |                     |                     |                |            |                     |
| Z8F0413PB005EC                             | 4 KB  | 1 KB | 6         | 12         | 2                   | 0                   | 1              | 1          | PDIP 8-pin package  |
| Z8F0413QB005EC                             | 4 KB  | 1 KB | 6         | 12         | 2                   | 0                   | 1              | 1          | QFN 8-pin package   |
| Z8F0413SB005EC                             | 4 KB  | 1 KB | 6         | 12         | 2                   | 0                   | 1              | 1          | SOIC 8-pin package  |
| Z8F0413SH005EC                             | 4 KB  | 1 KB | 16        | 18         | 2                   | 0                   | 1              | 1          | SOIC 20-pin package |
| Z8F0413HH005EC                             | 4 KB  | 1 KB | 16        | 18         | 2                   | 0                   | 1              | 1          | SSOP 20-pin package |
| Z8F0413PH005EC                             | 4 KB  | 1 KB | 16        | 18         | 2                   | 0                   | 1              | 1          | PDIP 20-pin package |
| Z8F0413SJ005EC                             | 4 KB  | 1 KB | 24        | 18         | 2                   | 0                   | 1              | 1          | SOIC 28-pin package |
| Z8F0413HJ005EC                             | 4 KB  | 1 KB | 24        | 18         | 2                   | 0                   | 1              | 1          | SSOP 28-pin package |
| Z8F0413PJ005EC                             | 4 KB  | 1 KB | 24        | 18         | 2                   | 0                   | 1              | 1          | PDIP 28-pin package |
| Replace C with G for Lead-Free Packaging   |       |      |           |            |                     |                     |                |            |                     |



| Part Number                                                           | Flash | RAM   | I/O Lines | Interrupts | 16-Bit Timers w/PWM | 10-Bit A/D Channels | UART with IrDA | Comparator | Description         |
|-----------------------------------------------------------------------|-------|-------|-----------|------------|---------------------|---------------------|----------------|------------|---------------------|
| <b>Z8 Encore!® with 2KB Flash, 10-Bit analog-to-Digital Converter</b> |       |       |           |            |                     |                     |                |            |                     |
| <b>Standard Temperature: 0° to 70°C</b>                               |       |       |           |            |                     |                     |                |            |                     |
| Z8F0223PB005SC                                                        | 2 KB  | 512 B | 6         | 12         | 2                   | 4                   | 1              | 1          | PDIP 8-pin package  |
| Z8F0223QB005SC                                                        | 2 KB  | 512 B | 6         | 12         | 2                   | 4                   | 1              | 1          | QFN 8-pin package   |
| Z8F0223SB005SC                                                        | 2 KB  | 512 B | 6         | 12         | 2                   | 4                   | 1              | 1          | SOIC 8-pin package  |
| Z8F0223SH005SC                                                        | 2 KB  | 512 B | 16        | 18         | 2                   | 7                   | 1              | 1          | SOIC 20-pin package |
| Z8F0223HH005SC                                                        | 2 KB  | 512 B | 16        | 18         | 2                   | 7                   | 1              | 1          | SSOP 20-pin package |
| Z8F0223PH005SC                                                        | 2 KB  | 512 B | 16        | 18         | 2                   | 7                   | 1              | 1          | PDIP 20-pin package |
| Z8F0223SJ005SC                                                        | 2 KB  | 512 B | 22        | 18         | 2                   | 8                   | 1              | 1          | SOIC 28-pin package |
| Z8F0223HJ005SC                                                        | 2 KB  | 512 B | 22        | 18         | 2                   | 8                   | 1              | 1          | SSOP 28-pin package |
| Z8F0223PJ005SC                                                        | 2 KB  | 512 B | 22        | 18         | 2                   | 8                   | 1              | 1          | PDIP 28-pin package |
| <b>Extended Temperature: -40° to 105°C</b>                            |       |       |           |            |                     |                     |                |            |                     |
| Z8F0223PB005EC                                                        | 2 KB  | 512 B | 6         | 12         | 2                   | 4                   | 1              | 1          | PDIP 8-pin package  |
| Z8F0223QB005EC                                                        | 2 KB  | 512 B | 6         | 12         | 2                   | 4                   | 1              | 1          | QFN 8-pin package   |
| Z8F0223SB005EC                                                        | 2 KB  | 512 B | 6         | 12         | 2                   | 4                   | 1              | 1          | SOIC 8-pin package  |
| Z8F0223SH005EC                                                        | 2 KB  | 512 B | 16        | 18         | 2                   | 7                   | 1              | 1          | SOIC 20-pin package |
| Z8F0223HH005EC                                                        | 2 KB  | 512 B | 16        | 18         | 2                   | 7                   | 1              | 1          | SSOP 20-pin package |
| Z8F0223PH005EC                                                        | 2 KB  | 512 B | 16        | 18         | 2                   | 7                   | 1              | 1          | PDIP 20-pin package |
| Z8F0223SJ005EC                                                        | 2 KB  | 512 B | 22        | 18         | 2                   | 8                   | 1              | 1          | SOIC 28-pin package |
| Z8F0223HJ005EC                                                        | 2 KB  | 512 B | 22        | 18         | 2                   | 8                   | 1              | 1          | SSOP 28-pin package |
| Z8F0223PJ005EC                                                        | 2 KB  | 512 B | 22        | 18         | 2                   | 8                   | 1              | 1          | PDIP 28-pin package |
| Replace C with G for Lead-Free Packaging                              |       |       |           |            |                     |                     |                |            |                     |



| Part Number                                | Flash | RAM   | I/O Lines | Interrupts | 16-Bit Timers w/PWM | 10-Bit A/D Channels | UART with IrDA | Comparator | Description         |
|--------------------------------------------|-------|-------|-----------|------------|---------------------|---------------------|----------------|------------|---------------------|
| <b>Z8 Encore!® with 2KB Flash</b>          |       |       |           |            |                     |                     |                |            |                     |
| <b>Standard Temperature: 0° to 70°C</b>    |       |       |           |            |                     |                     |                |            |                     |
| Z8F0213PB005SC                             | 2 KB  | 512 B | 6         | 12         | 2                   | 0                   | 1              | 1          | PDIP 8-pin package  |
| Z8F0213QB005SC                             | 2 KB  | 512 B | 6         | 12         | 2                   | 0                   | 1              | 1          | QFN 8-pin package   |
| Z8F0213SB005SC                             | 2 KB  | 512 B | 6         | 12         | 2                   | 0                   | 1              | 1          | SOIC 8-pin package  |
| Z8F0213SH005SC                             | 2 KB  | 512 B | 16        | 18         | 2                   | 0                   | 1              | 1          | SOIC 20-pin package |
| Z8F0213HH005SC                             | 2 KB  | 512 B | 16        | 18         | 2                   | 0                   | 1              | 1          | SSOP 20-pin package |
| Z8F0213PH005SC                             | 2 KB  | 512 B | 16        | 18         | 2                   | 0                   | 1              | 1          | PDIP 20-pin package |
| Z8F0213SJ005SC                             | 2 KB  | 512 B | 24        | 18         | 2                   | 0                   | 1              | 1          | SOIC 28-pin package |
| Z8F0213HJ005SC                             | 2 KB  | 512 B | 24        | 18         | 2                   | 0                   | 1              | 1          | SSOP 28-pin package |
| Z8F0213PJ005SC                             | 2 KB  | 512 B | 24        | 18         | 2                   | 0                   | 1              | 1          | PDIP 28-pin package |
| <b>Extended Temperature: -40° to 105°C</b> |       |       |           |            |                     |                     |                |            |                     |
| Z8F0213PB005EC                             | 2 KB  | 512 B | 6         | 12         | 2                   | 0                   | 1              | 1          | PDIP 8-pin package  |
| Z8F0213QB005EC                             | 2 KB  | 512 B | 6         | 12         | 2                   | 0                   | 1              | 1          | QFN 8-pin package   |
| Z8F0213SB005EC                             | 2 KB  | 512 B | 6         | 12         | 2                   | 0                   | 1              | 1          | SOIC 8-pin package  |
| Z8F0213SH005EC                             | 2 KB  | 512 B | 16        | 18         | 2                   | 0                   | 1              | 1          | SOIC 20-pin package |
| Z8F0213HH005EC                             | 2 KB  | 512 B | 16        | 18         | 2                   | 0                   | 1              | 1          | SSOP 20-pin package |
| Z8F0213PH005EC                             | 2 KB  | 512 B | 16        | 18         | 2                   | 0                   | 1              | 1          | PDIP 20-pin package |
| Z8F0213SJ005EC                             | 2 KB  | 512 B | 24        | 18         | 2                   | 0                   | 1              | 1          | SOIC 28-pin package |
| Z8F0213HJ005EC                             | 2 KB  | 512 B | 24        | 18         | 2                   | 0                   | 1              | 1          | SSOP 28-pin package |
| Z8F0213PJ005EC                             | 2 KB  | 512 B | 24        | 18         | 2                   | 0                   | 1              | 1          | PDIP 28-pin package |
| Replace C with G for Lead-Free Packaging   |       |       |           |            |                     |                     |                |            |                     |



| Part Number                                                           | Flash | RAM   | I/O Lines | Interrupts | 16-Bit Timers w/PWM | 10-Bit A/D Channels | UART with IrDA | Comparator | Description         |
|-----------------------------------------------------------------------|-------|-------|-----------|------------|---------------------|---------------------|----------------|------------|---------------------|
| <b>Z8 Encore!® with 1KB Flash, 10-Bit Analog-to-Digital Converter</b> |       |       |           |            |                     |                     |                |            |                     |
| <b>Standard Temperature: 0° to 70°C</b>                               |       |       |           |            |                     |                     |                |            |                     |
| Z8F0123PB005SC                                                        | 1 KB  | 256 B | 6         | 12         | 2                   | 4                   | 1              | 1          | PDIP 8-pin package  |
| Z8F0123QB005SC                                                        | 1 KB  | 256 B | 6         | 12         | 2                   | 4                   | 1              | 1          | QFN 8-pin package   |
| Z8F0123SB005SC                                                        | 1 KB  | 256 B | 6         | 12         | 2                   | 4                   | 1              | 1          | SOIC 8-pin package  |
| Z8F0123SH005SC                                                        | 1 KB  | 256 B | 16        | 18         | 2                   | 7                   | 1              | 1          | SOIC 20-pin package |
| Z8F0123HH005SC                                                        | 1 KB  | 256 B | 16        | 18         | 2                   | 7                   | 1              | 1          | SSOP 20-pin package |
| Z8F0123PH005SC                                                        | 1 KB  | 256 B | 16        | 18         | 2                   | 7                   | 1              | 1          | PDIP 20-pin package |
| Z8F0123SJ005SC                                                        | 1 KB  | 256 B | 22        | 18         | 2                   | 8                   | 1              | 1          | SOIC 28-pin package |
| Z8F0123HJ005SC                                                        | 1 KB  | 256 B | 22        | 18         | 2                   | 8                   | 1              | 1          | SSOP 28-pin package |
| Z8F0123PJ005SC                                                        | 1 KB  | 256 B | 22        | 18         | 2                   | 8                   | 1              | 1          | PDIP 28-pin package |
| <b>Extended Temperature: -40° to 105°C</b>                            |       |       |           |            |                     |                     |                |            |                     |
| Z8F0123PB005EC                                                        | 1 KB  | 256 B | 6         | 12         | 2                   | 4                   | 1              | 1          | PDIP 8-pin package  |
| Z8F0123QB005EC                                                        | 1 KB  | 256 B | 6         | 12         | 2                   | 4                   | 1              | 1          | QFN 8-pin package   |
| Z8F0123SB005EC                                                        | 1 KB  | 256 B | 6         | 12         | 2                   | 4                   | 1              | 1          | SOIC 8-pin package  |
| Z8F0123SH005EC                                                        | 1 KB  | 256 B | 16        | 18         | 2                   | 7                   | 1              | 1          | SOIC 20-pin package |
| Z8F0123HH005EC                                                        | 1 KB  | 256 B | 16        | 18         | 2                   | 7                   | 1              | 1          | SSOP 20-pin package |
| Z8F0123PH005EC                                                        | 1 KB  | 256 B | 16        | 18         | 2                   | 7                   | 1              | 1          | PDIP 20-pin package |
| Z8F0123SJ005EC                                                        | 1 KB  | 256 B | 22        | 18         | 2                   | 8                   | 1              | 1          | SOIC 28-pin package |
| Z8F0123HJ005EC                                                        | 1 KB  | 256 B | 22        | 18         | 2                   | 8                   | 1              | 1          | SSOP 28-pin package |
| Z8F0123PJ005EC                                                        | 1 KB  | 256 B | 22        | 18         | 2                   | 8                   | 1              | 1          | PDIP 28-pin package |
| Replace C with G for Lead-Free Packaging                              |       |       |           |            |                     |                     |                |            |                     |





| Part Number                                | Flash | RAM   | I/O Lines | Interrupts | 16-Bit Timers w/PWM | 10-Bit A/D Channels | UART with IrDA | Comparator | Description                       |
|--------------------------------------------|-------|-------|-----------|------------|---------------------|---------------------|----------------|------------|-----------------------------------|
| <b>Z8 Encore!® with 1KB Flash</b>          |       |       |           |            |                     |                     |                |            |                                   |
| <b>Standard Temperature: 0° to 70°C</b>    |       |       |           |            |                     |                     |                |            |                                   |
| Z8F0113PB005SC                             | 1 KB  | 256 B | 6         | 12         | 2                   | 0                   | 1              | 1          | PDIP 8-pin package                |
| Z8F0113QB005SC                             | 1 KB  | 256 B | 6         | 12         | 2                   | 0                   | 1              | 1          | QFN 8-pin package                 |
| Z8F0113SB005SC                             | 1 KB  | 256 B | 6         | 12         | 2                   | 0                   | 1              | 1          | SOIC 8-pin package                |
| Z8F0113SH005SC                             | 1 KB  | 256 B | 16        | 18         | 2                   | 0                   | 1              | 1          | SOIC 20-pin package               |
| Z8F0113HH005SC                             | 1 KB  | 256 B | 16        | 18         | 2                   | 0                   | 1              | 1          | SSOP 20-pin package               |
| Z8F0113PH005SC                             | 1 KB  | 256 B | 16        | 18         | 2                   | 0                   | 1              | 1          | PDIP 20-pin package               |
| Z8F0113SJ005SC                             | 1 KB  | 256 B | 24        | 18         | 2                   | 0                   | 1              | 1          | SOIC 28-pin package               |
| Z8F0113HJ005SC                             | 1 KB  | 256 B | 24        | 18         | 2                   | 0                   | 1              | 1          | SSOP 28-pin package               |
| Z8F0113PJ005SC                             | 1 KB  | 256 B | 24        | 18         | 2                   | 0                   | 1              | 1          | PDIP 28-pin package               |
| <b>Extended Temperature: -40° to 105°C</b> |       |       |           |            |                     |                     |                |            |                                   |
| Z8F0113PB005EC                             | 1 KB  | 256 B | 6         | 12         | 2                   | 0                   | 1              | 1          | PDIP 8-pin package                |
| Z8F0113QB005EC                             | 1 KB  | 256 B | 6         | 12         | 2                   | 0                   | 1              | 1          | QFN 8-pin package                 |
| Z8F0113SB005EC                             | 1 KB  | 256 B | 6         | 12         | 2                   | 0                   | 1              | 1          | SOIC 8-pin package                |
| Z8F0113SH005EC                             | 1 KB  | 256 B | 16        | 18         | 2                   | 0                   | 1              | 1          | SOIC 20-pin package               |
| Z8F0113HH005EC                             | 1 KB  | 256 B | 16        | 18         | 2                   | 0                   | 1              | 1          | SSOP 20-pin package               |
| Z8F0113PH005EC                             | 1 KB  | 256 B | 16        | 18         | 2                   | 0                   | 1              | 1          | PDIP 20-pin package               |
| Z8F0113SJ005EC                             | 1 KB  | 256 B | 24        | 18         | 2                   | 0                   | 1              | 1          | SOIC 28-pin package               |
| Z8F0113HJ005EC                             | 1 KB  | 256 B | 24        | 18         | 2                   | 0                   | 1              | 1          | SSOP 28-pin package               |
| Z8F0113PJ005EC                             | 1 KB  | 256 B | 24        | 18         | 2                   | 0                   | 1              | 1          | PDIP 28-pin package               |
| Replace C with G for Lead-Free Packaging   |       |       |           |            |                     |                     |                |            |                                   |
| Z8F04A28100KIT                             |       |       |           |            |                     |                     |                |            | 20-Pin and 28-Pin Development Kit |
| Z8F04A08100KIT                             |       |       |           |            |                     |                     |                |            | 8-Pin Development Kit             |
| ZUSBSC0100ZAC                              |       |       |           |            |                     |                     |                |            | USB Smart Cable Accessory Kit     |



## Part Number Suffix Designations

Z8 F 04 23 S H 005 S C

### Environmental Flow:

C = Plastic Standard  
G = Lead Free

### Temperature Range (°C):

S = Standard, 0 to +70  
E = Extended, -40 to +105

### Speed:

005 = 5 MHz

### Pin Count:

B = 8  
H = 20  
J = 28

### Package:

Q = QFN  
H = SSOP  
P = PDIP  
S = SOIC

### Device Type

### Memory Size:

04 = 4 KB Flash, 1 KB RAM  
02 = 2 KB Flash, 512 B RAM  
01 = 1 KB Flash, 256 B RAM

### Memory Type:

F = Flash

### Device Family



This publication is subject to replacement by a later edition. To determine whether a later edition exists, or to request copies of publications, contact:

**ZiLOG Worldwide Headquarters**

532 Race Street  
San Jose, CA 95126  
Telephone: 408.558.8500  
Fax: 408.558.8300  
[www.ZiLOG.com](http://www.ZiLOG.com)

**Document Disclaimer**

ZiLOG is a registered trademark of ZiLOG Inc. in the United States and in other countries. All other products and/or service names mentioned herein may be trademarks of the companies with which they are associated.

©2006 by ZiLOG, Inc. All rights reserved. Information in this publication concerning the devices, applications, or technology described is intended to suggest possible uses and may be superseded. ZiLOG, INC. DOES NOT ASSUME LIABILITY FOR OR PROVIDE A REPRESENTATION OF ACCURACY OF THE INFORMATION, DEVICES, OR TECHNOLOGY DESCRIBED IN THIS DOCUMENT. ZiLOG ALSO DOES NOT ASSUME LIABILITY FOR INTELLECTUAL PROPERTY INFRINGEMENT RELATED IN ANY MANNER TO USE OF INFORMATION, DEVICES, OR TECHNOLOGY DESCRIBED HEREIN OR OTHERWISE. Except with the express written approval ZiLOG, use of information, devices, or technology as critical components of life support systems is not authorized. No licenses or other rights are conveyed, implicitly or otherwise, by this document under any intellectual property rights.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## ZiLOG:

[Z8F0413PH005SC](#) [Z8F0413SH005SC](#) [Z8F0213PJ005EC](#) [Z8F0213SJ005EC](#) [Z8F0213HH005EC](#)  
[Z8F0213HH005SC](#) [Z8F0223SJ005EC](#) [Z8F0223PJ005EC](#) [Z8F0423SB005SC](#) [Z8F0423PB005SG](#) [Z8F0423SB005SG](#)  
[Z8F0423PB005SC](#) [Z8F0413HJ005EC](#) [Z8F0413HJ005SC](#) [Z8F0423SH005SC](#) [Z8F0423PH005EC](#)  
[Z8F0423PH005SC](#) [Z8F0423SH005EC](#) [Z8F0113HJ005EC](#) [Z8F0113HJ005SC](#) [Z8F0123HJ005SC](#) [Z8F0123HJ005EC](#)  
[Z8F0223HH005SC](#) [Z8F0223HJ005SC](#) [Z8F0223HJ005EC](#) [Z8F0413HH005SC](#) [Z8F0223PJ005SC](#)  
[Z8F0223SJ005SC](#) [Z8F0123PJ005SC](#) [Z8F0123SJ005SC](#) [Z8F0123PJ005EC](#) [Z8F0123SJ005EC](#) [Z8F0413HH005EC](#)  
[Z8F0213HJ005SC](#) [Z8F0413PJ005EC](#) [Z8F0413SJ005EC](#) [Z8F0423HH005EC](#) [Z8F0423HH005SC](#) [Z8F0123PH005EC](#)  
[Z8F0123SH005EC](#) [Z8F0123SH005SC](#) [Z8F0123PH005SC](#) [Z8F0213PJ005SC](#) [Z8F0213SJ005SC](#)  
[Z8F0113HH005EC](#) [Z8F0113HH005SC](#) [Z8F0413PH005EC](#) [Z8F0413SH005EC](#) [Z8F0223SH005EC](#)  
[Z8F0223PH005EC](#) [Z8F0223PH005SC](#) [Z8F0223SH005SC](#) [Z8F0423HJ005SC](#) [Z8F0423HJ005EC](#) [Z8F0113PJ005EC](#)  
[Z8F0113SJ005EC](#) [Z8F0423PJ005EC](#) [Z8F0423SJ005EC](#) [Z8F0423SJ005SC](#) [Z8F0423PJ005SC](#) [Z8F0113SJ005SC](#)  
[Z8F0113PJ005SC](#) [Z8F0213HJ005EC](#) [Z8F0123HH005SC](#) [Z8F0123HH005EC](#) [Z8F0413SJ005SC](#) [Z8F0413PJ005SC](#)  
[Z8F0213SH005EC](#) [Z8F0213PH005EC](#) [Z8F0213PH005SC](#) [Z8F0213SH005SC](#) [Z8F0113PH005EC](#)  
[Z8F0113PH005SC](#) [Z8F0113SH005SC](#) [Z8F0113SH005EC](#) [Z8F0223HH005EC](#) [Z8F0123HJ005SG](#) [Z8F0123HJ005EG](#)  
[Z8F0113HJ005EG](#) [Z8F0113HJ005SG](#) [Z8F0223PH005EG](#) [Z8F0223SH005EG](#) [Z8F0223PH005SG](#)  
[Z8F0223SH005SG](#) [Z8F0423HJ005SG](#) [Z8F0423HJ005EG](#) [Z8F0213SH005SG](#) [Z8F0213PH005SG](#)  
[Z8F0213PH005EG](#) [Z8F0213SH005EG](#) [Z8F0413HJ005EG](#) [Z8F0413HJ005SG](#) [Z8F0113PJ005SG](#) [Z8F0113SJ005SG](#)  
[Z8F0113SJ005EG](#) [Z8F0113PJ005EG](#) [Z8F0123PJ005SG](#) [Z8F0123SJ005SG](#) [Z8F0123SJ005EG](#) [Z8F0123PJ005EG](#)