










KTT 217



Specifications:


Contact rating:	max. 20mA, max. 50V DC, max. 0.5W
Contact resistance:	100mOhm max.
Insulation resistance:	1 000MOhm min. at 100V DC
Dielectric strength:	250V, 50Hz for the duration of 1 minute
Operating temperature:	-40°C to +85°C
Mechanical life:	min. 1 000 000 cycles
Operating force:	4.5 +/-1.0N; return force: min. 1N
Travel:	0.45 +/-0.25mm
Soldering conditions:	auto-soldering: max.: 270°C, 5 +/-1sec.
Material:	Terminal contact: brass, 0.025µm gold plated Terminal: brass, tin plated Base: thermoplastic UL94V-0, blue Contact: stainless steel, 0.025µm gold plated Button: silicone, black

IP rating:

IP 67

Compliance: RohS II (2011/65/EU)

CIRCUIT DIAGRAM



Tolerances: up to 10: ±0.2mm above 10-50: ±0.3mm			Date	Name	TMP 1-1	
			09/14	dr		
					30 31 71	
Modifications	Date	Name				

knitter-switch

Page

1/1