


Recommended PCB Layout (Bottom View)



Material and Finish

Shell: Steel, zinc plated or tin plated
 Insulator: PBT with glass-fiber reinforcement
 UL 94V-0
 color-black

Contact Material:
 Socket- Phosphor bronze

Duplex plated as follows:
 -30 .000030" [0.00076mm] gold on mating end, tin-lead on termination end, with entire contact nickel
 -15 .000015" [0.00038mm] gold on mating end, tin-lead on termination end, with entire contact nickel

(Standard) Gold flash on mating end, Gold flash or tin-lead on termination end, with nickel underplate on entire contact

Electrical Specifications

Rated Current: 5A
 Rated Voltage: 300V DC
 Withstanding Voltage: 500V (rms) AC for 1 min
 Insulation Resistance: more than 1000 Mohm at 500v DC
 Contact Resistance: 13 mohm Max
 Dielectric Strength: 1000V for 1 min
 Temperature Rating: -55°C to +105°C

Ferrite Specifications		
Test Frequency	Edge Hole	Inner Hole
30 Mhz	17-27 Ohms	22-30 Ohms
50 Mhz	22-30 Ohms	29-37 Ohms
100 Mhz	29-34 Ohms	35-40 Ohms

Part Number	t_gold
KF22-E9S-N	Flash
KF22-E9S-N15	15u"
KF22-E9S-N30	30u"

CSA NRTL/C Certified File No. LR78160
 UL Recognized File No. E169636

REVISION	DATE	DESCRIPTION	DRAWN BY	DESIGNED BY	UNITS
A	11/6/98	New Drawing	C. Leiva		mm
A2	10/26/00	Ref ECD 00-122	CHECKED BY	APPROVED BY	DATE
					11/6/98

KF22-E9S-N

Rt. Ang Ferrite D-Sub
 9 Pos. Female, 0.318" Footprint



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KF22-E9S-N](#)