


*** UNCONTROLLED DOCUMENT * FOR REFERENCE ONLY**

STEWARD



CORE DIMENSIONS				
UNCOATED CORE			35T1000-000	
	MM	INCHES	MM	INCHES
OD	25.40	(1.000)	± .51	(.020)
ID	15.50	(.610)	± .51	(.020)
TH	10.00	(.394)	± .25	(.010)
EPOXY COATING			35T1000-00H	
OD	26.67	(1.050)	±	max
ID	14.23	(.560)	±	min
TH	11.02	(.434)	±	max

WEIGHT / K 15.4224 KGS 34.0000 LBS
INITIAL PERMEABILITY 5000

ELECTRICAL SPECIFICATIONS								
	MIN (μ H)	MIN TOL.	NOM (μ H)	MAX (μ H)	MAX TOL.	FREQ. (kHz)	VOLT. (V)	TURNS
L1	3.864	(-20%)	4.830	5.796	+20%	100	≤ .0215	1
L2	386.4	(-20%)	483.0	579.6	+20%	100	≤ .2154	10
Q	10	-	-	-	-	100	≤ .0215	1

COATING SPECIFICATIONS					
		Max. Coating Thickness (mm)	Min. DLB VAC	Min. DLB VDC	TEST FORCE (LB)
TYPE					
35T1000-000	UNCOATED	-	-	-	-
35T1000-00H	EPOXY	0.76	1000	1333	4.93

NOTES

Steward

THIS DOCUMENT CONTAINS INFORMATION WHICH IS PROPRIETARY TO STEWARD. NO PRODUCTION OR PUBLICATION OF THIS DOCUMENT IN WHOLE OR IN PART SHALL BE MADE WITHOUT WRITTEN AUTHORIZATION FROM STEWARD.

Date:	01/05/2006	DWG #:	35T1000-00H-E	Title:	35T1000-00H	REV:	E
Drawn By:	JRK						

REV	Description	ECN #	Date	INT
E	Chg coating description from Poly to Epoxy Add Kgs to weight		01/05/06	JRK