



UPC Code : 078477040782

Country Of Origin : Mexico

1755-2I

Decora Three Rocker Combination Switch

Individual Switches: 15 Amp, 120 Volt/Device Total: 20 Amp, 120 Volt. Decora Three Rocker Combination Switch w/ Grounding Lead Screw Terminals and Push-in Wiring.

Leviton's Decora Combination Switch is the perfect choice for any area in a home. Its simple, functional design allows you to save space wherever the switch is installed. Beautifully styled and part of the notable Decora line, the switch comes in a variety of popular colors. Its impact-resistant exterior ensures damage protection and a long service life.

Technical Information

Product Features

Actuator Material : Thermoplastic

Amperage : 15 A

Body Material : Thermoplastic

Color : Ivory

Feature : Single-Pole / Single-Pole / Single-Pole

Grounding : Grounding

Product Type : 3-Switch Combo

Standards and Certifications : UL/CSA

Strap Material : Steel

Termination : Quickwire Push-In

Type : Three Rocker Combination Switch

Voltage : 120 VAC

Warranty : 2-Year Limited

SPECIFICATION SUBMITTAL

JOB NAME:		CATALOG NUMBERS:	
<input type="text"/>		<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

