


MI0603M121R-10

**UNCONTROLLED
DOCUMENT**

PHYSICAL DIMENSIONS:

A	1.60 [.063]	$\pm$ 0.15	[.006]
B	0.80 [.031]	$\pm$ 0.15	[.006]
C	0.80 [.031]	$\pm$ 0.15	[.006]
D	0.36 [.014]	$\pm$ 0.15	[.006]




ELECTRICAL CHARACTERISTICS:


	Z @ 100MHz (Ω)	DCR (Ω)	Rated Current
Nominal	120		
Minimum	90		
Maximum	150	0.05	2500 mA

NOTES: UNLESS OTHERWISE SPECIFIED

1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS 7" REELS, 4000 PCS/REEL.
2. TERMINATION FINISH IS 100% TIN.
3. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
4. OPERATION TEMPERATURE TEMP: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$. (INCLUDING SELF-HEATING)





LAND PATTERNS FOR REFLOW SOLDERING



(For wave soldering, add 0.762
[.030] to this dimension)

RECOMMENDED SOLDERING CONDITIONS



DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.				Laird™						
				PROJECT/PART NUMBER:				REV		PART TYPE:		DRAWN BY:		
C	ADD OPERATING TEMPERATURE UPDATE LAIRD LOGO AND REFLOW CURVE			08/05/13	QU	MI0603M121R-10				C	CO-FIRE		TMB	
B	UPDATE COMPANY LOGO ADD ROHS			07/25/08	JRK	DATE: 04/05/04		SCALE: —		SHEET: 2 of 2				
A	ORIGINAL DRAFT			04/05/04	TMB	CAD # MI0603M121R-10-C		TOOL # —						
REV	DESCRIPTION			DATE	INT									