


Specifications: Military Unit

| | |
|-------------------------|-----------------------------------|
| Sound level Category | Medium Sound Level |
| Mode of Operation | Fast Warble |
| Mounting | Panel (see note B) |
| Voltage Rating | 6 to 28 Vdc |
| Frequency | 2900 Hz ±500 Hz |
| Loudness (Min. Voltage) | 70 dB(A) min. @ 2 FT and 6 Vdc |
| Loudness (Max Voltage) | 85 dB(A) min. @ 2FT and 28 Vdc |
| Current Draw | 4 mA Max @ 6 Vdc |
| Current Draw | 16 mA Max @ 28 Vdc |
| Min Pulse Rate (PPS) | 2 @ 6 Vdc |
| Max Pulse Rate (PPS) | 10 @ 16 Vdc |
| Duty Cycle (%) | 50 (Approx) |
| Storage Temperature | -65°C to +85°C |
| Operating Temperature | -40°C to +85°C |
| Weight (Typical) | 2.3 oz (65 g) |
| Housing | 6/6 Nylon, Color Black |
| Options | For other options contact factory |

Dimensions: Inches (mm)



NOTE A: TERMINALS-.032 BRASS TIN PLATED, TAPPED FOR #6-32 SCREW. TWO #6-32 NICKEL PLATED BRASS SCREWS INCLUDED. WILL ACCEPT 1/4" QUICK CONNECT.

NOTE B: MOUNTING- REMOVE KNURLED NUT AND INSERT THREADED FRONT THROUGH 1.25" HOLE PUNCHED IN PANEL, IF ORIENTATION IS NEEDED, NOTE LOCKING FLATS ON DRAWING. SCREW NUT BACK ON. DO NOT OVERTIGHTEN.

PRODUCES TWO TONES ALTERNATELY WHEN USED WITH ADDITIONAL CONTINUOUS UNIT