


PART NUMBER	CATALOG NUMBER	UPC CODE	DESCRIPTION
ORBOX001Z	RBOX1	0 79458 09453	LOW PROFILE MINI MODULE RB

PLACE FUSES (SEE BILL OF MAT'L) AND 00970038Z FUSE PULLER
IN PLASTIC RBOX-SMALL-8 (896-509) AS SHOWN ACCORDING TO THE ILLUSTRATION



AFFIX CONTENT LABEL RB1 (914-866) TO RIGHT SIDE OF PLASTIC RBOX-SMALL-8 (896-509).
AFFIX COO RB LABEL (914-865) CENTERED ON TOP OF PLASTIC RBOX-SMALL-8 LID.

AFFIX UPC LABEL (914-020) PRINTED TO GENERAL LABEL SPEC. LS-000004,
TO BOTTOM RIGHT BACK OF PLASTIC RBOX-SMALL-8.

SHRINK WRAP WITH 60 GAUGE CROVAC FILM OR EQUIVALENT.

NOTE: PACKAGER TO FURNISH SHRINK FILM.

PACK IN ANY APPROPRIATE OVERPACK CARTON FOR STOCK
LABEL WITH 914-183 PRINTED TO GENERAL LABEL SPEC. LS-000027

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED

-	914-183	LABEL 4" x 2"	1000	EAD
-	914-020	LABEL UPC	1000	EAD
-	914-865	COO RB LABEL	1000	EA
-	914-866	CONTENT LABEL RB1	1000	EA
-	896-509	PLASTIC RBOX-SMALL-8	1000	EA
-	00970038Z	ACS ATO/MINI PULLER: WHITE	1000	EA
-	0891030.NXS	30A LOW PROFIL MINI FUSE	10,000	EA
-	0891025.NXS	25A LOW PROFIL MINI FUSE	5000	EA
-	0891020.NXS	20A LOW PROFIL MINI FUSE	5000	EA
-	0891015.NXS	15A LOW PROFIL MINI FUSE	10,000	EA
-	0891010.NXS	10A LOW PROFIL MINI FUSE	10,000	EA
-	089107.5NXS	7.5A LOW PROFIL MINI FUSE	10,000	EA
-	0891005.NXS	5A LOW PROFIL MINI FUSE	5000	EA
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL			
COPIES TO		MATL SPEC	FINISH
1	9 18	DRW	SCALE
2	10 19	BJJ	12/3/03
3	12 20	CHK	DATE
4	13 21	APPD	DATE
5	14 23		RAW STK WT
6	15 33		LBS/M
7	16 43		TOLERANCE UNLESS OTHERWISE SPECIFIED
8	17 53		TWO PLACE DEC $\pm .01$
			THREE PLACE DEC $\pm .005$
			ANGULAR $\pm 1^\circ$
TITLE			
LOW PROFILE MINI MODULE RB			

LTR	REVISION	CHK	APD
-----	----------	-----	-----

0	001032EC-CHG 0897XXX.N TO 0891XXX.NXS 03/11/09 JCU		
---	--	--	--

LITTELFUSE [®]		REVISION	DRWG. NO.	FINAL
DES PLAINES, ILLINOIS 60016		B	ORBOX001Z	

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
CPK DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION
OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT
AND TRACKING TO BE DEFINED IN
LITTELFUSE INSPECTION INSTRUCTIONS.
CPK DENOTES CP DIMENSIONS, -MINIMUM CP VALUE
MUST BE WITHIN THE DIMENSIONAL LIMITATIONS
SHOWN ON DRAWING AND INITIALLY LOCATED TO
ALLOW FOR MAXIMUM TOOL LIFE.