

# Double Row Terminal Blocks

## Kulka® 600 GP Series

300 Volts AC/DC (Class B)

150 Volts AC/DC (Class C)



600 GP 07 PSB

### Specifications:

- Base, Phenolic, 150°C (UL RTI)
- Open Back Design (Insulator Strip required for Voltage Rating - see page 112)
- JJ (GDI-30F) Material Available
- Screws, #5-40 Binder Head, Phil-Slot, Brass
- Terminals, Plated Brass
- 1-22 Poles
- 3/8" Centers
- Wire Range With Wire Binding Screw  
#14 - #22 AWG – 15 Amps
- UL Recognized File No. XCFR2.E47811
- CSA Certified File No. LR19766
- **CE**
- RoHS Compliant

| Kulka®<br>Catalog # | # of poles | Dimensions |      |
|---------------------|------------|------------|------|
|                     |            | A          | B    |
| 600 GP 01 PSB       | 1          | 1.03       | 0.75 |
| 600 GP 02 PSB       | 2          | 1.41       | 1.13 |
| 600 GP 03 PSB       | 3          | 1.78       | 1.50 |
| 600 GP 04 PSB       | 4          | 2.16       | 1.88 |
| 600 GP 05 PSB       | 5          | 2.53       | 2.25 |
| 600 GP 06 PSB       | 6          | 2.91       | 2.63 |
| 600 GP 07 PSB       | 7          | 3.28       | 3.00 |
| 600 GP 08 PSB       | 8          | 3.66       | 3.38 |
| 600 GP 09 PSB       | 9          | 4.03       | 3.75 |
| 600 GP 10 PSB       | 10         | 4.41       | 4.13 |
| 600 GP 11 PSB       | 11         | 4.78       | 4.50 |
| 600 GP 12 PSB       | 12         | 5.16       | 4.88 |
| 600 GP 13 PSB       | 13         | 5.53       | 5.25 |
| 600 GP 14 PSB       | 14         | 5.91       | 5.63 |
| 600 GP 15 PSB       | 15         | 6.28       | 6.00 |
| 600 GP 16 PSB       | 16         | 6.66       | 6.38 |
| 600 GP 17 PSB       | 17         | 7.03       | 6.75 |
| 600 GP 18 PSB       | 18         | 7.41       | 7.13 |
| 600 GP 19 PSB       | 19         | 7.78       | 7.50 |
| 600 GP 20 PSB       | 20         | 8.16       | 7.88 |
| 600 GP 21 PSB       | 21         | 8.53       | 8.25 |
| 600 GP 22 PSB       | 22         | 8.91       | 8.63 |

mm=dim X 25.4

For electronic drawings or 2D/3D CAD data, submit request at [www.marathonsp.com/drawings.html](http://www.marathonsp.com/drawings.html)

### Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

| CATALOG # | PRODUCT DESCRIPTION           | PAGE REFERENCE |
|-----------|-------------------------------|----------------|
| MSP       |                               |                |
| KULKA     |                               |                |
| KT19      | Full Quick Connect (0° Flat)  | See Page 105   |
| KT20      | Full Quick Connect (45° Bend) | See Page 105   |
| KT21      | Full Quick Connect (90° Bend) | See Page 105   |
| KT25      | Half Quick Connect (0° Flat)  | See Page 105   |
| KT26      | Half Quick Connect (45° Bend) | See Page 105   |
| KT27      | Half Quick Connect (90° Bend) | See Page 105   |
| ST        | Full Solder                   | See Page 106   |
| 3/4 ST    | Half Solder                   | See Page 106   |
| Y         | Feed Thru Solder (.312)       | See Page 106   |
| YSY       | Feed Thru Solder (.500)       | See Page 106   |
| Z         | Lug Over the Side (.625)      | See Page 106   |
| J 600     | Line to Line Jumper           | See Page 107   |
| 600 RJ(S) | Multiple Position Jumper      | See Page 107   |
| 2004      | Feed Thru Solder              | See Page 109   |

Quick Connects: .020" x .187"

See pages 104-115 for terminal block accessories

