


PCB MOUNTING LEDs - Ø 5 mm

- Ideal for status indication, mounted on edge of card
- Multi-colour permutations available
- Reverse polarity options



108 SERIES

MLQ = 100



Ordering Information & Typical Technical Characteristics (Ta = 25°C)

Mean Time Between Failure = 100,000 Hours. Low Current Models 250,000 Hours. Luminous intensity figures refer to the unmodified discrete LED.

PART NUMBER	COLOUR	LENS	VOLTAGE DC Vopr	CURRENT DC Iopr	LUMINOUS INTENSITY lv@20mA	WAVE LENGTH l p	VIEWING ANGLE	OPERATING TEMP Topr	STORAGE TEMP Tstg
STANDARD INTENSITY									
108-505-01	Red	Coloured Diffused	2.0	2	15	625	Wide	-40 ~ + 85	-40 ~ + 85
108-511-01	Yellow		2.1	2	20	590			
108-514-01	Green		2.2	2	20	565			
108-505-04	Red		2.0*	20	15	625			
108-511-04	Yellow		2.1*	20	20	590			
108-514-04	Green		2.2*	20	20	565			
108-530-04	Red/Green	White Diffused	2.0/2.2*	20	30/20	625/565	Wide	-40 ~ + 85	-40 ~ + 85
108-581-20	Red	Coloured Diffused	5	10	40@10mA	625			
108-582-20	Yellow		5	10	25@10mA	590			
108-583-20	Green		5	10	25@10mA	565			
UNITS			Vdc	mA	mcd	nm		°C	°C

* = Voltage DC for 20mA product is Vf@20mA, not Vopr

Please contact our Sales office for multi-colour array part numbers.



CUSTOM DESIGN SERVICE