



Micro Commercial Components



Micro Commercial Components  
 20736 Marilla Street Chatsworth  
 CA 91311  
 Phone: (818) 701-4933  
 Fax: (818) 701-4939

# BSS138W

## N-Channel Enhancement Mode Field Effect Transistor


### Features

- Halogen free available upon request by adding suffix "-HF"
- High dense cell design for extremely low  $R_{DS(ON)}$
- Rugged and reliable
- Lead free product is acquired
- SOT-323 Package
- Marking Code: SS
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1


### Maximum Ratings @ 25°C Unless Otherwise Specified

Symbol	Parameter	Rating	Unit
$V_{DS}$	Drain-source Voltage	50	V
$I_D$	Drain Current-Continuous	0.22	A
$V_{GS}$	Gate-source Voltage	$\pm 20$	V
$P_D$	Total Power Dissipation	0.3	W
$R_{\theta JA}$	Thermal Resistance Junction to Ambient	417	$^{\circ}C/W$
$T_J$	Operating Junction Temperature	-55 to +150	$^{\circ}C$
$T_{STG}$	Storage Temperature	-55 to +150	$^{\circ}C$


### Internal Block Diagram



### SOT-323




1. GATE
2. SOURCE
3. DRAIN



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.071	.087	1.80	2.20	
B	.045	.053	1.15	1.35	
C	.083	.096	2.10	2.45	
D	.026 Nominal		0.65Nominal		
E	.047	.055	1.20	1.40	
F	.012	.016	.30	.40	
G	.000	.004	.000	.100	
H	.035	.039	.90	1.00	
J	.004	.010	.100	.250	
K	.006	.016	.15	.40	

### Suggested Solder Pad Layout



# BSS138W


## Electrical characteristics (T<sub>a</sub>=25°C unless otherwise noted)

Parameter	Symbol	Test Condition	Min	Typ	Max	Units
<b>Off characteristics</b>						
Drain-source breakdown voltage	V <sub>(BR)DSS</sub>	V <sub>GS</sub> = 0V, I <sub>D</sub> = 250μA	50			V
Gate-body leakage	I <sub>GSS</sub>	V <sub>DS</sub> = 0V, V <sub>GS</sub> = ±20V			±100	nA
Zero gate voltage drain current	I <sub>DSS</sub>	V <sub>DS</sub> = 50V, V <sub>GS</sub> = 0V			0.5	μA
		V <sub>DS</sub> = 30V, V <sub>GS</sub> = 0V			100	nA
<b>On characteristics</b>						
Gate-threshold voltage (note 1)	V <sub>GS(th)</sub>	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 1mA	0.80		1.50	V
Static drain-source on-resistance (note 1)	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10V, I <sub>D</sub> = 0.22A			3.50	Ω
		V <sub>GS</sub> = 4.5V, I <sub>D</sub> = 0.22A			6	
Forward transconductance (note 1)	g <sub>FS</sub>	V <sub>DS</sub> = 10V, I <sub>D</sub> = 0.22A	0.12			S
<b>Dynamic characteristics (note 2)</b>						
Input capacitance	C <sub>iss</sub>	V <sub>DS</sub> = 25V, V <sub>GS</sub> = 0V, f = 1MHz		27		pF
Output capacitance	C <sub>oss</sub>			13		
Reverse transfer capacitance	C <sub>rss</sub>			6		
<b>Switching characteristics</b>						
Turn-on delay time (note 1,2)	t <sub>d(on)</sub>	V <sub>DD</sub> = 30V, V <sub>DS</sub> = 10V, I <sub>D</sub> = 0.29A, R <sub>GEN</sub> = 6Ω			5	ns
Rise time (note 1,2)	t <sub>r</sub>				18	
Turn-off delay time (note 1,2)	t <sub>d(off)</sub>				36	
Fall time (note 1,2)	t <sub>f</sub>				14	
<b>Drain-source body diode characteristics</b>						
Body diode forward voltage (note 1)	V <sub>SD</sub>	I <sub>S</sub> = 0.44A, V <sub>GS</sub> = 0V			1.4	V


### Notes:

1. Pulse Test ; Pulse Width ≤ 300μs, Duty Cycle ≤ 2%.
2. These parameters have no way to verify.


**Output Characteristics**




**Transfer Characteristics**




**$R_{DS(ON)}$  —  $I_D$**




**$R_{DS(ON)}$  —  $V_{GS}$**



**$I_S$  —  $V_{SD}$**



**Threshold Voltage**





Micro Commercial Components

### Ordering Information :

Device	Packing
Part Number-TP	Tape&Reel: 3Kpcs/Reel

Note : Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

#### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp .** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp .** and all the companies whose products are represented on our website, harmless against all damages.

#### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

#### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

[www.mccsemi.com](http://www.mccsemi.com)