

INTERCONNECTS

SERIES 342 • .100" GRID BOARD STACKING HEADERS • SINGLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3




FIG. 4

- Series 342 interconnect header strips come in four heights with .018" dia. pluggable solder tails at both ends

342...591 uses pin #4259-1 (L = .210")

342...592 uses pin #4259-2 (L = .335")

342...593 uses pin #4259-3 (L = .585")

342...594 uses pin #4259-4 (L = .835")

See page 212 for details

- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 342...591	.018" / .018" Dia. Solder Tails												
	342-XX-1	-00-591000	Specify number of pins 01-64											
FIG. 2	Series 342...592	.018" / .018" Dia. Solder Tails												
	342-XX-1	-00-592000	Specify number of pins 01-64											
FIG. 3	Series 342...593	.018" / .018" Dia. Solder Tails												
	342-XX-1	-00-593000	Specify number of pins 01-64											
FIG. 4	Series 342...594	.018" / .018" Dia. Solder Tails												
	342-XX-1	-00-594000	Specify number of pins 01-64											
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264 <table><tr><td>SPECIFY PLATING CODE XX=</td><td>10 </td><td>90</td><td>40 </td><td></td></tr><tr><td>Pin Plating </td><td>10 μ" Au</td><td>200 μ" Sn/Pb</td><td>200 μ" Sn</td><td></td></tr></table>					SPECIFY PLATING CODE XX=	10	90	40		Pin Plating	10 μ" Au	200 μ" Sn/Pb	200 μ" Sn	
SPECIFY PLATING CODE XX=	10	90	40											
Pin Plating	10 μ" Au	200 μ" Sn/Pb	200 μ" Sn											