

| | | | |
|---|---|---|---|
| <h3>4011</h3> <p>4011-0-15-XX-30-XX-04-0 Press-fit in .057 mounting hole</p> | <h3>1801</h3> <p>1801-0-15-XX-30-XX-04-0 Press-fit in .057 mounting hole Shell is Ph. Br. Alloy 544 (B2)</p> | <h3>1001</h3> <p>1001-0-15-XX-3X-XX-04-0 Press-fit in .057 mounting hole</p> | <h3>0156</h3> <p>0156-0-18-XX-30-XX-04-0 Self-retention socket pin .038-.043 hole prior to soldering</p> |
|---|---|---|---|

| | | | |
|---|--|---|---|
| <h3>0255</h3> <p>0255-0-15-XX-30-XX-04-0 Solder mount in .022 min. mounting hole</p> | <h3>1109</h3> <p>1109-0-15-XX-30-XX-04-0 Hex press-fit in .057 plated thru hole</p> | <h3>3013</h3> <p>3013-0-15-XX-32-XX-04-0 Press-fit in .057 mounting hole</p> | <h3>0134</h3> <p>0134-0-15-XX-3X-XX-04-0 Press-fit in .057 mounting hole</p> |
|---|--|---|---|

| <h3>0132/0135</h3> <p>013X-0-15-XX-30-XX-04-0 Press-fit in .057 mounting hole</p> | <table border="1"> <thead> <tr> <th>Basic Part Number</th> <th>Length A</th> </tr> </thead> <tbody> <tr> <td>0132-0</td> <td>.273</td> </tr> <tr> <td>0135-0</td> <td>.183</td> </tr> </tbody> </table> | Basic Part Number | Length A | 0132-0 | .273 | 0135-0 | .183 | <h3>0133/0147</h3> <p>01XX-0-15-XX-30-XX-04-0 Press-fit in .059 mounting hole</p> | <table border="1"> <thead> <tr> <th>Basic Part Number</th> <th>Length A</th> </tr> </thead> <tbody> <tr> <td>0133-0</td> <td>.382</td> </tr> <tr> <td>0147-0</td> <td>.563</td> </tr> </tbody> </table> | Basic Part Number | Length A | 0133-0 | .382 | 0147-0 | .563 |
|--|---|-------------------|----------|--------|------|--------|------|--|---|-------------------|----------|--------|------|--------|------|
| Basic Part Number | Length A | | | | | | | | | | | | | | |
| 0132-0 | .273 | | | | | | | | | | | | | | |
| 0135-0 | .183 | | | | | | | | | | | | | | |
| Basic Part Number | Length A | | | | | | | | | | | | | | |
| 0133-0 | .382 | | | | | | | | | | | | | | |
| 0147-0 | .563 | | | | | | | | | | | | | | |

| | | |
|--|--|--|
| <h3>SPECIFICATIONS</h3> <p>SHELL MATERIAL: Brass Alloy 360, 1/2 Hard</p> <p>CONTACT MATERIAL: Beryllium Copper Alloy 172, HT</p> <p>DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°</p> | <p>ORDER CODE: XXXX - X - 1X - XX - 3X - XX - 04 - 0</p> <p>BASIC PART # →</p> <p>SPECIFY SHELL FINISH:</p> <p>01 200µ" TIN/LEAD OVER NICKEL</p> <p>80 200µ" TIN OVER NICKEL ◊</p> <p>15 10µ" GOLD OVER NICKEL ◊</p> <p>SPECIFY CONTACT FINISH:</p> <p>02 100µ" TIN/LEAD OVER NICKEL</p> <p>84 100µ" TIN OVER NICKEL ◊</p> <p>27 30µ" GOLD OVER NICKEL ◊</p> <p>SELECT CONTACT</p> <p>#30 or #32 CONTACT (DATA ON PAGES 218 & 219)</p> | |
|--|--|--|