







20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

- NOTES:
1. MATERIAL: SEE LEGEND
2. FINISH: SEE LEGEND
3. PRODUCT SPECIFICATION: PS-40-02
4. DIMENSIONS GIVEN ACROSS CENTERLINES ARE SYMMETRICAL ABOUT THOSE CENTERLINES WITHIN HALF THE TOTAL TOLERANCE.
5. CRIMP FOR 22 TO 26 GA. WIRE WITH MAX. INSULATION DIA. OF (.165)/.065
6. THIS PRODUCT CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.




SELECTIVE PLATING AREA



MAT'L: (.27)/.0106 THK
7258-*(*)- FORM
BLANK=BRASS
A=PHOS. BRONZE
BLANK= CHAIN PER DETAIL B
A=CHAIN PER DETAIL A
L= LOOSE

PLATING PER SDES- 88

(909) - HOT TIN DIP: (0.00254)/.000100 MIN.
(558) - SELECT GOLD: (0.00076)/.000030 MIN.
OVERALL GOLD FLASH: (0.00005)/.000002 MIN.
OVERALL NICKEL UNDERPLATE: (0.00127)/.000050 MIN.
(561) - SELECT GOLD: (0.00076)/.000030 MIN.
OVERALL NICKEL UNDERPLATE: (0.00127)/.000050 MIN.
(555) - SELECT GOLD: (0.00038)/.000015 MIN.
OVERALL NICKEL UNDERPLATE: (0.00076)/.000030 MIN.



REMOVE P/N'S		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
IEC NO: UCP2012-1821	2012/01/04	▽=0	mm	mm	INCH	MM/IN	DATE	---	---	INCH	---	---	---
DRWN: MSTRCH	2012/01/04	▽=0	3 PLACES ±	3 PLACES ±	±.010	JJS	12/03/87	---	---	---	---	---	---
CHKD: KIPPER	2012/01/04	▽=0	2 PLACES ±	2 PLACES ±	±.014	PATEL	12/03/87	---	---	---	---	---	---
APPR: FSWTH	2012/02/02	▽=0	1 PLACE ±	1 PLACE ±	±.036	LENZ	12/03/87	---	---	---	---	---	---
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		ANGULAR ±1/2°		MATERIAL NO.		SEE CHART		DOCUMENT NO.		SD-7258		SHEET NO.	
SIZE D		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		MATERIAL NO.		SEE CHART		DOCUMENT NO.		SD-7258		SHEET NO.	

	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	
	7258-(*)*			7258-A(*)*																	
M	PART NO.	ENG. NO.		PART NO.	ENG. NO.		PART NO.	ENG. NO.		PART NO.	ENG. NO(SUFFIX ONLY)		PART NO.	ENG. NO(SUFFIX ONLY)	VOID CKT.	PART NO.	ENG. NO(SUFFIX ONLY)	VOID CKT.			
	08-50-0183	7258-(P909)		08-04-0001	7258-A(999)																
	08-50-0185	7258-(P909)L		08-65-0121	7258-A(P56 I)	ES-276-P56 I															
	08-50-0283	7258-(P909)A		08-65-0122	7258-A(P56 I)L																
				08-56-0123	7258-A(P558)	MAKE FROM															
				08-56-0124	7258-A(P558)L	7258-A(P56 I)															
L																					
					7258-A(56 I)																
					7258-A(56 I)L																
				08-52-0124	7258-A(P909)																
				08-52-0125	7258-A(P909)L																
K				08-65-0126	7258-A(P555)	ES-276-P555															
				08-65-0127	7258-A(P555)L																
J																					
I																					
H																					
G																					
F																					
E																					
	COLUMN NO. 1	CON'T. IN COLUMN NO.	SHEET NO.	COLUMN NO. 2	CON'T. IN COLUMN NO.	SHEET NO.	COLUMN NO. 3	CON'T. IN COLUMN NO.	SHEET NO.	COLUMN NO. 4	CON'T. IN COLUMN NO.	SHEET NO.	COLUMN NO. 4	CON'T. IN COLUMN NO.	SHEET NO.	COLUMN NO. 4	CON'T. IN COLUMN NO.	SHEET NO.			
D																					
C																					
B																					
A																					

SEE SHEET 1

EC NO: UCP2012-1821

U

2012/01/04

2012/01/05

2012/02/02

DRW:MMSTROH

CHK:MKIPPER

APP:FSMTH

REV

DESCRIPTION

QUALITY SYMBOLS

▽=0

▽=0

▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

mm

INCH

4 PLACES ± --- ± ---

3 PLACES ± --- ± ---

2 PLACES ± --- ± ---

1 PLACE ± --- ± ---

ANGULAR ±1/2°

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

MM ONLY

DRAWN BY

JJS

DATE

12/07/187

CHECKED BY

PATEL

DATE

12/07/187

APPROVED BY

LENZ

DATE

12/07/187

MATERIAL NO.

SEE CHART

SIZE

D

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE

DESIGN UNITS

INCH

THIRD ANGLE PROJECTION

TITLE

TRIFURCON TERMINAL CRIMP TYPE

DOCUMENT NO.

SD-7258

SHEET NO.

2 OF 2