



**TRADE
TITAN**
INDUSTRIAL WORK CARTS

Heavy Duty Productivity

48-60-5010

48-60-5015



What You Need, Where You Need It, When You Need It

TRADE TITAN™ Industrial Work Carts

Designed specifically for the construction and maintenance trades, the Milwaukee Trade Titan Industrial Work Carts help get the job done faster and easier whether you are on the job, in the plant or in the shop.



48-60-5010
TradeTitan™ - Industrial Work Cart



48-60-5015
TradeTitan™ - Industrial Work Cart
with Locking Cabinet



Overall cart dimensions

Heavy Duty Mobility

Built from the ground up for durability and mobility. These carts will go wherever your job takes you.

- Heavy duty structural foam construction
- Steel reinforced base deck
- Industrial grade 6" x 2" rubber casters with total lock brakes
- Non-marking, round rubber tread for smooth, quiet performance
- 4" x 4-1/2" steel top caster plate and heavy duty 1/2" axles
- 26" cart width easily fits through standard doorways



Milwaukee Casters

6" x 2" wheels
4" x 4-1/2" top plate



Industrial Grade 6" x 2" Casters easily conquer rough terrain and jobsite environments.

Competitive Casters


5" x 1" wheels
2-1/2" x 3-5/8" top plate



Organized Storage/Security

These heavy duty mobile work carts will help you organize and store your tools, equipment and materials so that you have what you need, where you need it, when you need it.

- Dedicated storage areas for frequently used tools like a cordless drill and pipe benders.
- Large open storage area with a 4-1/2" sidewall keeps fasteners, fittings and small parts boxes secure and organized.
- Large cabinet and drawer for secure storage.
- Hooks to store extension cords, hoses and a Job Site radio.
- Heavy-duty cabinet latch and drawer can each be secured with a standard padlock.



Versatility / Productivity

The Trade Titan™ Work Carts can be customized for specific work applications with several trade accessories that mount to the front of the cart. Electrical, plumbing, mechanical and maintenance trades can set up their work cart to organize and handle the tools and materials that they use every day.

- The Removable Wire Spool Rack has three (3) heavy duty wire caddies that each hold up to one (1) network or four (4) 500' spools of 12 AWG wire. These caddies allow wire to be pulled when they are mounted to the cart or with the wire caddy on the floor.
- The Heavy Duty Tank and Fire Extinguisher Mounting Kit allows up to two (2) 'B' size Acetylene tanks and (1) 20 lb fire extinguisher to be securely mounted to the front of the cart.
- With a large 16" x 16" worksurface and a material cutting groove at a 38" work height, fabrication and cutting operations are comfortable and secure.
- The Heavy Duty 2-1/2" Chain Vise mounts in line to the molded in material cutting groove for applications that require material to be secured.
- A 6' ladder can be vertically stored on the extended front deck while still allowing the cart to pass through a standard 80" doorway.
- Nine stake holes in the top deck accept 3/4" conduit so that the user can create a pipe cart or a bar to mount plans from standard building material.



Heavy Duty System of Productivity

Durability - Organization - Versatility

Customized Cart for the Electrical Trades

Everything an electrician needs to do their job is stored and organized on the Trade Titan™ cart. Tools, supplies and equipment are all easily accessible, mobile and secure. Three removable wire caddies and a heavy duty chain vise make daily tasks quick and easy.



Trade Titan Open Cart

Wire Spool Rack

Chain Vise

Loaded Cart

Customized Cart for the Plumbing and Mechanical Trades

The Heavy Duty Tank and Fire Extinguisher Mounting Kit allow up to (2) 'B' size Acetylene tanks and (1) 20 lb fire extinguisher to be securely mounted to the front of the cart. The Tank Kit Includes (2) heavy duty mounting brackets and (1) regulator wrench.



Trade Titan Cabinet Cart

Tank & Extinguisher Kit


Chain Vise

Loaded Cart

48-60-5120 - Industrial Grade 6" x 2" Caster Set



- Includes (2) swivel casters and (2) rigid casters
- Total lock brakes on swivel casters lock swivel and rotation
- Non-marking, debris rejecting round rubber tread
- 450 lbs. load rating per caster



Industrial standard bolt pattern for heavy duty applications like gang boxes, pipe carts and supply carts

Specifications

Catalog #	Description	Net Weight	Ship Weight	L	W	H	Cube
Trade Titan™ Carts							
48-60-5010	Trade Titan™ - Industrial Work Cart	100.00 lbs.	110.50 lbs.	13.50"	52.00"	27.50"	11.17"
48-60-5015	Trade Titan™ - Industrial Work Cart with Cabinet	120.00 lbs.	133.00 lbs.	16.50"	52.00"	27.50"	13.65"
Trade Titan™ Accessories							
48-60-5100	Trade Titan™ Removable Wire Spool Rack	9.50 lbs.	10.00 lbs.	17.00"	8.00"	25.00"	1.97"
48-60-5105	Trade Titan™ Tank and Extinguisher Kit	4.50 lbs.	5.00 lbs.	17.00"	8.00"	3.00"	0.24"
48-60-5115	Trade Titan™ 2-1/2" Chain Vise	9.50 lbs.	10.00 lbs.	7.00"	9.00"	9.00"	0.33"
48-60-5120	Trade Titan™ HD 6" x 2" Caster Set	19.50 lbs.	20.00 lbs.	15.50"	13.50"	5.00"	0.61"

MILWAUKEE ELECTRIC TOOL CORPORATION

For More Information Call 1-800-SAWDUST (800-729-3878) • www.milwaukeetool.com