









20 CIRCUIT RIGHT ANGLE
HEADER ASSEMBLY SHOWN



DATECODE, SEE NOTE 6





HARNESS ASSEMBLY
SEE SALES DRAWING
SD-30700-120.



NOTES:

1. MATERIAL: HOUSING: SPS, GLASS FILLED, COLOR: SEE CHART.
TERMINAL: COPPER ALLOY.
PIN ALIGNMENT PLATE: MYLAR, COLOR: NATURAL (WHITE).
2. FINISHES: TERMINAL: TIN (Sn) OVERALL,
THICKNESS = 1.5 MICROMETER MINIMUM;
NICKEL (Ni) UNDERPLATE OVERALL.
3. PRODUCT SPECIFICATION: PS-30700-0001
4. PACKAGING SPECIFICATION : TUBE: PK-30907-227, TRAY: PK-30907-260
5. MATES WITH: SERIES 30700, SEE SALES DRAWING SD-30700-120.
6. DATECODE DESCRIPTION:
 - 1ST DIGIT: MACHINE ID# (ALWAYS WILL BE '2')
 - 2ND THROUGH 4TH DIGIT: DAY# OF THE CALENDAR YEAR (EXAMPLE: FEB. 3RD = '034')
 - 5TH DIGIT: LAST DIGIT OF THE CALENDAR YEAR (EXAMPLE: 1999 = '9')
 - 6TH THROUGH 7TH DIGIT: HOUR OF THE DAY.
7. RECOMMENDED OPTIONAL SCREW: M2 x 0.89, 6mm IN LENGTH, PAN COLLAR HEAD, 6 LOBE.
TORQUE: 7 NEWTON CENTIMETERS

BELOW VIEWS APPLY TO
30700-5067/8/9 PART NUMBERS



SEE ECN# UAU2001-0258 EC NO: UAU2014-1769 DRWN: JFISCHERO 2014/05/19 CHKD: APPR: RBAUMAN 2014/05/28	DESCRIPTION	QUALITY SYMBOLS ▽ - 0 ▽ C - 0	GENERAL TOLERANCES (UNLESS SPECIFIED)	SCALE 2:1		DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	REVISE ON CAD ONLY			
						DIMENSION STYLE		TITLE 6-20 CIRCUIT RIGHT ANGLE HEADER ASSEMBLY MOLEX INCORPORATED			
						MM ONLY					
						DRAWN BY DATE					
				mm		INCH					RCARLSON 01/03/20
4 PLACES ± --- ± ---		CHECKED BY DATE									
3 PLACES ± --- ± ---		CKRISHNA 01/03/27		MOLEX							
2 PLACES ± 0.13 ± ---		APPROVED BY DATE									
1 PLACE ± 0.25 ± ---		LGEIB 01/03/28		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
ANGULAR ± 1 °											
DRAFT WHERE APPLICABLE											
MUST REMAIN WITHIN DIMENSIONS											

