

CKT	A	B
4	18.80 .740	4.20 .165
6	23.00 .906	8.40 .331
8	27.20 1.071	12.60 .496
10	31.40 1.237	16.80 .661
12	35.60 1.402	21.00 .827
14	39.80 1.567	25.20 .992
16	44.00 1.733	29.40 1.157
18	48.20 1.898	33.60 1.323
20	52.40 2.063	37.80 1.488
22	56.60 2.229	42.00 1.654
24	60.80 2.394	46.20 1.819

- NOTES:
- MATERIAL: HOUSING: GLASS FILLED NYLON, UL94 V-0, BLACK
TERMINAL: PHOSPHOR BRONZE
BOARD RETENTION CLIP: BRASS
 - TERMINAL FINISH:
1 = 0.00254/.000100 MIN. BRIGHT TIN OVER 0.00127/.000050 MIN. NICKEL OVERALL
4 = 0.00076/.000030 MIN. GOLD IN CONTACT AREA, 0.00254/.000100 MIN. MATTE TIN IN TAIL AREA OVER 0.00127/.000050 MIN. NICKEL OVERALL
5 = 0.00254/.000100 MIN. MATTE TIN OVER 0.00127/.000050 MIN. NICKEL OVERALL
 - PRODUCT SPECIFICATION: PS-43879-001
 - PARTS ARE TRAY PACKED PER PK-43879-001
 - THIS PART MATES WITH RECEPTACLE NUMBERS 5557, 42474, 44516 AND HEADER NUMBER 42385.
 - PART ALLOWS FOR 1.27/.050 MAX. MIS-ALIGNMENT WITH MATING HOUSING IN ANY DIRECTION.
 - CONNECTOR ASSEMBLIES ARE NOT DESIGNED TO BE MATED AND UNMATED WHILE CIRCUITS ARE LIVE.
 - PART IS NOT DESIGNED FOR CURRENT SHARING.
 - DRILLED HOLE DIAMETER IS EQUIVALENT TO 5/64 STANDARD DRILL BIT.
 - PART CONFORMS TO CLASS "B" REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.
 - THIS HEADER REQUIRES A MOLEX INSERTION TOOL (62200-9400) TO PROPERLY INSTALL IT TO THE PCB.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

ADD 43879-6055 EC NO: 100771 DRWN: JBELL CHK'D: FSMITH APPR: FSMITH	2015/07/15	2015/07/17	2015/07/21	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 2.0 ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 0.25 1 PLACE ± 0.38 0 PLACES ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION UNITS	SCALE	 VERT. HDR. ASSY, BMI/CPI MAKE-FIRST/BREAK-LAST MINI-FIT BMI SERIES PRODUCT CUSTOMER DRAWING SERIES 43879 MATERIAL NUMBER SEE CHART CUSTOMER GENERAL MARKET DOCUMENT NUMBER SD-43879-061 DOC TYPE PSD DOC PART 000 SHEET NUMBER 1 OF 4	
				▽ = 0		HYBRID	2:1		
				▽ = 0		DRWN BY RFC_PLMMW DATE 2015/07/14			
				▽ = 0		CHK'D BY DATE			
			▽ = 0	APPR BY DATE 2015/07/14					
			▽ = 0	DRAWING SIZE B THIRD ANGLE PROJECTION					
			▽ = 0						



ITEM NO.	CKT. SIZE	TERMINAL VERSION REQUIRED AT EACH CIRCUIT LOCATION: SEE LEGEND BELOW																							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
43879-6001	10	M1	M1	S1	M1	M1	M1	M1	M1	M1	M1	-	-	-	-	-	-	-	-	-	-	-	-	-	
43879-6004	14	S1	S1	S1	S1	S1	S1	S1	M1	M1	M1	M1	M1	M1	S1	-	-	-	-	-	-	-	-	-	
43879-6005	18	S1	S1	S1	S1	S1	S1	S1	S1	S1	M1	M1	S1	S1	S1	S1	S1	S1	S1	-	-	-	-	-	
43879-6006	14	S1	S1	M1	S1	M1	S1	M1	S1	S1	S1	S1	S1	S1	S1	-	-	-	-	-	-	-	-	-	
43879-6008	14	S1	S1	M1	M1	S1	M1	S1	S1	S1	M1	M1	S1	S1	S1	-	-	-	-	-	-	-	-	-	
43879-6009	18	M1	M1	M1	M1	S1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	-	-	-	-	-	
43879-6010	6	S1	M1	M1	S1	M1	M1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
43879-6012	18	M4	M4	M4	M4	S4	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	-	-	-	-	-	
43879-6013	10	M4	S4	S4	S4	S4	M4	M4	S4	S4	M4	-	-	-	-	-	-	-	-	-	-	-	-		
43879-6014	10	S4	S4	M4	S4	S4	M4	M4	M4	S4	S4	-	-	-	-	-	-	-	-	-	-	-	-		
43879-6015	10	S4	S4	S4	S4	M4	S4	M4	S4	S4	M4	-	-	-	-	-	-	-	-	-	-	-	-		
43879-6016	10	S4	S4	M4	S4	M4	S4	M4	S4	S4	M4	-	-	-	-	-	-	-	-	-	-	-	-		
43879-6020	14	S4	S4	S4	M4	M4	M4	S4	S4	S4	S4	S4	S4	S4	S4	-	-	-	-	-	-	-	-		
43879-6022	24	M4	M4	M4	S4	S4	S4	M4	S4	S4	S4	S4	S4	M4	M4	M4	S4	S4	S4	S4	S4	S4	S4	S4	
43879-6025	18	M4	S4	S4	S4	S4	S4	S4	S4	S4	S4	S4	S4	M4	M4	M4	S4	S4	M4	-	-	-	-	-	
43879-6026	14	S1	S1	S1	M1	M1	S1	S1	S1	S1	S1	M1	M1	S1	S1	-	-	-	-	-	-	-	-	-	
43879-6027	14	M1	M1	M1	M1	M1	M1	S1	M1	M1	M1	M1	M1	M1	S1	-	-	-	-	-	-	-	-	-	
43879-6029	4	M1	M1	M1	M1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
43879-6030	14	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	-	-	-	-	-	-	-	-	-	

LEGEND

M = MAKE-FIRST/BREAK-LAST
S = STANDARD LENGTH

1 = BRIGHT TIN OVER NICKEL
4 = GOLD & TIN OVER NICKEL
5 = MATTE TIN OVER NICKEL

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

ADD 43879-6055 EC NO: 100771 DRWN: JBELL CHK'D: FSMITH APP'R: FSMITH REV: G13	2015/07/15	2015/07/17	2015/07/21	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 2.0 ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 0.25 1 PLACE ± 0.38 0 PLACES ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION UNITS	SCALE	 VERT. HDR. ASSY, BMI/CPI MAKE-FIRST/BREAK-LAST MINI-FIT BMI SERIES PRODUCT CUSTOMER DRAWING SERIES: 43879 MATERIAL NUMBER: SEE CHART CUSTOMER: GENERAL MARKET DOCUMENT NUMBER: SD-43879-061 DOC TYPE: PSD DOC PART: 000 SHEET NUMBER: 2 OF 4
				▽ = 0		HYBRID	2:1	
				▽ = 0		DRWN BY	DATE	
				▽ = 0		RFK_PLMMW	2015/07/14	
			▽ = 0	CHK'D BY	DATE			
			▽ = 0	APPR BY	DATE			
			▽ = 0	RFK_PLMMW	2015/07/14			
			▽ = 0	DRAWING SIZE	THIRD ANGLE PROJECTION			
			▽ = 0	B				



ITEM NO.	CKT. SIZE	TERMINAL VERSION REQUIRED AT EACH CIRCUIT LOCATION: SEE LEGEND BELOW																							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
43879-6031	18	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	-	-	-	-	-	-
43879-6032	24	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5
43879-6033	10	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	-	-	-	-	-	-	-	-	-	-	-	-	-	
43879-6034	14	S1	S1	S1	S1	S1	S1	S1	M1	M1	M1	S1	S1	S1	S1	-	-	-	-	-	-	-	-	-	
43879-6035	18	S1	S1	M1	S1	S1	S1	M1	S1	S1	S1	S1	M1	S1	S1	S1	M1	S1	S1	-	-	-	-	-	
43879-6036	14	M4	M4	M4	M4	S4	M4	S4	M4	M4	M4	M4	M4	M4	S4	-	-	-	-	-	-	-	-	-	
43879-6037	14	S4	S4	S4	S4	S4	S4	S4	M4	M4	M4	M4	M4	M4	S4	-	-	-	-	-	-	-	-	-	
43879-6038	24	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	S1	M1	M1	M1	M1	S1	M1	M1	S1
43879-6039	10	M5	M5	M5	M5	M5	M5	M5	M5	M5	M5														
43879-6041	24	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1	M1
43879-6042	18	S4	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	-	-	-	-	-	-
43879-6043	14	S4	S4	M4	M4	S4	M4	S4	S4	S4	M4	M4	S4	S4	S4	-	-	-	-	-	-	-	-	-	
43879-6044	10	M4	M4	M4	M4	M4	M4	M4	M4	V	V	-	-	-	-	-	-	-	-	-	-	-	-	-	
43879-6045	24	S4	S4	M4	M4	M4	M4	M4	M4	M4	M4	M4	M4	S4	S4	M4	M4	M4	M4	M4	M4	M4	M4	S4	
43879-6046	06	M4	M4	M4	S4	M4	M4	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
43879-6047	10	M1	S1	S1	M1	S1	M1	S1	S1	S1	S1	-	-	-	-	-	-	-	-	-	-	-	-	-	
43879-6048	14	M1	M1	M1	M1	S1	M1	M1	M1	M1	M1	M1	S1	M1	M1	-	-	-	-	-	-	-	-	-	
43879-6049	18	M1	S1	S1	S1	S1	S1	S1	S1	M1	M1	S1	S1	S1	S1	S1	S1	S1	M1	-	-	-	-	-	
43879-6054	18	M1	M1	S1	S1	S1	S1	S1	M1	M1	M1	M1	S1	M1	S1	S1	M1	M1	M1	-	-	-	-	-	

LEGEND

M = MAKE-FIRST/BREAK-LAST
S = STANDARD LENGTH

1 = BRIGHT TIN OVER NICKEL
4 = GOLD & TIN OVER NICKEL
5 = MATTE TIN OVER NICKEL

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

ADD 43879-6055 EC NO: 100771 DRWN: JBELL CHK'D: FSMITH APPR: FSMITH	2015/07/15	2015/07/17	2015/07/21	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 2.0 ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 0.25 1 PLACE ± 0.38 0 PLACES ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION UNITS	SCALE	 VERT. HDR. ASSY, BMI/CPI MAKE-FIRST/BREAK-LAST MINI-FIT BMI SERIES PRODUCT CUSTOMER DRAWING				
				▽ = 0 ▽ = 0 ▽ = 0		HYBRID	2:1		DRWN BY	DATE		
				▽ = 0 ▽ = 0 ▽ = 0					RFC_PLMMW	2015/07/14	CHK'D BY	DATE
				▽ = 0 ▽ = 0 ▽ = 0							APPR BY	DATE
				☒ = 0 ■ = 0 ▽ = 0		DRAWING SIZE	THIRD ANGLE PROJECTION	SERIES	MATERIAL NUMBER	CUSTOMER		
						B		43879	SEE CHART	GENERAL MARKET		
								DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER	
								SD-43879-061	PSD	000	3 OF 4	

