

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [45912-0008](#)
Status: **Active**
Overview: Edge Card Connectors
Description: 12.90mm Pitch EXTreme PowerEdge™, Mixed Power/Signal Card Edge Connector, Double Sided, 3 Segments (Power, Signal, Power Sequence), Press-Fit

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Edge Card Connectors
 Series [45912](#)
 Component Type Edgecard to PCB
 Overview [Edge Card Connectors](#)
 Product Name EXTreme PowerEdge™
 UPC 822350709880

Physical

(p)ower-(s)ignal Configuration 2p - 8s - 2p
 Circuits (Loaded) 12
 Circuits (maximum) 12
 Color - Resin Black
 Durability (mating cycles max) 250
 Entry Angle Vertical (Top Entry)
 Flammability 94V-0
 Keying to Mating Part N/A
 Material - Metal High Performance Alloy (HPA), Phosphor Bronze
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 6.896/g
 PC Tail Length 4.50mm
 PCB Thickness - Recommended 2.40mm
 Packaging Type Tray
 Pitch - Mating Interface 12.90mm
 Plating min - Mating 0.762µm
 Plating min - Termination 3.810µm
 Temperature Range - Operating -40°C to +105°C
 Termination Interface: Style Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact 3A, 40A
 Voltage - Maximum 250V

Material Info

Reference - Drawing Numbers

Sales Drawing RSD-45912-1001, SD-45912-001




image - Reference only

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[45912Series](#)

Mates With

1.58mm Double Sided Card Edge

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION