

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F




E

D

C


B

A



注記
NOTES

1. 材質
MATERIAL
りん青銅 (板厚: 0.2)
PHOSPHOR BRONZE (THICKNESS : 0.2)
2. メッキ仕様
TERMINAL PLATING
接点部 : 金メッキ 0.25 μ m MIN.
CONTACT AREA : GOLD 0.25 μ m MIN.
圧着部 : 錫メッキ 1.0 μ m MIN.
CRIMP AREA : TIN 1.0 μ m MIN.
下地メッキ : ニッケルメッキ 2 μ m MIN.
UNDER PLATE : NICKEL 2 μ m MIN.
3. 適用電線 : UL1007, AWG #24~28
APPLICABLE WIRE RANGE : UL1007, AWG #24~28
4. 被覆外径 : ϕ 1.6 MAX.
INSULATION EXTERNAL DIA : ϕ 1.6 MAX.
5. 適用ハウジング : 51238-****, 51239-****
APPLICABLE HOUSING : 51238-****, 51239-****



バラ状 LOOSE	56120-8528	56120-8***
連鎖状 CHAIN	56120-8428	
端子形状 TERMINAL CONFIGURATION	MATERIAL No.	MODEL No.

RELEASED EC NO: J2005-2545 DRWN: YSUGIURA01 2005/03/04 CHKD: MATANAKA 2005/03/07 APPR: NUKITA 2005/03/15 0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		10 UNDER	±0.2	DRAWN BY YSUGIURA	DATE 2005/03/03	TITLE COMPACT ROBOT CONN. (CRC) CRIMP SOCKET -LEAD FREE-			
		10 OVER 30 UNDER	±0.25	CHECKED BY MTANAKA	DATE 2005/03/03				
		30 OVER	±0.3	APPROVED BY NUKITA	DATE 2005/03/03	molex MOLEX INCORPORATED			
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.			SHEET NO.
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-56120-009		1 OF 1		
	REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							