


Home: Terminal Blocks >

Part Number: 39532-9708

5.08mm Pitch Eurostyle™ Horizontal PCB Header, with Reverse Imprinting, Surface Mount Compatible, Green Housing, Gold (Au) Plated, 8 Circuits



Series image - Reference only

Status:	OBSOLETE
Replacement:	Contact Molex
Series:	39532
Category:	Terminal Blocks

Go to [Part Detail](#)▼

CHECK DISTRIBUTOR INVENTORY

- [Add to My Parts](#)
- [Email this page](#)

Mates With Part(s):

[39530](#) Horizontal Plug, [39533](#) Vertical Plug, Most 5.08mm Pitch Industry Standard Plugs

Product Environmental Compliance

[EU ELV](#):Product not active

[EU RoHS](#):Product not active

[EU RoHS Phthalates](#):Product not active

[China RoHS](#):

[REACH SVHC](#):Product not active

[Low-Halogen Status](#):Product not active

[EU RoHS Certificate of Compliance \(PDF\)](#)

[Multiple Part Product Compliance Statements](#)
EU RoHS, REACH SVHC, & Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- *IPC 1752A Class C
- *IPC 1752A Class D
- *Molex Product Compliance Declaration

Questions on Product Environmental Compliance? Email ProductCompliance@molex.com

Request Molex's CMRT from conflictminerals@molex.com

Part Detail

COLLAPSE ALL

▼ General

Status	Obsolete
Category	Terminal Blocks
Series	39532
Application	N/A
Comments	with Reverse Imprinting
Component Type	PCB Header
Product Name	ESE, Eurostyle™ Pluggable
Type	Euro Block
UPC	822350522564

▼ Physical

Circuits (Loaded)	8
Entry Angle	N/A
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Horizontal
PC Tail Length	5.08mm
PCB Thickness - Recommended	3.20mm
Panel Mount	No
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Shrouded	Closed Ends
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +140°C
Wire Size AWG	N/A

▼ Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

▼ Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

UL	E48521
----	--------

▼ Solder Process Data

[Solderability Shelf Life Statement](#)

Lead-freeProcess Capability	N/A
-----------------------------	-----

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

- PRODUCTS**
- Antennas
 - Application Tooling
 - Cable Assemblies
 - Connected Lighting
 - Connectors
 - Copper Flex
 - Electrical Products
 - Industrial Automation
 - Membrane Switches
 - Optical Solutions
 - Printed Electronic Solutions

- QUICK LINKS**
- Company Information
 - Contact Molex
 - Cross-Reference
 - Koch Industries
 - Industries
 - Investor Relations
 - Literature
 - Molex Racing
 - Press Room / Press Releases
 - Product Index
 - Sitemap
 - Terms & Conditions

- RESOURCES**
- Supply Chain Transparency
 - Business Continuity
 - Compliance
 - ecocare
 - Feedback | Help
 - Jobs
 - Legal | Trademarks
 - Mobile Site
 - Supplier Portal
 - Privacy Policy
 - Tradeshows

STAY CONNECTED

