


	10		9		8		7		6		5		4		3		2		19077		
F	MATERIAL NO.	ENG. NO.	MATERIAL NUMBER TAPE MOUNTED	ENG. NO. TAPE MOUNTED	STUD SIZE	"S" ±.005/.127	"K" REF DIA	WIRE RANGE AWG / MM²	INSULATION COLOR	I.D. MIN	MWID										F
	190770001	SRA-829-06	190770002	SRA-829-06T	6	.146 (3.71)	.236 (5.99)	22-18/.25-1.3	RED	.062/1.57	.138/3.51										
	190770005	SRA-829-08	190770006	SRA-829-08T	8	.173 (4.39)	.263 (6.68)														
	190770007	SRA-829-10	190770008	SRA-829-10T	10	.198 (5.03)	.288 (7.32)														
	190770015	SRB-829-06	190770016	SRB-829-06T	6	.146 (3.71)	.236 (5.99)	16-14/1.0-2.6	BLUE	.086/2.18	.169/4.29										
	190770017	SRB-829-08	190770018	SRB-829-08T	8	.173 (4.39)	.263 (6.68)														
	190770019	SRB-829-10	190770020	SRB-829-10T	10	.198 (5.03)	.288 (7.32)														



SALES DRAWING

NOTES:

1. MATERIAL: BRASS.
PLATING: ELECTROPLATE TIN.
2. FERRULE: BRASS ELECTROPLATE TIN.
PLATING: ELECTROPLATE TIN.
3. INSULATION: NYLON.
4. MWID=MAXIMUM WIRE INSULATION DIA.
5. ALL DIMENSIONS IN INCHES (MM).

EC NO: ETC2004-0126 DRWN:DMYRICK 2004/01/06 CHKD:SBEITZEL 2004/01/06 APPR:RDEROSS 2004/01/07	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		REVISE ON CAD ONLY		
		 = 0  = 0	mm	INCH	DIMENSION STYLE IN/MM		TITLE AVIKRIMP STAR RING TONGUE TERMINALS  MOLEX INCORPORATED				
			4 PLACES ± --- ± ---	DRAWN BY DATE DMYRICK 03/12/22							
			3 PLACES ± --- ± .005	CHECKED BY DATE SBEITZEL 03/12/22							
			2 PLACES ± 0.13 ± .01	APPROVED BY DATE RDEROSS 03/12/22							
B	REV	1 PLACE ± 0.25 ± ---	ANGULAR ± 1/2°		MATERIAL NO.		DOCUMENT NO.	SHEET NO.			
		DRAFT WHERE APPLICABLE		SEE CHART		SD-19077-001	1 OF 1				
		MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							