


10 9 8 7 6 5 4 3 2 1


FOR 3~12CKTS.



FOR 13~17CKTS.

(ONLY COVER SHAPE IS DIFFERENT FROM 3~12CKTS.)

TRADE MARK



NOTES: 1. MATERIAL

TERMINAL: PHOS-BRO, TIN-PLATED. (t=0.254)

HOUSING: PBT(15%G.F.), UL94V-0

G.E. PLASTICS JAPAN LTD.

VALOX DR-48 UL FILE NO. E45587

COVER: PBT(30%G.F.), UL94V-0

G.E. PLASTICS JAPAN LTD.

VALOX 420-SEO UL FILE NO. E45587





2. APPLICABLE WIRE

1.5 PITCH RIBBON CABLE


(UL2468, AWG#24~#26 TOP-COATED WIRE)

3. THE CABLE STRIPED AS SHOWN IN THE FIG.,

* (MARKED INSULATION) PART SHOULD NOT BE PUSHED AND SLID DIRECTLY BY THE COVER, BECAUSE THE COVER MAY BE POSSIBLY PUSHED DOWN.



RECOMMENDED WIRE DIM.



30	24	52004-1710	17
28.5	22.5	-1610	16
27	21	-1510	15
25.5	19.5	-1410	14
24	18	-1310	13
22.5	16.5	-1210	12
21	15	-1110	11
19.5	13.5	-1010	10
18	12	-0910	9
16.5	10.5	-0810	8
15	9	-0710	7
13.5	7.5	-0610	6
12	6	-0510	5
10.5	4.5	-0410	4
9	3	-0310	3
IB	A	52004-0310	3
		ENG. NO.	極数

REVISED ECNO: J2004-4815 T DRAWN: IIDA CHKD: TAKASE APPR: JIM YAZAW 2004/08/05 2004/08/05 2004/08/17	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		10 UNDER	±0.2	DRAWN BY SKUNISHI	DATE 86/08/27	TITLE 1.5 WIRE TRAP CONN.			
		10 OVER 30 UNDER	±0.25	CHECKED BY HII	DATE 93/01/18				
		30 OVER	±0.3	APPROVED BY MFUKUSHIMA	DATE 93/01/18				
		ANGULAR ±3 °		MATERIAL NO. SEE CHART		DOCUMENT NO. SD-52004-**10			SHEET NO. 1 OF 2
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

