







4 CIRCUIT SHOWN



1. MATERIAL: SEE TABLE
2. INCH DIMENSIONS ARE SHOWN IN BRACKETS [XXX].
3. 'XX' REFERS TO THE QUANTITY OF CIRCUITS.
4. ALL COMPONENTS ARE ROHS COMPLIANT.



INITIAL RELEASE EC NO: ETC2007-0073 2006/09/28 DRWN:EHILE 2006/09/28 CHKD:JMACNEIL 2006/09/29 APPR: JMACNEIL DESCRIPTION REV					QUALITY SYMBOLS ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2:1		DESIGN UNITS INCH		THIRD ANGLE PROJECTION	
6	XX	SCREW&WASHER, 6-32X.250, PAN, PH/SL (-50 OPTION)	STEEL	ZN, CLEAR CHROMATE	4 PLACES ± --- ± ---		INCH ± ---		DRAWN BY EHILE DATE 2006/09/13		TITLE 9.53MM [.375] SR BTS ASSY, INSULATED TURRET TERMINAL W/MTG MOLEX MOLEX INCORPORATED					
5	XX	SCREW, 6-32X.250, BHD, PHIL-SLOT (-49 OPTION)	BRASS	NICKEL	3 PLACES ± --- ± .005		± .005		CHECKED BY JMACNEIL DATE 2006/09/13							
4	XX	SCREW, 6-32X.250, BHD, PHIL-SLOT (STANDARD)	STEEL	ZN, CLEAR CHROMATE	2 PLACES ± 0.13 ± .01		± .01		APPROVED BY JMACNEIL DATE 2006/09/13							
3	XX	TERMINAL, SOLDER TURRET	BRASS	TIN	1 PLACE ± 0.25 ± ---		± ---		MATERIAL NO. SEE CHART		DOCUMENT NO. SD-38720-010		SHEET NO. 1 OF 2			
2	XX	MOUNTING PLATE	BRASS	NICKEL	ANGULAR ± 2 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
1	1	INSULATOR, SR, W/MTG	THERMOPLASTIC	BLACK												
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH												

