



FEATURES SELECTION GUIDE






CIRCUIT SIZE	FEATURES				
	FRICTION LOCKS		③ DUAL SIDE SLOTS	④ CENTER POLARIZATION	SHEET NO
	① DUAL	②CENTER			
4 TO 6	N.A	N.A	YES	N.A	2 - 3
	N.A	YES	YES	N.A	
8 TO 12	N.A	N.A	YES	YES	4 - 5
	N.A	YES	YES	N.A	
14 TO 50	YES	N.A	YES	YES	6 - 9
	N.A	N.A	YES	YES	





PACKAGING SPECIFICATION TABLE

TAPE AND REEL PACKAGING	PK-87831-300
TUBE STANDARD PACKAGING	PK-87831-001
TUBE NON-STANDARD PACKAGING FOR: 87833-0861 87833-1420	PK-87831-002


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
EC NO: 727481 DRWN: DANUSA CHK'D: DANUSA APPR: MIRAMAKRISHNA	2022/11/07 2022/11/07 2022/11/07	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex® MILLIGRID, 2MM PITCH SHROUDED HEADER R/A, THROUGH HOLE							
					MM		NTS									
					DRWN BY		DATE									
					GMENARLY		2015/09/29									
		4 PLACES ± ±			CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING							
		3 PLACES ± ±			CGOH		2015/10/30									
		2 PLACES ± 0.2 ±			APPR BY		DATE									
		1 PLACES ± ±			KHLIM		2015/11/03									
		0 PLACES ± ±			DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER			CUSTOMER		
		ANGULAR TOL ± 3.0			A3				87833		SEE TABLE			GENERAL MARKET		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER			
A14		REV					SD-87833-0001		PSD		001		1 OF 9			



4 TO 6 CIRCUITS




ISO VIEW OF HEADER
DUAL SIDE SLOTS











RECOMMENDED PCB LAYOUT

NOTES:

1. MATERIALS:
HOUSING: 30% GF, NYLON, UL94V-0, COLOR: BLACK.
PIN: 0.50mm SQ. PHOSPHOR BRONZE.
2. FINISHES: REFER TO PLATING OPTIONS.
3. PRODUCT SPECIFICATION: PS-87831-027
4. PACKAGING SPECIFICATION: SEE PACKAGING SPECS TABLE ON SHEET 1
5. MATES WITH: A. MOLEX CRIMP RECEPTACLE HOUSING: 51110 SERIES AND CRIMP TERMINAL: 50394 SERIES.
B. MOLEX 2MM MILLIGRID DUAL ROW IDT: 87568 SERIES.
C. MOLEX 2MM MILLIGRID DUAL ROW RECEPTACLE: 79107 (GOLD PLATED), 78787 (TIN PLATED)
6. FOR ILLUSTRATION PURPOSE, 6 CIRCUITS HEADER IS SHOWN.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
EC NO: 727481 DRWN: DANUSA CHK'D: DANUSA REV APPR: MIRAMAKRISHNA	2022/11/07 2022/11/07 2022/11/07	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex®		
			MM	INCH	MM		NTS				
		4 PLACES	±	±	DRWN BY		DATE		MILLIGRID, 2MM PITCH SHROUDED HEADER R/A, THROUGH HOLE		
		3 PLACES	±	±	GMENARLY		2015/09/29				
		2 PLACES	± 0.2	±	CHK'D BY		DATE				
		1 PLACES	±	±	CGOH		2015/10/30				
		0 PLACES	±	±	APPR BY		DATE				
		ANGULAR TOL ± 3.0			KHLIM		2015/11/03		PRODUCT CUSTOMER DRAWING		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DRAWING SIZE		THIRD ANGLE PROJECTION				
		A3					SERIES	MATERIAL NUMBER		CUSTOMER	
A14			REV	87833	SEE TABLE		GENERAL MARKET				
					DOCUMENT NUMBER		DOC TYPE	DOC PART	SHEET NUMBER		
					SD-87833-0001		PSD	001	2 OF 9		


8 TO 12 CIRCUITS



- NOTES:
1. MATERIALS:
HOUSING: 30% GF, NYLON, UL94V-0, COLOR: BLACK
PIN: 0.50mm SQ. PHOSPHOR BRONZE.
 2. FINISHES: REFER TO PLATING OPTIONS.
 3. PRODUCT SPECIFICATION: PS-87831-027
 4. PACKAGING SPECIFICATION: SEE PACKAGING SPECS TABLE ON SHEET 1
 5. MATES WITH: A. MOLEX CRIMP RECEPTACLE HOUSING: 51110 SERIES AND CRIMP TERMINAL: 50394 SERIES.
B. MOLEX 2mm MILLIGRID DUAL ROW IDT: 87568 SERIES.
C. MOLEX 2mm MILLIGRID DUAL ROW RECEPTACLE: 79107 (GOLD PLATED), 78787 (TIN PLATED)
 6. FOR ILLUSTRATION PURPOSE, 8 CIRCUIT HEADER IS SHOWN.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

EC NO: 727481 DRWN: DANUSA CHK'D: DANUSA APPR: MRAMAKRISHNA		2022/11/07		GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex®								
		2022/11/07					MM		NTS										
		2022/11/07				MM		INCH		DRWN BY		DATE		MILLIGRID, 2MM PITCH SHROUDED HEADER R/A, THROUGH HOLE					
				4 PLACES		±		±		GMENARLY		2015/09/29							
				3 PLACES		±		±		CHK'D BY		DATE							
				2 PLACES		± 0.2		±		CGOH		2015/10/30							
				1 PLACES		±		±		APPR BY		DATE							
				0 PLACES		±		±		KHLIM		2015/11/03							
														PRODUCT CUSTOMER DRAWING					
																SERIES 87833 MATERIAL NUMBER SEE TABLE CUSTOMER GENERAL MARKET			
																DOCUMENT NUMBER SD-87833-0001 DOC TYPE PSD DOC PART 001 SHEET NUMBER 4 OF 9			



		9		8		7		6		5		4		3		2		1																					
14 TO 24 CIRCUITS																																							
E	CKT SIZE	ASSY. P/N WITHOUT KAPTON IN TUBE	ASSY. P/N WITH KAPTON IN TUBE	ASSY. P/N WITH KAPTON IN T&R	ASSY. P/N WITHOUT KAPTON IN T&R	PLATING OPTIONS	FRICTION LOCKS		DUAL SIDE SLOTS	CENTER	DIMENSION																												
							DUAL	CENTER			A	B	C	D	E	F	G (SOLDER TAIL)																						
	14	87833-1419	N.A	N.A	N.A	1	YES	N.A	YES	YES	16.65	12.00	15.00	14.85	8.00	N.A	2.16																						
		87833-1420	N.A	N.A	N.A	2																																	
		87833-1421	N.A	N.A	N.A	3																																	
		87833-5320	N.A	N.A	N.A	2	YES	N.A	YES	YES							3.18																						
		87833-5321	N.A	N.A	N.A	3																																	
		87833-1436	N.A	N.A	N.A	3												YES	N.A	YES	YES	3.50																	
N.A	N.A	87833-7420	N.A	2	YES	N.A	YES	YES	1.70																														
D	16	87833-1619	N.A	N.A	N.A	1	YES	N.A	YES	YES	18.65	14.00	17.00	16.85	10.00	N.A	2.16																						
		87833-1620	N.A	N.A	N.A	2																																	
		87833-1621	N.A	87833-7821	N.A	3												YES	N.A	YES	YES	3.18																	
		87833-6120	N.A	87833-7120	N.A	2																																	
C	18	87833-1819	N.A	N.A	N.A	1	YES	N.A	YES	YES	20.65	16.00	19.00	18.85	12.00	N.A	2.16																						
		87833-1820	N.A	N.A	N.A	2																																	
		87833-1821	N.A	N.A	N.A	3												YES	N.A	YES	YES	3.18																	
		87833-6220	N.A	N.A	N.A	2																																	
B	20	87833-2019	N.A	N.A	N.A	1	YES	N.A	YES	YES	22.65	18.00	21.00	20.85	14.00	N.A	2.16																						
		87833-2020	N.A	87833-7220	N.A	2																																	
		87833-2021	N.A	N.A	N.A	3																																	
		87833-6520	N.A	N.A	N.A	2	YES	N.A	YES	YES							3.18																						
		87833-6521	N.A	N.A	(A14) 87833-2037	3																																	
		87833-2036	N.A	N.A	N.A	3												YES	N.A	YES	YES	3.50																	
A	22	87833-2219	N.A	N.A	N.A	1	YES	N.A	YES	YES	24.65	20.00	23.00	22.85	16.00	N.A	2.16																						
		87833-2220	N.A	N.A	N.A	2																																	
		87833-2221	N.A	N.A	N.A	3																																	
A	24	87833-2419	N.A	N.A	N.A	1	YES	N.A	YES	YES	26.65	22.00	25.00	24.85	18.00	N.A	2.16																						
		87833-2420	N.A	87833-7020	N.A	2																																	
		87833-2421	N.A	N.A	N.A	3																																	
		87833-7320	N.A	N.A	N.A	2	YES	N.A	YES	YES							2.00																						
		87833-2436	N.A	N.A	N.A	3	YES	N.A	YES	YES							3.50																						
		87833-6920	N.A	N.A	N.A	2	YES	N.A	YES	YES							3.27																						
PLATING OPTIONS: 1 - 0.05-0.13µm/2-5µin GOLD IN CONTACT AREA AND 1.88µm/75µin MIN. MATTE TIN IN SOLDER TAIL AREA OVER 1.27µm/50µin MIN. NICKEL OVERALL. 2 - 0.38µm/15µin MIN. GOLD IN CONTACT AREA AND 1.88µm/75µin MIN. MATTE TIN IN SOLDER TAIL AREA OVER 1.27µm/50µin MIN. NICKEL OVERALL. 3 - 0.76µm/30µin MIN. GOLD IN CONTACT AREA AND 1.88µm/75µin MIN. MATTE TIN IN SOLDER TAIL AREA OVER 1.27µm/50µin MIN. NICKEL OVERALL. THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION EC NO: 727481 DRWN: DANUSA CHK'D: DANUSA REV APPR: MIRAMAKRISHNA 2022/11/07 2022/11/07 2022/11/07 GENERAL TOLERANCES (UNLESS SPECIFIED) MM INCH 4 PLACES ± ± 3 PLACES ± ± 2 PLACES ± 0.2 ± 1 PLACES ± ± 0 PLACES ± ± ANGULAR TOL ± 3.0 DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DIMENSION UNITS MM SCALE NTS DRWN BY DATE GMENARLY 2015/09/29 CHK'D BY DATE CGOH 2015/10/30 APPR BY DATE KHLIM 2015/11/03 DRAWING SIZE THIRD ANGLE PROJECTION A3 SERIES MATERIAL NUMBER CUSTOMER 87833 SEE TABLE GENERAL MARKET DOCUMENT NUMBER DOC TYPE DOC PART SHEET NUMBER SD-87833-0001 PSD 001 7 OF 9 RELEASE STATUS P1 RELEASE DATE 2022/11/07 17:03:16 <tr><td colspan="2"></td><td colspan="2">9</td><td colspan="2">8</td><td colspan="2">7</td><td colspan="2">6</td><td colspan="2">5</td><td colspan="2">4</td><td colspan="2">3</td><td colspan="2">2</td><td colspan="2">1</td></tr>																						9		8		7		6		5		4		3		2		1	
		9		8		7		6		5		4		3		2		1																					

[illegible]

40 TO 50 CIRCUITS																	
E	CKT SIZE	ASSY. P/N WITHOUT KAPTON IN TUBE	ASSY. P/N WITH KAPTON IN TUBE	ASSY. P/N WITH KAPTON IN T&R	ASSY. P/N WITHOUT KAPTON IN T&R	PLATING OPTIONS	FRICTION LOCKS		DUAL SIDE SLOTS	CENTER POLARIZATI ON	DIMENSION						
							DUAL	CENTER			A	B	C	D	E	F	G (SOLDER TAIL)
	40	87833-4019	N.A	N.A	N.A	1	YES	N.A	YES	YES	42.65	38.00	41.00	40.85	34.00	N.A	2.16
		87833-4020	N.A	N.A	N.A	2											
87833-4021		N.A	N.A	N.A	3												
42	87833-4219	N.A	N.A	N.A	1	YES	N.A	YES	YES	44.65	40.00	43.00	42.85	36.00	N.A	2.16	
	87833-4220	N.A	N.A	N.A	2												
	87833-4221	N.A	N.A	N.A	3											YES	N.A
	87833-4222	N.A	87833-4322	87833-4223	3												
44	87833-4419	N.A	N.A	N.A	1	44.65	40.00	43.00	42.85	2.16	42.00	45.00	44.85	38.00	N.A	2.16	
	87833-4420	N.A	N.A	N.A	2												
	87833-4421	N.A	N.A	N.A	3												
	87833-4424	N.A	N.A	N.A	2	N.A	N.A	YES	YES								2.92
	87833-4425	N.A	N.A	N.A	3												
46	87833-4619	N.A	N.A	N.A	1	YES	N.A	YES	YES	48.65	44.00	47.00	46.85	40.00	N.A	2.16	
	87833-4620	N.A	N.A	N.A	2												
	87833-4621	N.A	N.A	N.A	3												
48	87833-4819	N.A	N.A	N.A	1	YES	N.A	YES	YES	50.65	46.00	49.00	48.85	42.00	N.A	2.16	
	87833-4820	N.A	N.A	N.A	2												
	87833-4821	N.A	N.A	N.A	3												
50	87833-5019	N.A	N.A	N.A	1	YES	N.A	YES	YES	52.65	48.00	51.00	50.85	44.00	N.A	2.16	
	87833-5020	N.A	N.A	N.A	2												
	87833-5021	N.A	N.A	N.A	3												
PLATING OPTIONS: 1 - 0.05-0.13µm/2-5µin GOLD IN CONTACT AREA AND 1.88µm/75µin MIN. MATTE TIN IN SOLDER TAIL AREA OVER 1.27µm/50µin MIN. NICKEL OVERALL. 2 - 0.38µm/15µin MIN. GOLD IN CONTACT AREA AND 1.88µm/75µin MIN. MATTE TIN IN SOLDER TAIL AREA OVER 1.27µm/50µin MIN. NICKEL OVERALL. 3 - 0.76µm/30µin MIN. GOLD IN CONTACT AREA AND 1.88µm/75µin MIN. MATTE TIN IN SOLDER TAIL AREA OVER 1.27µm/50µin MIN. NICKEL OVERALL.																	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
A14	REV	EC NO: 727481 DRWN: DANUSA CHK'D: DANUSA APPR: MIRAMAKRISHNA	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex®							
				MM	INCH	MM	NTS										
			4 PLACES	±	±	DRWN BY		DATE		MILLIGRID, 2MM PITCH SHROUDED HEADER R/A, THROUGH HOLE							
			3 PLACES	±	±	GMENARLY		2015/09/29									
			2 PLACES	± 0.2	±	CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING							
			1 PLACES	±	±	CGOH		2015/10/30									
			0 PLACES	±	±	APPR BY		DATE		SERIES MATERIAL NUMBER CUSTOMER 87833 SEE TABLE GENERAL MARKET							
ANGULAR TOL ± 3.0			KHLIM		2015/11/03												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DRAWING SIZE		THIRD ANGLE PROJECTION		DOCUMENT NUMBER DOC TYPE DOC PART SHEET NUMBER SD-87833-0001 PSD 001 9 OF 9										
A3		3															

RELEASE STATUS	P1	RELEASE DATE	2022/11/07	17:03:16
9		8		7
6		5		4
3		2		1