



FOR 3~12CKTS.



FOR 13~17CKTS.

(ONLY COVER SHAPE IS DIFFERENT FROM 3~12CKTS.)



NOTES: 1. MATERIAL

TERMINAL: PHOS-BRO, TIN-PLATED. (t=0.254)
HOUSING: PBT(15%G.F.), UL94V-0
G.E. PLASTICS JAPAN LTD.
VALOX DR-48 UL FILE NO. E45587
COVER: PBT(30%G.F.), UL94V-0
G.E. PLASTICS JAPAN LTD.
VALOX 420-SEO UL FILE NO. E45587






2. APPLICABLE WIRE

1.5 PITCH RIBBON CABLE


(UL2468, AWG#24~#26 TOP-COATED WIRE)

3. THE CABLE STRIPED AS SHOWN IN THE FIG.,

* (MARKED INSULATION) PART SHOULD NOT BE PUSHED AND SLID DIRECTLY BY THE COVER, BECAUSE THE COVER MAY BE POSSIBLY PUSHED DOWN.



RECOMMENDED WIRE DIM.



30	24	52004-1710	17
28.5	22.5	-1610	16
27	21	-1510	15
25.5	19.5	-1410	14
24	18	-1310	13
22.5	16.5	-1210	12
21	15	-1110	11
19.5	13.5	-1010	10
18	12	-0910	9
16.5	10.5	-0810	8
15	9	-0710	7
13.5	7.5	-0610	6
12	6	-0510	5
10.5	4.5	-0410	4
9	3	-0310	3
IB	A	52004-0310	3
		ENG. NO.	極数

REVISED ECNO: J2004-4815 DRAWN: DA CHKD: TAKASE APPR: JIM YAZAW 2004/08/05 2004/08/05 2004/08/17	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1 DESIGN UNITS METRIC THIRD ANGLE PROJECTION
	10 UNDER	±0.2	DRAWN BY	DATE	
	10 OVER 30 UNDER	±0.25	SKUNISHI	86/08/27	
	30 OVER	±0.3	CHECKED BY	DATE	
DESCRIPTION REV	ANGULAR	±3°	APPROVED BY	DATE	TITLE 1.5 WIRE TRAP CONN. MOLEX INCORPORATED DOCUMENT NO. SD-52004-**10 SHEET NO. 1 OF 2
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MFUKUSHIMA	93/01/18	
	SEE CHART		MATERIAL NO.		
	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SIZE	A3	

EN-02JA(021)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[52004-0510](#)