



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG


REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1369	C	Bulk Items Added	JWM	10/21/03	JC	10/21/03	JC	10/21/03
1745	D	Oper. temp corrected	JWM	7/2/04	JC	7/2/04	JC	7/2/04

NOTES:


1. Material Electro-Tin Plated Copper
2. Insulated Terminals: Nylon 6/6 (UL94V-2)
Operating Temp: -40°F to 221°F (-40°C~105°C)
3. Voltage Rating: 600V



Style 1



Style 2



Style 3

LISTED



E58918



LR22190M6

OSHA
Acceptable

SPC Type No.	Wire Range (AWG)	Mates with Male Tab Width (W) x Thickness	L	B	T	M	U	Insulation Material	Style	Package Qty
CMS-DY-1025	12 ~ 10	.250 x .032	1.05	.25	.185	.25	.032	Nylon - Yellow	1	50
SPC3881										500
CMS-DY-1425	16 ~ 14	.250 x .032	.94		.085	.170		Nylon - Blue	1	100
SPC3880										1000
CMS-TO-1425	16 ~ 14	.250 x .032	.73		.085	NA	Non-Insulated	2	100	
SPC3868									1000	
CMS-TO-1818	22 ~ 18	.187 x .020	.64	.24	.080	NA		2	100	
SPC3866						1000				
CMS-TO-1825	22 ~ 18	.250 x .032	.73	.25	.065	NA	.032	3	100	
SPC3867						1000				

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
Tolerances: Unless
Otherwise Specified:
.X = ±.015
.XX = ±.010
.XXX = ±.005

DRAWN BY:
JC
CHECKED BY:
JOHN COLE
APPROVED BY:
JL
DATE:
3/11/91
DATE:
12/11/91
DATE:
12/11/91

DRAWING TITLE:
Butted Seam Male Disconnects

SIZE: A
DWG. NO.: TA-483
ELECTRONIC FILE: TA-483.dwg
REV: D
SCALE: NTS
U.O.M.: INCHES [mm]
SHEET: 1 OF 1