


ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED			Jagan		KK	



SPECIFICATION

- 1.Rated Voltage 3.0V
- 2.Operating Voltage 2.0~4.0 V
- 3.Max.Rated Current 100mA
- 4.Coil Resistance $12 \pm 3 \Omega$
- 5.Coil Impedance 40Ω
- 6.Min.Sound Pressure Level 78dB/10cm
- 7.Resonant Frequency 4000Hz
- 8.Case Material/Color LCP 6130/Black
- 9.Operating Temperature $-30 \sim +70^{\circ}\text{C}$
- 10.Store Temperature $-40 \sim +85^{\circ}\text{C}$

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on Information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

Veena

DATE:

24/05/10

CHECKED BY:

Jagan

DATE:

24/05/10

APPROVED BY:

KK

DATE:

07/06/10

DRAWING TITLE:

Magnetic Transducer

SIZE
A

DWG NO.

MCSMT-G5030A1-3712

ELECTRONIC FILE

25R0970

REV
A

SCALE: NTS

U.O.M.: mm

SHEET: 1 OF 1