






WAFER: 15% GLASS FILLED POLYESTER
TO UL 94V-0.
COLOUR: BLACK.

PINS: (0.650)/.0255 SQ.
BRASS WIRE.
PLATED AS PER
SHEETS 2 TO 6.



NOTES
2. RECOMMENDED PCB THICKNESS: 1.6MM
3. PRODUCT SPECIFICATION: PS-99020-0001



REVISE PIN DIM
EC NO: S2012-0325
DRWN:SKANG
CHKD:ATSEE
APPR:MLONG
REV
M2

QUALITY
SYMBOLS
F_A=0
F_B=0
F_C=0
REV

GENERAL TOLERANCES
(UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± ---
2 PLACES ± 0.05 ± .002
1 PLACE ± --- ± ---
ANGULAR ± ---°
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS


DIMENSION STYLE
MM ONLY
DRAWN BY DB DATE 16/07/87
CHECKED BY DB DATE 1987/07/16
APPROVED BY DB DATE 1987/07/16
MATERIAL NO.
SEE TABLE
SIZE A3
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE
NTS
DESIGN UNITS
METRIC
THIRD ANGLE
PROJECTION
C-GRID III
DUAL ROW RIGHT
ANGLE HEADER
MOLEX INCORPORATED
SDA-90122
SHEET NO.
1 OF 6

CKT SIZE	DIM. " A"		DIM. " B" ^{(+0.20 -0.35 +0.008 -0.014}		CKT SIZE	DIM. " A"		DIM. " B" ^{(±0.20 ±.008}	
2X 1	—————		(2.54) .100		2X21	(50.80) 2.000	(53.34) 2.100		
2X 2	(2.54)	.100	(5.08)	.200	2X22	(53.34) 2.100	(55.88)	2.200	
2X 3	(5.08)	.200	(7.62)	.300	2X23	(55.88) 2.200	(58.42)	2.300	
2X 4	(7.62)	.300	(10.16)	.400	2X24	(58.42) 2.300	(60.96)	2.400	
2X 5	(10.16)	.400	(12.70)	.500	2X25	(60.96) 2.400	(63.50)	2.500	
2X 6	(12.70)	.500	(15.24)	.600	2X26	(63.50) 2.500	(66.04)	2.600	
2X 7	(15.24)	.600	(17.78)	.700	2X27	(66.04) 2.600	(68.58)	2.700	
2X 8	(17.78)	.700	(20.32)	.800	2X28	(68.58) 2.700	(71.12)	2.800	
2X 9	(20.32)	.800	(22.86)	.900	2X29	(71.12) 2.800	(73.66)	2.900	
2X10	(22.86)	.900	(25.40)	1.000	2X30	(73.66) 2.900	(76.20)	3.000	
2X11	(25.40)	1.000	(27.94)	1.100	2X31	(76.20) 3.000	(78.74)	3.100	
2X12	(27.94)	1.100	(30.48)	1.200	2X32	(78.74) 3.100	(81.28)	3.200	
2X13	(30.48)	1.200	(33.02)	1.300	2X33	(81.28) 3.200	(83.82)	3.300	
2X14	(33.02)	1.300	(35.56)	1.400	2X34	(83.82) 3.300	(86.36)	3.400	
2X15	(35.56)	1.400	(38.10)	1.500	2X35	(86.36) 3.400	(88.90)	3.500	
2X16	(38.10)	1.500	(40.64)	1.600	2X36	(88.90) 3.500	(91.44)	3.600	
2X17	(40.64)	1.600	(43.18)	1.700	2X37	(91.44) 3.600	(93.98)	3.700	
2X18	(43.18)	1.700	(45.72)	1.800	2X38	(93.98) 3.700	(96.52)	3.800	
2X19	(45.72)	1.800	(48.26)	1.900	2X39	(96.52) 3.800	(99.06)	3.900	
2X20	(48.26)	1.900	(50.80)	2.000	2X40	(99.06) 3.900	(101.60)	4.000	

NOTES

1. FOR ASSY NUMBERS WITH FINISH OPTIONS
AND DIM'S C & D SEE SHEETS 2 TO 6.



	10	9		8		7		6		5		4		3		2		1	
F		CIRCUIT SIZE		PLATING TYPE A PART NO.		PLATING TYPE E PART NO.		PLATING TYPE F PART NO.											
		2 X 1		90122-0121		90122-0761		90122-0921											
		2 X 2		▲ -0122		▲ -0762		▲ -0922											
		2 X 3		-0123		-0763		-0923											
		2 X 4		-0124		-0764		-0924											
		2 X 5		-0125		-0765		-0925											
		2 X 6		-0126		-0766		-0926											
		2 X 7		-0127		-0767		-0927											
		2 X 8		-0128		-0768		-0928											
		2 X 9		-0129		-0769		-0929											
E	DIM C (±0.20) ±.008 (6.75) .266	2 X 10		-0130		-0770		-0930											
		2 X 11		-0131		-0771		-0931											
		2 X 12		-0132		-0772		-0932											
		2 X 13		-0133		-0773		-0933											
		2 X 14		-0134		-0774		-0934											
		2 X 15		-0135		-0775		-0935											
		2 X 16		-0136		-0776		-0936											
		2 X 17		-0137		-0777		-0937											
		2 X 18		-0138		-0778		-0938											
		2 X 19		-0139		-0779		-0939											
D	DIM D (±0.25) ±.010 (2.90) .114	2 X 20		-0140		-0780		-0940											
		2 X 21		-0141		-0781		-0941											
		2 X 22		-0142		-0782		-0942											
		2 X 23		-0143		-0783		-0943											
		2 X 24		-0144		-0784		-0944											
		2 X 25		-0145		-0785		-0945											
		2 X 26		-0146		-0786		-0946											
		2 X 27		-0147		-0787		-0947											
		2 X 28		-0148		-0788		-0948											
		2 X 29		-0149		-0789		-0949											
C		2 X 30		-0150		-0790		-0950											
		2 X 31		-0151		-0791		-0951											
		2 X 32		-0152		-0792		-0952											
		2 X 33		-0153		-0793		-0953											
		2 X 34		-0154		-0794		-0954											
		2 X 35		-0155		-0795		-0955											
		2 X 36		-0156		-0796		-0956											
		2 X 37		-0157		-0797		-0957											
		2 X 38		-0158		-0798		-0958											
		2 X 39		▼ -0159		▼ -0799		▼ -0959											
B		2 X 40		90122-0160		90122-0800		90122-0960											
A	NOTES: FOR PLATING VARIATIONS SEE ENG.STD. SDES-99000-0003.																		

	10	9	8	7	6	5	4	3	2	1	
F		CIRCUIT SIZE	PLATING TYPE A PART NO.	PLATING TYPE E PART NO.	PLATING TYPE F PART NO.		CIRCUIT SIZE	PLATING TYPE A PART NO.	PLATING TYPE E PART NO.	PLATING TYPE F PART NO.	F
		2 X 1	90122-0041	90122-0681	90122-0841		2 X 1	90122-0081	90122-0721	90122-0881	
		2 X 2	▲ -0042	▲ -0682	▲ -0842		2 X 2	▲ -0082	▲ -0722	▲ -0882	
		2 X 3	-0043	-0683	-0843		2 X 3	-0083	-0723	-0883	
		2 X 4	-0044	-0684	-0844		2 X 4	-0084	-0724	-0884	
		2 X 5	-0045	-0685	-0845		2 X 5	-0085	-0725	-0885	
		2 X 6	-0046	-0686	-0846		2 X 6	-0086	-0726	-0886	
		2 X 7	-0047	-0687	-0847		2 X 7	-0087	-0727	-0887	
		2 X 8	-0048	-0688	-0848		2 X 8	-0088	-0728	-0888	
		2 X 9	-0049	-0689	-0849		2 X 9	-0089	-0729	-0889	
		2 X 10	-0050	-0690	-0850		2 X 10	-0090	-0730	-0890	
		2 X 11	-0051	-0691	-0851		2 X 11	-0091	-0731	-0891	
		2 X 12	-0052	-0692	-0852		2 X 12	-0092	-0732	-0892	
		2 X 13	-0053	-0693	-0853		2 X 13	-0093	-0733	-0893	
		2 X 14	-0054	-0694	-0854		2 X 14	-0094	-0734	-0894	
		2 X 15	-0055	-0695	-0855		2 X 15	-0095	-0735	-0895	
		2 X 16	-0056	-0696	-0856		2 X 16	-0096	-0736	-0896	
		2 X 17	-0057	-0697	-0857		2 X 17	-0097	-0737	-0897	
		2 X 18	-0058	-0698	-0858		2 X 18	-0098	-0738	-0898	
		2 X 19	-0059	-0699	-0859		2 X 19	-0099	-0739	-0899	
		2 X 20	-0060	-0700	-0860		2 X 20	-0100	-0740	-0900	
		2 X 21	-0061	-0701	-0861		2 X 21	-0101	-0741	-0901	
		2 X 22	-0062	-0702	-0862		2 X 22	-0102	-0742	-0902	
		2 X 23	-0063	-0703	-0863		2 X 23	-0103	-0743	-0903	
		2 X 24	-0064	-0704	-0864		2 X 24	-0104	-0744	-0904	
		2 X 25	-0065	-0705	-0865		2 X 25	-0105	-0745	-0905	
		2 X 26	-0066	-0706	-0866		2 X 26	-0106	-0746	-0906	
		2 X 27	-0067	-0707	-0867		2 X 27	-0107	-0747	-0907	
		2 X 28	-0068	-0708	-0868		2 X 28	-0108	-0748	-0908	
		2 X 29	-0069	-0709	-0869		2 X 29	-0109	-0749	-0909	
		2 X 30	-0070	-0710	-0870		2 X 30	-0110	-0750	-0910	
		2 X 31	-0071	-0711	-0871		2 X 31	-0111	-0751	-0911	
		2 X 32	-0072	-0712	-0872		2 X 32	-0112	-0752	-0912	
		2 X 33	-0073	-0713	-0873		2 X 33	-0113	-0753	-0913	
		2 X 34	-0074	-0714	-0874		2 X 34	-0114	-0754	-0914	
		2 X 35	-0075	-0715	-0875		2 X 35	-0115	-0755	-0915	
		2 X 36	-0076	-0716	-0876		2 X 36	-0116	-0756	-0916	
		2 X 37	-0077	-0717	-0877		2 X 37	-0117	-0757	-0917	
		2 X 38	-0078	-0718	-0878		2 X 38	-0118	-0758	-0918	
		2 X 39	▼ -0079	▼ -0719	▼ -0879		2 X 39	▼ -0119	▼ -0759	▼ -0919	
		2 X 40	90122-0080	90122-0720	90122-0880		2 X 40	90122-0120	90122-0760	90122-0920	
E		DIM C (± 0.20) $\pm .008$ (5.75) .226					DIM C (± 0.20) $\pm .008$ (5.75) .226				E
D		DIM D (± 0.25) $\pm .010$ (2.90) .114					DIM D (± 0.25) $\pm .010$ (4.50) .177				D
C											C
B											B

NOTES:
FOR PLATING VARIATIONS SEE
ENG.STD. SDES-99000-0003.

REVISE PIN DIM EC NO: S2012-0325 2011/10/21 DRWN:SKANG CHKD:ATSEE 2011/10/31 APPR:MLONG 2011/10/31			DESCRIPTION	QUALITY SYMBOLS FA=0 FE=0 FP=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		mm			INCH	DRAWN BY DATE		TITLE C-GRID III DUAL ROW RIGHT ANGLE HEADER				
4 PLACES ± --- ± ---					DB 16/07/87							
3 PLACES ± --- ± ---					CHECKED BY DATE		MOLEX INCORPORATED					
2 PLACES ± 0.05 ± .002					DB 1987/07/16							
1 PLACE ± --- ± ---					APPROVED BY DATE		SDA-90122					
ANGULAR ± ---°					DB 1987/07/16							
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE		DOCUMENT NO.		SHEET NO. 3 OF 6				
M2		REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

	10		9		8		7		6		5		4		3		2		1																																																																																																		
F	CIRCUIT SIZE		PLATING TYPE A PART NO.		PLATING TYPE E PART NO.		PLATING TYPE F PART NO.																																																																																																														
		2 X 1	90122-0161	90122-0801	90122-0961																																																																																																																
		2 X 2	▲ -0162	▲ -0802	▲ -0962																																																																																																																
		2 X 3	-0163	-0803	-0963																																																																																																																
		2 X 4	-0164	-0804	-0964																																																																																																																
		2 X 5	-0165	-0805	-0965																																																																																																																
		2 X 6	-0166	-0806	-0966																																																																																																																
		2 X 7	-0167	-0807	-0967																																																																																																																
		2 X 8	-0168	-0808	-0968																																																																																																																
		2 X 9	-0169	-0809	-0969																																																																																																																
E	DIM C (±0.20) ±.008 (6.75) .266	2 X 10	-0170	-0810	-0970																																																																																																																
		2 X 11	-0171	-0811	-0971																																																																																																																
		2 X 12	-0172	-0812	-0972																																																																																																																
		2 X 13	-0173	-0813	-0973																																																																																																																
		2 X 14	-0174	-0814	-0974																																																																																																																
		2 X 15	-0175	-0815	-0975																																																																																																																
		2 X 16	-0176	-0816	-0976																																																																																																																
		2 X 17	-0177	-0817	-0977																																																																																																																
		2 X 18	-0178	-0818	-0978																																																																																																																
		2 X 19	-0179	-0819	-0979																																																																																																																
D	DIM D (±0.25) ±.010 (4.50) .177	2 X 20	-0180	-0820	-0980																																																																																																																
		2 X 21	-0181	-0821	-0981																																																																																																																
		2 X 22	-0182	-0822	-0982																																																																																																																
		2 X 23	-0183	-0823	-0983																																																																																																																
		2 X 24	-0184	-0824	-0984																																																																																																																
		2 X 25	-0185	-0825	-0985																																																																																																																
		2 X 26	-0186	-0826	-0986																																																																																																																
		2 X 27	-0187	-0827	-0987																																																																																																																
		2 X 28	-0188	-0828	-0988																																																																																																																
		2 X 29	-0189	-0829	-0989																																																																																																																
C		2 X 30	-0190	-0830	-0990																																																																																																																
	2 X 31	-0191	-0831	-0991																																																																																																																	
	2 X 32	-0192	-0832	-0992																																																																																																																	
	2 X 33	-0193	-0833	-0993																																																																																																																	
	2 X 34	-0194	-0834	-0994																																																																																																																	
	2 X 35	-0195	-0835	-0995																																																																																																																	
	2 X 36	-0196	-0836	-0996																																																																																																																	
	2 X 37	-0197	-0837	-0997																																																																																																																	
	2 X 38	-0198	-0838	-0998																																																																																																																	
	2 X 39	▼ -0199	▼ -0839	▼ -0999																																																																																																																	
B		2 X 40	90122-0200	90122-0840	90122-1000																																																																																																																
A	NOTES: FOR PLATING VARIATIONS SEE ENG.STD. SDES-99000-0003.																																																																																																																				
	<table><tr><td rowspan="11">REVISE PIN DIM EC NO: S2012-0325 2011/10/21 DRWN:SKANG CHKD:ATSEE 2011/10/31 APPR:MLONG 2011/10/31</td><td rowspan="11">DESCRIPTION</td><td>QUALITY SYMBOLS</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2" rowspan="10"> THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="4"> </td><td rowspan="4">4 PLACES 3 PLACES 2 PLACES 1 PLACE</td><td rowspan="4">mm INCH</td><td rowspan="4">±--- ±--- ±0.05 ±---</td><td rowspan="4">±--- ±--- ±.002 ±---</td><td rowspan="4">DRAWN BY DATE CHECKED BY DATE APPROVED BY DATE</td><td rowspan="4">DB 16/07/87 DB 1987/07/16 DB 1987/07/16</td></tr><tr><td colspan="2">ANGULAR ±---°</td><td colspan="2">APPROVED BY DATE</td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">MATERIAL NO.</td></tr><tr><td colspan="2">SEE TABLE</td><td colspan="2">DOCUMENT NO.</td></tr><tr><td colspan="2">SIZE A3</td><td colspan="4">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td><td colspan="2">SHEET NO. 4 OF 6</td></tr><tr><td colspan="10"></td></tr><tr><td colspan="10"></td></tr><tr><td colspan="10"></td></tr><tr><td colspan="10"></td></tr><tr><td colspan="10"></td></tr><tr><td colspan="10"></td></tr></table>																			REVISE PIN DIM EC NO: S2012-0325 2011/10/21 DRWN:SKANG CHKD:ATSEE 2011/10/31 APPR:MLONG 2011/10/31	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		 	4 PLACES 3 PLACES 2 PLACES 1 PLACE	mm INCH	±--- ±--- ±0.05 ±---	±--- ±--- ±.002 ±---	DRAWN BY DATE CHECKED BY DATE APPROVED BY DATE	DB 16/07/87 DB 1987/07/16 DB 1987/07/16	ANGULAR ±---°		APPROVED BY DATE		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		SEE TABLE		DOCUMENT NO.		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				SHEET NO. 4 OF 6																																																													
	REVISE PIN DIM EC NO: S2012-0325 2011/10/21 DRWN:SKANG CHKD:ATSEE 2011/10/31 APPR:MLONG 2011/10/31	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																																																											
			 	4 PLACES 3 PLACES 2 PLACES 1 PLACE	mm INCH	±--- ±--- ±0.05 ±---	±--- ±--- ±.002 ±---	DRAWN BY DATE CHECKED BY DATE APPROVED BY DATE	DB 16/07/87 DB 1987/07/16 DB 1987/07/16																																																																																																												
												ANGULAR ±---°		APPROVED BY DATE																																																																																																							
												DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.																																																																																																							
												SEE TABLE		DOCUMENT NO.																																																																																																							
			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				SHEET NO. 4 OF 6																																																																																																												
fb_frame_A3_P_AM.T Rev. F 2009/06/18																																																																																																																					
	9		8		7		6		5		4		3		2		1																																																																																																				

	10		9		8		7		6		5		4		3		2		1			
F			CIRCUIT SIZE		PLATING TYPE B PART NO.		PLATING TYPE C PART NO.		PLATING TYPE D PART NO.		PLATING TYPE G PART NO.		CIRCUIT SIZE		PLATING TYPE B PART NO.		PLATING TYPE C PART NO.		PLATING TYPE D PART NO.		PLATING TYPE G PART NO.	F
			2 X 1		90122-0281		90122-0441		90122-0601		90122-1081		2 X 1		90122-0201		90122-0361		90122-0521		90122-1001	
			2 X 2		▲ -0282		▲ -0442		▲ -0602		▲ -1082		2 X 2		▲ -0202		▲ -0362		▲ -0522		▲ -1002	
			2 X 3		-0283		-0443		-0603		-1083		2 X 3		-0203		-0363		-0523		-1003	
			2 X 4		-0284		-0444		-0604		-1084		2 X 4		-0204		-0364		-0524		-1004	
			2 X 5		-0285		-0445		-0605		-1085		2 X 5		-0205		-0365		-0525		-1005	
			2 X 6		-0286		-0446		-0606		-1086		2 X 6		-0206		-0366		-0526		-1006	
			2 X 7		-0287		-0447		-0607		-1087		2 X 7		-0207		-0367		-0527		-1007	
			2 X 8		-0288		-0448		-0608		-1088		2 X 8		-0208		-0368		-0528		-1008	
			2 X 9		-0289		-0449		-0609		-1089		2 X 9		-0209		-0369		-0529		-1009	
			2 X 10		-0290		-0450		-0610		-1090		2 X 10		-0210		-0370		-0530		-1010	
			2 X 11		-0291		-0451		-0611		-1091		2 X 11		-0211		-0371		-0531		-1011	
			2 X 12		-0292		-0452		-0612		-1092		2 X 12		-0212		-0372		-0532		-1012	
			2 X 13		-0293		-0453		-0613		-1093		2 X 13		-0213		-0373		-0533		-1013	
			2 X 14		-0294		-0454		-0614		-1094		2 X 14		-0214		-0374		-0534		-1014	
			2 X 15		-0295		-0455		-0615		-1095		2 X 15		-0215		-0375		-0535		-1015	
			2 X 16		-0296		-0456		-0616		-1096		2 X 16		-0216		-0376		-0536		-1016	
			2 X 17		-0297		-0457		-0617		-1097		2 X 17		-0217		-0377		-0537		-1017	
			2 X 18		-0298		-0458		-0618		-1098		2 X 18		-0218		-0378		-0538		-1018	
			2 X 19		-0299		-0459		-0619		-1099		2 X 19		-0219		-0379		-0539		-1019	
			2 X 20		-0300		-0460		-0620		-1100		2 X 20		-0220		-0380		-0540		-1020	
			2 X 21		-0301		-0461		-0621		-1101		2 X 21		-0221		-0381		-0541		-1021	
			2 X 22		-0302		-0462		-0622		-1102		2 X 22		-0222		-0382		-0542		-1022	
			2 X 23		-0303		-0463		-0623		-1103		2 X 23		-0223		-0383		-0543		-1023	
			2 X 24		-0304		-0464		-0624		-1104		2 X 24		-0224		-0384		-0544		-1024	
			2 X 25		-0305		-0465		-0625		-1105		2 X 25		-0225		-0385		-0545		-1025	
			2 X 26		-0306		-0466		-0626		-1106		2 X 26		-0226		-0386		-0546		-1026	
			2 X 27		-0307		-0467		-0627		-1107		2 X 27		-0227		-0387		-0547		-1027	
			2 X 28		-0308		-0468		-0628		-1108		2 X 28		-0228		-0388		-0548		-1028	
			2 X 29		-0309		-0469		-0629		-1109		2 X 29		-0229		-0389		-0549		-1029	
			2 X 30		-0310		-0470		-0630		-1110		2 X 30		-0230		-0390		-0550		-1030	
			2 X 31		-0311		-0471		-0631		-1111		2 X 31		-0231		-0391		-0551		-1031	
			2 X 32		-0312		-0472		-0632		-1112		2 X 32		-0232		-0392		-0552		-1032	
			2 X 33		-0313		-0473		-0633		-1113		2 X 33		-0233		-0393		-0553		-1033	
			2 X 34		-0314		-0474		-0634		-1114		2 X 34		-0234		-0394		-0554		-1034	
			2 X 35		-0315		-0475		-0635		-1115		2 X 35		-0235		-0395		-0555		-1035	
			2 X 36		-0316		-0476		-0636		-1116		2 X 36		-0236		-0396		-0556		-1036	
			2 X 37		-0317		-0477		-0637		-1117		2 X 37		-0237		-0397		-0557		-1037	
			2 X 38		-0318		-0478		-0638		-1118		2 X 38		-0238		-0398		-0558		-1038	
			2 X 39		▼ -0319		▼ -0479		▼ -0639		▼ -1119		2 X 39		▼ -0239		▼ -0399		▼ -0559		▼ -1039	
			2 X 40		90122-0320		90122-0480		90122-0640		90122-1120		2 X 40		90122-0240		90122-0400		90122-0560		90122-1040	

DIM
C (± 0.20)
 $\pm .008$
(6.75)
.266

DIM
D (± 0.25)
 $\pm .010$
(2.90)
.114

DIM
C (± 0.20)
 $\pm .008$
(5.75)
.226

DIM
D (± 0.25)
 $\pm .010$
(2.90)
.114

NOTES:
FOR PLATING VARIATIONS SEE
ENG.STD. SDES-99000-0003.

REVISE PIN DIM EC NO: S2012-0325		2011/10/21 DRWN:SKANG	2011/10/31 CHKD:ATSEE	2011/10/31 APPR:MLONG	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
							mm	INCH	DRAWN BY	DATE	TITLE				
$\nabla_A=0$							4 PLACES	$\pm \text{---}$	$\pm \text{---}$	DB	16/07/87	C-GRID III DUAL ROW RIGHT ANGLE HEADER			
							3 PLACES	$\pm \text{---}$	$\pm \text{---}$	CHECKED BY	DATE				
$\nabla_B=0$							2 PLACES	± 0.05	$\pm .002$	DB	1987/07/16	MOLEX INCORPORATED			
							1 PLACE	$\pm \text{---}$	$\pm \text{---}$	APPROVED BY	DATE				
$\nabla_P=0$							ANGULAR $\pm \text{---}^\circ$		DB	1987/07/16	MOLEX		SDA-90122		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							MATERIAL NO.		DOCUMENT NO.		SHEET NO.				
									SEE TABLE		5 OF 6				
M2							THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

	10	9	8	7	6	5	4	3	2	1			
F		CIRCUIT SIZE	PLATING TYPE B PART NO.	PLATING TYPE C PART NO.	PLATING TYPE D PART NO.	PLATING TYPE G PART NO.		CIRCUIT SIZE	PLATING TYPE B PART NO.	PLATING TYPE C PART NO.	PLATING TYPE D PART NO.	PLATING TYPE G PART NO.	F
		2 X 1	90122-0241	90122-0401	90122-0561	90122-1041		2 X 1	90122-0321	90122-0481	90122-0641	90122-1121	
E	DIM C (± 0.20) $\pm .008$ (5.75) .226	2 X 2	▲ -0242	▲ -0402	▲ -0562	▲ -1042		2 X 2	▲ -0322	▲ -0482	▲ -0642	▲ -1122	E
		2 X 3	-0243	-0403	-0563	-1043		2 X 3	-0323	-0483	-0643	-1123	
		2 X 4	-0244	-0404	-0564	-1044		2 X 4	-0324	-0484	-0644	-1124	
		2 X 5	-0245	-0405	-0565	-1045		2 X 5	-0325	-0485	-0645	-1125	
		2 X 6	-0246	-0406	-0566	-1046		2 X 6	-0326	-0486	-0646	-1126	
		2 X 7	-0247	-0407	-0567	-1047		2 X 7	-0327	-0487	-0647	-1127	
		2 X 8	-0248	-0408	-0568	-1048		2 X 8	-0328	-0488	-0648	-1128	
		2 X 9	-0249	-0409	-0569	-1049		2 X 9	-0329	-0489	-0649	-1129	
		2 X 10	-0250	-0410	-0570	-1050		2 X 10	-0330	-0490	-0650	-1130	
		2 X 11	-0251	-0411	-0571	-1051		2 X 11	-0331	-0491	-0651	-1131	
D	DIM D (± 0.25) $\pm .010$ (4.50) .177	2 X 12	-0252	-0412	-0572	-1052		2 X 12	-0332	-0492	-0652	-1132	D
		2 X 13	-0253	-0413	-0573	-1053		2 X 13	-0333	-0493	-0653	-1133	
		2 X 14	-0254	-0414	-0574	-1054		2 X 14	-0334	-0494	-0654	-1134	
		2 X 15	-0255	-0415	-0575	-1055		2 X 15	-0335	-0495	-0655	-1135	
		2 X 16	-0256	-0416	-0576	-1056		2 X 16	-0336	-0496	-0656	-1136	
		2 X 17	-0257	-0417	-0577	-1057		2 X 17	-0337	-0497	-0657	-1137	
		2 X 18	-0258	-0418	-0578	-1058		2 X 18	-0338	-0498	-0658	-1138	
		2 X 19	-0259	-0419	-0579	-1059		2 X 19	-0339	-0499	-0659	-1139	
		2 X 20	-0260	-0420	-0580	-1060		2 X 20	-0340	-0500	-0660	-1140	
		2 X 21	-0261	-0421	-0581	-1061		2 X 21	-0341	-0501	-0661	-1141	
C		2 X 22	-0262	-0422	-0582	-1062		2 X 22	-0342	-0502	-0662	-1142	C
		2 X 23	-0263	-0423	-0583	-1063		2 X 23	-0343	-0503	-0663	-1143	
		2 X 24	-0264	-0424	-0584	-1064		2 X 24	-0344	-0504	-0664	-1144	
		2 X 25	-0265	-0425	-0585	-1065		2 X 25	-0345	-0505	-0665	-1145	
		2 X 26	-0266	-0426	-0586	-1066		2 X 26	-0346	-0506	-0666	-1146	
		2 X 27	-0267	-0427	-0587	-1067		2 X 27	-0347	-0507	-0667	-1147	
		2 X 28	-0268	-0428	-0588	-1068		2 X 28	-0348	-0508	-0668	-1148	
		2 X 29	-0269	-0429	-0589	-1069		2 X 29	-0349	-0509	-0669	-1149	
		2 X 30	-0270	-0430	-0590	-1070		2 X 30	-0350	-0510	-0670	-1150	
		2 X 31	-0271	-0431	-0591	-1071		2 X 31	-0351	-0511	-0671	-1151	
B		2 X 32	-0272	-0432	-0592	-1072		2 X 32	-0352	-0512	-0672	-1152	B
		2 X 33	-0273	-0433	-0593	-1073		2 X 33	-0353	-0513	-0673	-1153	
		2 X 34	-0274	-0434	-0594	-1074		2 X 34	-0354	-0514	-0674	-1154	
		2 X 35	-0275	-0435	-0595	-1075		2 X 35	-0355	-0515	-0675	-1155	
		2 X 36	-0276	-0436	-0596	-1076		2 X 36	-0356	-0516	-0676	-1156	
		2 X 37	-0277	-0437	-0597	-1077		2 X 37	-0357	-0517	-0677	-1157	
		2 X 38	-0278	-0438	-0598	-1078		2 X 38	-0358	-0518	-0678	-1158	
		2 X 39	▼ -0279	▼ -0439	▼ -0599	▼ -1079		2 X 39	▼ -0359	▼ -0519	▼ -0679	▼ -1159	
		2 X 40	90122-0280	90122-0440	90122-0600	90122-1080		2 X 40	90122-0360	90122-0520	90122-0680	90122-1160	

NOTES:
FOR PLATING VARIATIONS SEE
ENG.STD. SDES-99000-0003.

REVISE PIN DIM EC NO: S2012-0325 DRWN:SKANG CHKD:ATSEE APPR:MLONG 2011/10/31 2011/10/31	QUALITY SYMBOLS $F_A=0$ $F_B=0$ $F_P=0$	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY DB	DATE 16/07/87	TITLE			
		4 PLACES	± ---	± ---	CHECKED BY DB	DATE 1987/07/16	C-GRID III DUAL ROW RIGHT ANGLE HEADER MOLEX INCORPORATED			
		3 PLACES	± ---	± ---	APPROVED BY DB	DATE 1987/07/16				
		2 PLACES	± 0.05	± .002	MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
1 PLACE	± ---	± ---	SEE TABLE		SDA-90122		6 OF 6			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						